

Asia Pacific Only

Fisher® Product Type Number ⁽¹⁾						
50	133	912N	C486	HSR	P539A	T208
61	133-LP	1098-EGR	C891	HSRL	P551, P551A	VS100
63EG	133HP	1190	CP200	J31	P590	Y600A
63EG-98HM	161	1290	CP400	J500	P650	Y602
64-LP	167D	1301	CS200	LR125	P700	Y610A, Y611A, Y612A
63EG-LP	168, 168H, 68	1301-LP	CS200-LP	LR128	R122H	Y690A - TB
66	252	1305	CS400	M3162	R130	Y690A - NG
66R	289	1367	CS400-LP	M570	R222	Y690VB
67C	289H	1805	CS800	MR95	R232	Y692
67C-LP	289P	1805P	CSB400	MR98	R232A	Y692VB
67D	289RC	1808	D	MR105	R232E	Y693
75A	299H, 299HS	6350, 6360	EZH, EZHOSX	MR108	R600	Y695A
92B	299H-LP	6365, 6358	EZL, EZLOSX	N100, N100A, N110	R622	Y695VR
92C	310A	ACE S.A.M.	EZR, EZROSX	N120	R632	Y696
92S	627	ACE95	EZR Relief	N201	R632A	Y696VR
92W	627-LP	ACE95jr	F100	N300, N400	R632E	----
95	627F	ACE95SR	G100	N480 & N481	R622E & R652E	----
98	627W, 627WH	ACE97	G200	N551	R622H	----
98H-LP	630	B NG	H120	N562	S200	----
99	630-LP	C407-10	H120-LP	N563	S402Y	----
99-LP	630R	C471, C477	H200	P100A, P102A, P100C	SR5	----
112	670	C483, C484	H284 & H5114	P163, P164	SR8	----
119	749B	C404-32	H722 & H733	P313 & P340	T205	----
122A	912	C804H-32	H800	P520L	T205B	----
Tartarini™ Product Type Number ⁽¹⁾						
971	BM5	CRONOS	MF, MN	PS & RE Series	RP/10	----
A/100	BM6X	DOSAODOR-D	MIC, MIR	R Series	SR, SRS, STP, STL	----
A/140	BM7	FA, FAG	OL ODORIZER	RLC/20	V/50, V/60, V/20	----
B/240	CNF, CN, CF	FL	PRX	RP	VS/FL	----
Francel™ Product Type Number ⁽¹⁾						
TYPE B	BLE, BLX	OSE	REGAL 3	RPE	----	----
TESCOM™ Product Type Number ⁽¹⁾						
04 Series	44-2200	64-2800	Line Pressure Reducer 6.0	26-1700	Diaphragm Metering Valve	ER3000
12 Series	44-2600	64-3200	MiniLabo 2	26-2300	High Pressure Valve	ER3000 Kits
15 Series	44-2800	64-3400	MiniLabo 2 Ultra High Purity	26-2500	Metal Bellows Shut-off Valve	ER3100 & ER3110
20-1000	44-3200	64-3600	PH-1600	26-2700	Metal Diaphragm Shut-off Valve	ER5000
20-1100	44-3400	64-5000	PH-1800	26-2900	Needle Metering Valve	70-2000
20-1200	44-4000	64-5400	PH-2200	44-1700	VA/VG Series	Systems Capabilities
22-2200	44-4200	74-2400	PH-2600	44-2300	VJ	Pressure Transducers (100-625)
22-5400	44-4600	74-3000	PH-3200	44-2500	VK	42 MW Series
23 Series	44-5000	74-3800	PS-3400	44-2900	VM	Filters (98 Series)
26-1000	44-5200	BB-1 Series	Regulus 3	44-4700	VN	Filters (TEE Type)
26-1100	44-5800	BE Series	Regulus 4	44-5500	VT	Pressure Gauges
26-1200	44-7400	CP32 Series	Regulus Stainless Steel	54-2100	Changeover Regulator (ACS012)	----
26-1500	449-254 Series	DA Series	SG1 Series	54-2300	Changeover Regulator (ACS3200)	----
26-1600	50-2000	DG Series	SG2 Series	54-2700	Changeover Regulator (CR441800)	----
26-2000	50-2200	DH Series	SG3 Series	54-3500	Changeover Regulator (CS-2200)	----
44-1100	54-2000	DH-16 Series	SJS Series	BB-3 Series	Compact Panel	----
44-1300	54-2200	DK Series	Wega 1 & 2	DV Series	Compact Panel Ultra High Purity	----
44-1500	54-2800	FR-2000 Series	Wega Corrosive Gases & Purging	30 Series	High Pressure Panel	----
44-1800	64-2600	Labo-F & Doppelregulus	Wega Mini	CC Metering Valve	NA-4 Series	----
1. Some products, systems and/or accessories may not be available in a particular country. Please consult your local Sales Office for current product availability.						