



Zoned Safety Manifold Reliability Data



Series	Type	Description	Component	Comments	Version	B _{10d} (cycles)	MTTF _d (h)
503	ISO 15407-1 & 15407-2 (26mm)		RubberSpool Valve	Double Solenoid	5/2 Gh-Gh	30,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Rubber Spool Valve	Single Solenoid Spring Return	5/2 Gh-R	20,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Rubber Spool Valve	Single Solenoid Differential Air Return W/O Spring	5/2 Gh-D	20,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Rubber Spool Valve	Closed Center	5/3 W1	20,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Rubber Spool Valve	Pressure Center	5/3 W2	20,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Rubber Spool Valve	Open Center	5/3 W3	20,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Rubber Spool Valve	Dual 3-Way Normally Closed	2x3/2NC-NC	20,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Rubber Spool Valve	Dual 3-Way Normally Open	2x3/2NO-NO	20,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Metal Spool Valve	Single Solenoid Spring Return	S&S - Mono	20,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Metal Spool Valve	Double Solenoid	S&S - Bi	20,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Rubber Spool Valve	Single Solenoid Spring Return	5/2 Gh-R	20,000,000	
503	ISO 15407-1 & 15407-2 (26mm)		Metal Spool Valve	Single Solenoid Spring Return	5/2 Gh-R	20,000,000	