

KJ2004X1-BA1 Remote Interface Unit

Hazardous Atmosphere



II 3 G

Nemko No. 02ATEX431U

EEx nA IIC T4

Power Specifications

LocalBus power rating +5 VDC at 300 mA (max)
+3.3 VDC at 500 mA (max)

Environmental Specifications

Ambient Temperature -40 to 70° C

Shock 10 G ½-sinewave for 11 ms

Vibration 1 mm peak-to-peak from 5 Hz to 16 Hz, 0.5 g from 16 Hz to 150 Hz

Airborne Contaminants ISA-S71.04 –1985 Airborne Contaminants Class G3

Relative Humidity 5% to 95% non-condensing

Note: See product label for serial number and location and date of manufacture.

Warning: This product has specific instructions for installation, removal and operation in hazardous areas. Refer to document 12P2046 "*DeltaV™ Scalable Process System Zone 2 Installation Instructions*". Other installation instructions are available in the "*Installing Your DeltaV™ Automation System*" manual.

The communications network connected to the DeltaV Remote Interface Unit must not be connected to a source that generates or contains under normal conditions a potential in excess of 60 VAC or 75 VDC.

Removal and Insertion

This unit cannot be removed or inserted with system power energized.

Maintenance and Adjustment

This unit contains no user serviceable parts and should not be disassembled for any reason. Calibration is not required.

Other Safety Approvals



CL. I Div. 2
GP. A, B, C, D
HAZ. LOC.
TEMP. Rating T4



LR87534