

KJ3212X1-BK1 S-Series Pulse Count Input Card

Hazardous Atmosphere



Nemko No. 11ATEX3029U
Ex nA IIC T4 Gc

Power Specifications

LocalBus power rating	12 VDC at 150 mA
Bussed field power rating	24 VDC at 150 mA
Field circuit rating	24 VDC at 25 mA/channel

Environmental Specifications

Ambient Temperature	-40 to 70° C
Shock	10g ½ Sinewave for 11 msec
Vibration	1mm Peak to Peak from 5 to 16Hz; 0.5g from 16 to 150Hz
Airborne Contaminants	ISA-S71.04 –1985 Airborne Contaminants Class G3
Relative Humidity	5 to 95% Non-Condensing IP 20 Rating
Terminal block key position	C6

Note: Refer to the product label for serial number and location and date of manufacture.

Warning: This product has specific instructions for installation, removal and operation in hazardous areas. Refer to document 12P5404 "*DeltaV™ S-Series Digital Automation System Zone 2 Installation Instructions*". Other installation instructions are available in the "*DeltaV™ S-series and CHARMs Hardware Installation*" manual.

Removal and Insertion

This unit cannot be removed or inserted with system power energized.

A terminal block fuse may NOT be removed with field power energized for non-sparking circuits.

A rotary keying system ensures compatibility between I/O cards and terminal blocks after installation is complete. The terminal block must have the keys set for the I/O card with which it is used.

Maintenance and Adjustment

This unit contains no user serviceable parts and should not be disassembled for any reason. Calibration is not required.

Other Safety Approvals



CL. 1 Div. 2
GP. A,B,C,D
HAZ. LOC.
TEMP. Rating T4

