



Member of the FM Global Group

FM Approvals
1151 Boston Providence Turnpike
P.O. Box 9102 Norwood, MA 02062 USA
T: 781 762 4300 F: 781-762-9375 www.fmaprovals.com

CERTIFICATE OF COMPLIANCE

ELECTRICAL EQUIPMENT

This certificate is issued for the following equipment:

OCX88A-abcdefgh. OCX 8800 Oxygen/Combustibles Transmitters.

Type 4X / IP66 *

a = Probe Length and Material 00, 11, 12, 13, 14, 21, 22, 23, 24, 31 or 32.

b = Probe Mounting Assembly 10, 11, 20 or 21.

c = Mounting Hardware - Stack Side 0, 1, 2, 3, 4 or 5.

d = Mounting Hardware - Probe Side 0, 1 or 4.

e = Electronics Housing H1, H2, H3, H4, F1, F2, F3 or F4.

f = Electronic Mounting 01, 02, 03, 04, 05, 06, 07 or 08.

g = In-Situ Filter 0, 1, 2 or 3

h = Accessories 0, 1, 2, 3, or 4

Special Conditions of Use:

*IP66 and Type 4X when reference air vents are routed to a dry area.

Equipment Ratings:

Series OCX 8800 Oxygen/Combustible Transmitters are suitable for Unclassified Locations; indoor and outdoor Type 4X / IP66.

FM Approved for:

Emerson Process Management Rosemount Analytical Inc.
Irvine, CA, USA

This certifies that the equipment described has been found to comply with the following Approval Standards and other documents:

Class 3810	2005
ANSI/NEMA 250	1991
ANSI/IEC 60529	2004

Original Project ID: 3024217

Approval Granted: September 21, 2005

Subsequent Revision Reports / Date Approval Amended

Report Number	Date	Report Number	Date
3035919	June 5, 2009		
RR201535	May 25, 2016		

FM Approvals LLC



J. E. Marquedant
Manager, Electrical Systems

25 May 2016
Date