

MATERIAL SAFETY DATA SHEET

MANUFACTURER: ROSEMOUNT ANALYTICAL INC.
ADDRESS: 2400 Barranca Parkway
Irvine, CA 92606

DATE REVISED: 3-23-11
PREPARED BY: T. Phillips

TELEPHONE: (949) 757-8500

(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

SECTION 1-Product Identification

Product Name: Conductivity Solution

Synonyms:

Part Number: SS6 SS6A

SECTION 2-Composition/Information on Ingredients

Ingredient(s)	CAS #	Percent	Hazardous
Water	7732-18-5	>99	no
Potassium Chloride	7447-40-7	0.1	no

SECTION 3-Hazards Identification

Health Rating: 0
Flammability Rating: 0
Reactivity Rating: 0

Lab Protective Equip: gloves, safety goggles

SECTION 4-First Aid Measures

INHALATION: No known effects, remove to fresh air if necessary.
INGESTION: Dilute with water. Seek medical attention. Do NOT induce vomiting unless directed to do so by medical personnel.
SKIN CONTACT: Wash with soap and water for 15 minutes.
EYE CONTACT: Flush with water for at least 15 minutes.

SECTION 5-Fire Fighting Measures

Fire: Non-flammable
Explosion: N/A
Fire Extinguishing Media: Fight Surrounding Fire
Special Information: N/A

SECTION 6-Accidental Release Measures

Rinse area with water; mop. Dispose in accordance with federal, state and local regulations.

SECTION 7-Handling and Storage

Keep in a tightly closed container, stored in a cool, dry, ventilated area.

SECTION 8-Exposure Controls/Personal Protection

Airborne Exposure Limits: N/A
Ventilation System: Normal room ventilation is generally adequate.
Personal Respirators (NIOSH Approved): Safety glasses.
Skin Protection: Gloves
Eye Protection: Use safety glasses or goggles.

SECTION 9-Physical and Chemical Properties

Appearance: Clear, colorless liquid
Odor: Odorless
Solubility: 100% Soluble
Specific Gravity: 1.00
pH: approximately 7
Boiling Point: Approximately 100°C
Melting Point: N/A
Vapor Density (Air=1): N/A
Vapor Pressure (mm Hg): N/E
Evaporation Rate (BuAc=1): N/E

SECTION 10-Stability and Reactivity

Stability: Stable
Hazardous Decomposition Products: not known
Hazardous Polymerization: Will not occur
Incompatibilities: None
Conditions to Avoid: None

SECTION 11-Toxicological Information:

Routes of absorption: Inhalation, skin, eyes, ingestion
Threshold limit value: N/E
Signs, symptoms and effects of exposure:
 Acute: N/A
 Chronic: N/A

Irritation Effects Data: None specified, possible sensitization from prolonged contact with raw material.

SECTION 12-Ecological Information

Environmental Fate: N/A
Environmental Toxicity: N/A

SECTION 13-Disposal Considerations

Material must be stored and disposed of in accordance with all local, state and federal laws.

SECTION 14-Transport Information

Not regulated

SECTION 15-Regulatory Information

Not regulated

SECTION 16-Other Information

N/A

NFPA Ratings: Health:0 Flammability:0 Reactivity:0

Rosemount Analytical Inc., a Division of Emerson Process Management, provides the information contained herein in good faith but makes no representation as to its comprehensiveness or accuracy. This document is intended only as a guide to the appropriate precautionary handling of the material by a properly trained person using this product. Individuals receiving the information must exercise their independent judgment in determining its appropriateness for a particular purpose. ROSEMOUNT ANALYTICAL INC. MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE WITH RESPECT TO THE INFORMATION SET FORTH HEREIN OR THE PRODUCT TO WHICH THE INFORMATION REFERS. ACCORDINGLY, ROSEMOUNT ANALYTICAL INC. WILL NOT BE RESPONSIBLE FOR DAMAGES RESULTING FROM USE OF OR RELIANCE UPON THIS INFORMATION.

.....

Prepared by: Rosemount Analytical Inc.
Phone Number: (949) 757-8500