

**MATERIAL SAFETY DATA SHEET**

MANUFACTURER: Manufactured for  
ROSEMOUNT ANALYTICAL INC.  
ADDRESS: 851 McKinley Avenue  
Colombus, OH 43222

DATE REVISED: 1-27-11  
PREPARED BY: T. Phillips

TELEPHONE: (614) 224-5345

(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

**SECTION 1-Product Identification**

**Product Name:** Reagent #2, color Reagent  
**Synonyms:** Ammonium Heptamolybdate  
**Part Number:** 180-1030-48

**SECTION 2-Composition/Information on Ingredients**

Ingredient(s)	CAS #	Percent	Hazardous
Water	7732-18-5	97	no
Proprietary Reagent	N/R	N/R	yes

**SECTION 3-Hazards Identification**

Health Rating: 1  
Flammability Rating: 0  
Reactivity Rating: 0

Lab Protective Equip: gloves, safety goggles

**SECTION 4-First Aid Measures**

INHALATION: N/A  
INGESTION: Human poisoning never reported  
SKIN CONTACT: Wash thoroughly with water  
EYE CONTACT: Wash thoroughly with water

**SECTION 5-Fire Fighting Measures**

**Fire:** Not Combustible  
**Explosion:** N/A  
**Fire Extinguishing Media:** Fight Surrounding Fire  
**Special Information:** May emit ammonia, nitrous gases and molybdenum trioxide fumes if in powder or crystal form. Not likely in solution.

**SECTION 6-Accidental Release Measures**

Wash area well with water

**SECTION 7-Handling and Storage**

None

**SECTION 8-Exposure Controls/Personal Protection**

Airborne Exposure Limits: N/E  
Ventilation System: Not Required  
Personal Respirators (NIOSH Approved): Not Required  
Skin Protection: Rubber Gloves  
Eye Protection: Safety Goggles

**SECTION 9-Physical and Chemical Properties**

Appearance: Clear, colorless liquid  
Odor: Odorless  
Solubility: Soluble  
Specific Gravity: N/E  
pH: N/E  
Boiling Point: Approximately 100°C  
Melting Point: N/A  
Vapor Density (Air=1): N/A  
Vapor Pressure (mm Hg): N/A  
Evaporation Rate (BuAc=1): N/A

**SECTION 10-Stability and Reactivity**

Stability: Stable  
Hazardous Decomposition Products: Will not occur  
Hazardous Polymerization: None  
Incompatibilities: N/A  
Conditions to Avoid: N/A

**SECTION 11-Toxicological Information:**  
None Reported

**SECTION 12-Ecological Information**

Environmental Fate: N/A  
Environmental Toxicity: N/A

**SECTION 13-Disposal Considerations**  
None Reported

**SECTION 14-Transport Information**  
N/A

**SECTION 15-Regulatory Information**  
None Reported

**SECTION 16-Other Information**  
N/A

**NFPA Ratings:** Health:1 Flammability:0 Reactivity:0

\*\*\*\*\*

**Rosemount Analytical Inc., a Division of Emerson Process Management, provides the information contained herein in good faith but makes no representation as to its comprehensiveness or accuracy. This document is intended only as a guide to the appropriate precautionary handling of the material by a properly trained person using this product. Individuals receiving the information must exercise their independent judgment in determining its appropriateness for a particular purpose. ROSEMOUNT ANALYTICAL INC. MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF**

**MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE WITH RESPECT TO THE INFORMATION SET FORTH HEREIN OR THE PRODUCT TO WHICH THE INFORMATION REFERS. ACCORDINGLY, ROSEMOUNT ANALYTICAL INC. WILL NOT BE RESPONSIBLE FOR DAMAGES RESULTING FROM USE OF OR RELIANCE UPON THIS INFORMATION.**

.....

**Prepared by: Rosemount Analytical Inc.**  
Phone Number: (949) 757-8500