



CABEL MARKING

MST/SPOT NO	WLS
1	+ Brown
2	- White
3	Gnd Shield
4	Yellow
5	Green
6	Blue
7	Violet
8	Grey
9	White
10	Pink
Common return	Black

MST/SPOT NO	OPTIONS
11	Brown Black
12	Red Black
13	Orange Black
14	Yellow Black

- ① T1 300mm FROM EYE BOLT IN LEVEL SENSOR
- ② POSSIBILITY EXIST TO SPECIFY WEIGHT FOR MOUNTING ON TOPSIDE OF WLS. WEIGHT DIA: 80mm /WEIGHT: 5KG. RECOMMENDED ANCHOR WEIGHT 3-15KG DEPEND ON INSTALLATION TYPE
- ③ ACTIVE PROBE LENGTH (500, 1000, OPTIONAL 1500)
- ④ DISTANCE TO BUTTOM CAN BE REDUCED TO 16mm BY REMOVING THE EYEBOLT
- ⑤ CALIBRATION DISTANCE TO BE USED FOR ZERO ADJUSTMENT DISTANCE IS FOUND ABOVE THE LINE IN THE TOP OF THE SENSOR

ISSUED BY	WEEK	PRODUCT CODE	TITLE	INSTALLATION DRAWING TITLE
GSP-AJ	0150	REX	ACAD	WATER LEVEL SENSOR
APPROVED BY	WEEK	ORIGINAL DWG NO.	SCALE	(WLS)
GSP	0150	9261 090-150		
ROSEMOUNT®		1 ST ANGLE	DOC TYPE	DWG NO.
Tank Gauging			2	9261 090-150
				ISSUE SHEET
				5 1/1

THE DESIGN/RESPONSIBILITY OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE CONTRACTOR MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR SUBJECT TO THE KNOWLEDGE OF A THIRD PARTY. COMMUNICATION WILL BE PROSECUTED. ROSEMOUNT TANK GAUGING AB, SWEDEN.