



FLÄNS ARTIKEL NR FLANGE ARTICLE NO	ØDi	ØD	ØDh	F	HAL HOLE		ANT PCS	Ds	FÖR FLÄNS FOR FLANGES	MAX PRESSURE AT 400°C
9150066-292	96	210	170	20	4	18	18	DN100 PN6	6 Bar	
9150066-264	96	220	180	22	8	18	18	DN100 PN10/16	16 Bar	
9150066-265	96	235	190	22	8	22	22	DN100 PN25/40	25 Bar	
9150066-266	96	229	191	22	8	22	22	ANSI 4" CLASS 150Lb	10 Bar	
9150066-267	96	254	200	22	8	22	22	ANSI 4" CLASS 300Lb	21 Bar	
9150066-293	125.5	265	225	22	8	18	18	DN150 PN6	6 Bar	
9150066-275	125.5	285	240	22	8	22	22	DN150 PN10/16	10.5 Bar	
9150066-276	125.5	279	241	22	8	22	22	ANSI 6" CLASS 150Lb	10 Bar	
9150066-280	125.5	318	270	22	12	22	22	ANSI 6" CLASS 300Lb	10.5 Bar	

- STANDARD BLIND FLANGE CAN BE MODIFIED TO FIT. THEN CHAMFER (5\*45) AND HOLE DI TO BE MACHINED. EN STANDARD BLIND FLÄNS KAN MODIFIERAS FÖR ATT PASSA. DA TILLOMER FASEN (5\*45) OCH Hålet DI.
- THE PART DELIVERED WITH MATERIAL CERTIFICATE, ACC TO DIN 50049/3.1B. DETALJEN LEVERERAD MED MATERIALCERTIFIKAT ENL. DIN 50049/3.1B.
- FLANGE MARKED WITH CHARGE NO (CH.NO) AND PART NO (P.NO). HEIGTH OF TEXT: MIN 5 MM. THE MARKING ACC. TO BOX BELOW: MÄRKNING ENLIGT RUTAN NEDAN:  

P.NO: 9150066-AAAY	CH.NO: XXXXX
--------------------	--------------

(A=ARTICLE NO./ARTIKEL NR.)  
(Y=REV. LTR./BOKSTAV.)  
(X=CHARGE NO./NR.)
- HOT-GALVANIZING Fe/Zn CLASS A SS3589 VARMFÖRZINKAD Fe/Zn KLASS A SS3589
- SHARP EDGES ARE TO BE BROKEN UNLESS OTHERWISE STATED. SKARPA KANTER BRYTES OM EJ ANNAT ANGES.

9150070-836

ISSUED BY GKT-AK	WEEK 9713	PRODUCT CODE TR PRO	MATERIAL Enr 1.0425, SS 1432-01
APPROVED BY GRT	WEEK 9739	DOC. TYPE 0 ACAD	TITLE FLANGE PROCESS SEAL
ALL DIMENSIONS ARE IN MILLIMETRES. TOLERANCES, UNLESS OTHERWISE STATED: FOR MACHINING: ISO 2768 FOR CASTING: ISO 8062 FOR WELDING: SS-EN ISO 13920, A, E		FINISH, UNLESS OTHERWISE STATED: 25	DWG NO. 9150070-836
1 ST ANGLE		SCALE	ISSUE SHEET 2 1/1



THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RÅDAR AB, SWEDEN.