

MODEL NO.


TVH-PB2GNMM1A11

PRODUCT LINE

Discrete Valve Controller

SPECIFICATIONS

Model	TVH, 316 Stainless Steel base and lid
Bus/Sensor	Profibus DP
Area Classification	Class 1, Div. 2, Groups A,B,C&D; Class II, Div. 2, Groups F&G; Type 4, 4X; Ex nA nC IIIC T4 Gc; Ex tc IIIC T115°C Dc, IP66/IP68
Visual Display	90° Green Open / Red Closed
Shaft	NAMUR, 304 Stainless Steel
Conduit Entries	(2) M20
O-rings	Silicone
Pilot	(1) 24Vdc pilot, 1W, fail open/closed
Spool Valve	Anodized Aluminum spool valve
Valve Cv	1.0 Cv w/ 1/4" NPT Ports
Manual Override	Single Pushbutton Momentary/ Latching Override
Temperature Rating	-40°C to 50°C



Current as of Jan 9, 2015 - subject to change without notice

TOPWORX

TopWorx, Inc.
3300 Fern Valley Rd.
Louisville, KY 40213

(502) 969-8000 ph.
(502) 969-5911 fax
www.topworx.com