



MODEL NO.
TVL-M20GNMM1A1
PRODUCT LINE

Valvetop Discrete Valve Controller

Model	Valvetop Model TVL, epoxy-coated A360 Aluminum enclosure
Bus Sensor	(2) Mech SPDT (10A@250VAC)
Area Classification	Intrinsically Safe; Ex ia IIC T4, Ex tb IIC T135C IP67, NEMA 4, 4X; CL I GPS A-D, CL 2 GPS E-F
Visual Display	90° Green Open / Red Closed
Shaft	NAMUR, 304 Stainless Steel
Conduit Entries	(2) M20
O-Rings	Silicone
Pilot	(1) 24Vdc, fail open/closed
Spool Valve	Aluminum - hard coat anodized, 1.0Cv with 1/4"NPT Ports
Valve Cv	1.0 Cv (1/4" NPT ports)
Manual Override	None
Temperature Rating	-40 °C to 60 °

Current as of Jun 12, 2013 - subject to change without notice.

TOPWORX
 TopWorx, Inc. (502) 969-8000 ph.
 3300 Fern Valley Rd. (502) 969-5911 fax
 Louisville, KY 40213 www.topworx.com