



MODEL NO.
TVL-P22GNEM161
PRODUCT LINE
Valvetop Discrete Valve Controller

Model	Valvetop Model TVL, epoxy-coated A360 Aluminum enclosure
Bus Sensor	(2) SPDT reed switch (3A max)
Area Classification	Class 1, Div. 2, Groups A,B,C&D; Class II, Div. 2 Groups F,G; Type 4,4x; Ex nA nC IIC T4 Gc Ex tc IIIC T115°C Dc, IP66/68
Visual Display	90° Green Open / Red Closed
Shaft	NAMUR, 304 Stainless Steel
Conduit Entries	(2) 3/4" NPT
O-Rings	Silicone
Pilot	(1) 24 vdc, fail open/closed
Spool Valve	316 Stainless Steel, 1.0Cv with 1/4" NPT Ports
Valve Cv	1.0 Cv (1/4" NPT ports)
Manual Override	None
Temperature Rating	-40 °C to 55 °C

Current as of Jun 12, 2013 - subject to change without notice.

TOPWORX
 TopWorx, Inc. (502) 969-8000 ph.
 3300 Fern Valley Rd. (502) 969-5911 fax
 Louisville, KY 40213 www.topworx.com