

Data sheet

Sheet No.: D101, Rev. C
Date: February 2016

Hytorch XL

Actuator Operating Speeds

XL26 to XL4581

Time is shown in seconds

Actuator Model	Operating Pressure = 80 psi (5.5 bar g)			
	Double Acting		Spring Return with S80 Springs	
	Opening Stroke	Closing Stroke	Opening Stroke	Closing Stroke
XL26	0.01	0.01	0.05	0.02
XL71	0.03	0.03	0.09	0.05
XL131	0.03	0.04	0.15	0.09
XL186	0.05	0.06	0.19	0.12
XL221	0.06	0.08	0.24	0.15
XL281	0.20	0.10	0.10	0.20
XL426	0.20	0.30	0.30	0.50
XL681	0.40	0.60	0.40	1.20
XL1127	0.70	0.60	0.50	0.70
XL1372	0.80	0.70	0.70	1.00
XL2586	1.50	1.20	1.20	1.50
XL4581	2.00	2.90	2.20	3.90



www.Hytorch.com

Copyright © Emerson Process Management. The information in this document is subject to change without notice.
Updated data sheets can be obtained from our website www.hytorch.com or from your nearest Valve Automation Center
USA: +1 813 630 2255 (fax 630 9449) UK: +44 191 5180020 (fax 5180032)

