



NOTE: Ground connection for over-voltage protection!

02 USB CONNECTION
USB 1.1 AND USB 2.0 COMPATIBLE
CABLE LENGTH: MAX 5m

TRL2 Bus to FCU or field devices (RTG & IDAU)
Single twisted, preferably shielded pair,
multidrop, polarity independent.
Individual shielding is mandatory if
parallel buses run in the same cable.

Recommended wiring length:
AWG 24 (0.25mm²): <1 km
AWG 22 (0.35mm²): <2 km
AWG 20 (0.50mm²): <3 km
AWG 18 (0.75mm²): <4 km

08	BUS CABLE	CUSTOMER
02	CABLE USB TYP A->B 3m	RTR
01	FBM 2180 TRL2 BUS MODEM	RTR
POS	ITEM DESCRIPTION	SUPPLIER
ISSUED BY	WEEK	PRODUCT CODE
GU-TKA	0537	REX
APPROVED BY	WEEK	ORIGINAL DWG NO.
GU-HF	0539	9150070-972
1 ST ANGLE	SCALE	INSTALLATION DRAWING TITLE
0.7	0.7	FBM 2180 USB CONNECTION
ROSEMOUNT Tank Gauging		
DOC TYPE DWG NO. ISSUE SHEET		
2 9150070-972 2 2/4		

THE COMPANY ASSUMES NO RESPONSIBILITY FOR THE ACCURACY OF THIS DOCUMENT. THE COMPANY WILL BE RESPONSIBLE FOR THE ACCURACY OF THIS DOCUMENT ONLY IF USED WITHOUT OUR AUTHORIZATION OR SUBJECT TO THE KNOWLEDGE OF A THIRD PARTY. COMMUNICATION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN.