


| No.    | L1     | t  | d2 | d3  | d4  |
|--------|--------|----|----|-----|-----|
| 1 1/2" | 300LBS | 20 | 22 | 114 | 155 |
| 2"     | 300LBS | 20 | 19 | 126 | 165 |

MTRL: STL. STEEL SS2342

|  |              |                             |               |  |
|--|--------------|-----------------------------|---------------|--|
| ISSUED BY<br>GKT-AK  | WEEK<br>9106 | PRODUCT CODE<br>REX         | TITLE<br>ACAD | INSTALLATION DRAWING TITLE<br>DIMENSIONAL DRAWING  |
| APPROVED BY<br>GKT   | WEEK<br>9242 | ORIGINAL DWG NO.<br>132-001 | SCALE<br>1:2  | FLANGED THERMOWELL   |
| <b>ROSEMOUNT</b><br>Tank Gauging   |              |                             |               | 1 ST ANGLE<br> |
| THE COMPANY ASSUMES NO RESPONSIBILITY FOR THE ACCURACY OF THIS DOCUMENT. THE USER SHALL BE RESPONSIBLE FOR THE ACCURACY OF THIS DOCUMENT. THE COMPANY SHALL NOT BE USED WITHOUT OUR AUTHORIZATION OR ENDORSEMENT TO THE KNOWLEDGE OF A THIRD PARTY. CONFORMANCE WILL BE PROSECUTED. ROSEMOUNT TANK GAUGING AB, SWEDEN. |              |                             |               | DOC TYPE<br>2  |
| DWG NO.<br>9242 132-001  |              |                             |               | ISSUE<br>4   |
| SHEET<br>1/1   |              |                             |               | INST. DWG. A3 070213   |