



LID SCREW  
SLOTTED HEAD

LCD-WINDOW  
PCB DDB  
(OPTION)

FOR ELECTRICAL CONNECTION  
SEE INSIDE THE LID

FOR MORE INFORMATION SEE ROSEMOUNT  
TANKRADAR REX INSTALLATION MANUAL

THE SLAVE DAU IS DESIGNED  
FOR USE IN HAZARDOUS AREA

CABLE ENTRY M20 FOR CABLE Ø10-14.

GROUND CONNECTION.  
SOCKET HEAD SCREW  
(FOR INSTALLATION ACC. TO  
NATIONAL CODE OF PRACTISE)

CABLE ENTRY M25 FOR CABLE Ø13-18.  
FOR RTG CONNECTION THE CABLE ENTRY MAY BE  
REPLACED BY THE HOSE COUPLING NIPPLE  
OF THE CABLE PROTECTION HOSE KIT.  
IF NECESSARY FIT THE REDUCTION ADAPTER FOR  
1/2" HOSE. MAKE SURE THE METAL HOSE IS  
ELECTRICALLY CONNECTED TO THE BOX.

PROTECTION CLASS IP65 IN COMPLIANCE WITH IEC 529

ISSUED BY GKM-EE	WEEK 9138	PRODUCT CODE REX	FILE ACAD	INSTALLATION DRAWING TITLE DIMENSIONAL DRAWING SLAVE DAU 2100		
APPROVED BY GKT	WEEK 9138	ORIGINAL DWG NO. D9240002-913	SCALE 1:2	DOC TYPE 2	DWG NO. D9240002-913	ISSUE 7
<b>ROSEMOUNT</b> Tank Gauging				1 ST ANGLE 1:1	SHEET 1/1	
THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN.						