


INCHES .XXX ± .005"
 (MILLIMETERS) .XX ± .020"
 X APPROX.

REV	DATE	BY	CL
A	04/04/05	14053	ERO



ENCLOSURE: IP65
 TORQUE: 6Kg.m (520 in-lbs)
 OPERATION TIME: 13sec
 POSITION SWITCH: 4 SPDT SWITCH
 CABLE ENTRY: 2 Plcs PG .531" (13.5)
 (1/4" - 1/2" Wire Cable)
 MOUNTING FLANGE: F03/F05/F07
 acc to DIN/ISO5211

