

KJ3242X1-EA1 Fieldbus H1 Terminal Block (Simplex)

Hazardous Atmosphere



Nemko No. 02ATEX431U

EEx nA IIC T4

Power Specifications

Voltage rating 35 VDC

Max current 500 mA

Environmental Specifications

Ambient Temperature -40 to 70° C

Shock 10g ½ Sinewave for 11 msec

Vibration 1mm Peak to Peak from 5 to 16Hz;
0.5g from 16 to 150Hz

Airborne Contaminants ISA-S71.04 –1985 Airborne
Contaminants Class G3

Relative Humidity 5 to 95% Non-Condensing IP 20
Rating

Note: Refer to the product label for serial number and location and date of manufacture.

Warning: This product has specific instructions for installation, removal and operation in hazardous areas. Refer to document 12P2046 "*DeltaV™ Scalable Process System Zone 2 Installation Instructions*". Other installation instructions are available in the "*Installing Your DeltaV Automation System*" manual.

Removal and Insertion

A rotary keying system ensures compatibility between I/O cards and terminal blocks after installation is complete. This terminal block must have the keys set for the I/O card it is to be used with.

Maintenance and Adjustment

This unit contains no user serviceable parts and should not be disassembled for any reason. Calibration is not required.

Other Safety Approvals



CL. I Div. 2
GP. A, B, C, D
HAZ. LOC.



TEMP. Rating T4