



Product Discontinued

PIPE SIZE	PIPE ID (mm) MAX-MIN	ANTENNA DIM (mm) DIA	ANTENNA DIM (mm) HEIGHT
5" SCH 10-60	Ø134,5-Ø125,3	120.2	56
6" SCH 10-60	Ø161,5-Ø150,3	145.2	59
8" SCH 20-80	Ø206,3-193,7	189	64.7
10" SCH 10-60	Ø264,7-247,7	243	72.5
12" SCH 10-40-XS	Ø314,7-298,5	293.5	79

08	GROUND CONNECTION (TO BE USED ACCORDING TO NATIONAL CODE OF PRACTISE)	RTR	
07	INTEGRATED JUNCTION BOX	RTR (OPTION JB1)	
06	Exp, Exi OR EXPLOSION PROOF JUNCTION BOX DEPENDING ON NATIONAL CODE OF PRACTISE	CUSTOMER (RTR OPTION)	
05	CABLE PROTECTION HOSE OR EXPLOSION PROOF CONDUIT DEPENDING ON NATIONAL CODE OF PRACTISE	CUSTOMER (RTR OPTION HOSE KIT)	
04	GASKET, SOFT TYPE	CUSTOMER	
03	BOLTING ACC. TO FLANGE STD IN POS 01	CUSTOMER	
02	STANDARD PIPE FLANGE ACC. TO POS 01	CUSTOMER	
01	FLANGE WITH CENTRE HOLE ACC. TO FIG.B. DIMENSIONS ACC. TO ANSI B16.5 5"-12" 150# OR EN1092-1: DN150 PN16, DN200 PN10, DN250 PN16.	RTR/CUSTOMER	
POS	ITEM DESCRIPTION	SUPPLIER	
ISSUED BY	WEEK	PRODUCT CODE	TITLE
GU-TKA	0403	REX	ACAD
APPROVED BY	WEEK	ORIGINAL DWG NO.	SCALE
GU-JW	0403	9150 070-941	RTG 3950 FIXED
1 ST ANGLE	DOC TYPE	DWG NO.	ISSUE
2	2	9150 070-941	2
MECHANICAL INSTALLATION DWG			SHEET
ROSEMOUNT TankRadarr Rex			1/1
Tank Gauging			

FOR MORE INFO. SEE
Rosemount TankRadarr Rex
INSTALLATION MANUAL

THE ROSEMOUNT TANKRADARR IS A TRADE MARK OF ROSEMOUNT TANK RADARR AB, SWEDEN.
ROSEMOUNT TANK RADARR AB, SWEDEN.
ROSEMOUNT TANK RADARR AB, SWEDEN.