



CABEL MARKING

MST/SPOT NO	WLS
1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Violet
8	Grey
9	White
10	Pink
Common return	Black

WLS	
+	Brown
-	White
Gnd	Shield

OPTIONS	
MST/SPOT NO	
11	Brown Black
12	Red Black
13	Orange Black
14	Yellow Black

- ① T1 300mm FROM EYE BOLT IN LEVEL SENSOR
- ② POSSIBILITY EXIST TO SPECIFY WEIGHT FOR MOUNTING ON TOPSIDE OF WLS. WEIGHT DIA: 80mm/WEIGHT: 5KG. RECOMMENDED ANCHOR WEIGHT 3-15KG DEPEND ON INSTALLATION TYPE
- ③ ACTIVE PROBE LENGTH (500, 1000, OPTIONAL 1500)
- ④ DISTANCE TO BUTTOM CAN BE REDUCED TO 16mm BY REMOVING THE EYEBOLT
- ⑤ CALIBRATION DISTANCE TO BE USED FOR ZERO ADJUSTMENT DISTANCE IS FOUND ABOVE THE LINE IN THE TOP OF THE SENSOR

ISSUED BY	WEEK	PRODUCT CODE	FILE	INSTALLATION DRAWING TITLE
GSP-AJ	0306	REX	ACAD	WATER LEVEL SENSOR OPEN
APPROVED BY	WEEK	ORIGINAL DWG NO.	SCALE	
GSP	0306	9261 090-150	X	
ROSEMOUNT		1 ST ANGLE	DOC TYPE	DWG NO.
Tank Gauging			2	9261 065-040
				ISSUE SHEET
				3 1/1

THE ROSEMOUNT LOGO/SYMBOL OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE ROSEMOUNT NAME MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR SUBJECT TO THE KNOWLEDGE OF A THIRD PARTY. COMMUNICATION WILL BE PROSECUTED. ROSEMOUNT TANK GAUGING AB, SWEDEN.