

**Mounting Kits for Namur Actuators (DXP/DXS, T Series)**

For ISO/Namur Quarter-Turn Actuators

**Cast Brackets (DXP/DXS, T Series\*)****Aluminum**

4N20080-G41A  
4N30080-G41A  
4N30130-G41A  
4N50130-G41A

**Stainless Steel**

4N20080-G41SC

**Stainless Steel Brackets (DXP/DXS, \*T Series)**

4N20080-G41S  
4N30080-G41S  
4N50130-G41S

**Stainless Steel Brackets (GO Switches)**

4N20080-G\_\_S  
4N30080-G\_\_S  
4N30130-G\_\_S  
4N50130-G\_\_S



\*T-Series mount directly to ISO/Namur 20 x 80 actuators.

See the following pages to view our 1,500+ custom mounting kits to fit Valvetop and GO Switch products to virtually any valve or actuator - rotary, linear, Namur and non-Namur.

Manufacturer	Applicable Switches	Part Number
<b>ACTREG ACTUATORS (NAMUR)</b> A20, 40, 80, 130, 200, 300, 500, 850, 1200, & 1750	T Series, DXP, 20, 70	4N30080-G__S
<b>AIR TORQUE ACTUATORS 'AT' SERIES (NAMUR)</b> 05, 10, 20, 25, & 30 35 & 40 50, 60, & 70	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4N20080-G__S 4N30130-G__S 4N50130-D__S
<b>AUTOMAX RACK &amp; PINION ROTARY ACTUATORS                      SUPERNOVA SERIES</b> N50 & S50 N63 & S63 N85 & S85 N100 & S100 N115 & N125, S115, S125 N150, N175, S150 & S175 N200 & S200 N250 & N300	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-A21110-S2_ 4-A21120-S2_ 4-A21130-S2_ 4-A21140-S2_ 4-A21150-S2_ 4-A21170-S2_ 4-A21280-S2_ 4-A21285-S2_
<b>AUTOMAX RACK &amp; PINION ROTARY ACTUATORS (NAMUR)</b> SNA050, 063, 085, & 100 SNA115, 125 150, 175 & 200 S115, S125 S200	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4N20080-G__S 4N30130-G__S 4N30130-D__S 4N50130-D__S
<b>AUTOMAX HEAVY DUTY ROTARY ACTUATORS</b> R205, 206, 207, 208, R310, 312, 314 & 316 R414, 416, 418, 420 & 422	T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-A21310-S2_ 4-A21420-S24
<b>BAUMANN LITTLE SCOTTIE ACTUATORS</b> 32 or 54 sq. in. actuator w/ 5/16" valve stem	70	#4-A21514-S24N 4-B02322-S27
<b>BETTIS CB SERIES ACTUATORS</b> CB-315 & 415 CB-420 & 520 CB-525 & 725	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-B05015-S2_ 4-B05020-S2_ 4-B05030-S2_
<b>BETTIS GT SERIES</b> GT-110 & 225 GT-450 & 900 GT-1350 & 2700	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-B05110-S2_ 4-B05120-S2_ 4-B05130-S2_
<b>BETTIS RP SERIES (OLD STYLE)</b> RP-250 & 450 RP-1000 RP-2250, 5000, 11000	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-B05210-S2_ 4-B05220-S2_ 4-B05230-S2_
<b>BETTIS RPB &amp; RPBQ SERIES</b> RPB-250, 450, 1000, 2250, 5000 & 11000	T Series, DXP, 20, 70	4-B05250-S2_
<b>BETTIS RPC SERIES (NAMUR)</b> RPC-250/251, 450/451, 1000/1001 2250/2251, 5000/5001, 11000/11001	T Series, DXP, 20, 70	4N20080-G__S
<b>BETTIS G SERIES (NAMUR)</b> 1, 2, 3, 4, 5, 7, 8, 10, 13	T Series, DXP, 20, 70	4N20080-G__S
<b>BETTIS HD SERIES ROTARY ACTUATORS</b> HD-521, 522 & 721 & 722 HD-731C & 732C	T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-B05510-S2_ 4-B05520-S2_
<b>BETTIS T SERIES ROTARY ACTUATORS</b> T-3 & 4 T-5 & 8	T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-B05310-S2_ 4-B05320-S2_
<b>BETTIS TR &amp; TRQ SERIES ROTARY ACTUATORS</b> TR-1012, 1016, 1020, 10212, 10216, 10220 TRQ-10410, 10412, 10416, 10420	T Series, DXP, 20, 70	4-B05410-S2_
<b>BIFFI (SEE KEYSTONE)</b> <b>BRAY VALVES &amp; CONTROLS</b> <b>SERIES 90/91</b>		
90/91 Size 60 & 80 90/91 Size 63 90/91 Size 83 90/91 Size 118 & 127	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-B18060-S2_ 4-B18063-S2_ 4-B18083-S2_ 4-B18118-S2_

Manufacturer	Applicable Switches	Part Number
90/91 Size 160, 210, 255A & 255B 90/91 Size 200	T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-B18160-S2_ 4-B18200-S2_
<b>BROOKS BRODIE</b>		#4-B08010-S2P
7031 Control Valve	70	4-B19703-S27
760 Relief Valve	70	4-B19760-S17
<b>CONBRACO ACTUATORS (NAMUR)</b>		
CT-20-60,30-60,40-60,50-60,60-60	T Series, DXP, 20, 70	4N20080-G__S
CT-70-60,80-60	T Series, DXP, 20, 70	4N30130-G__S
CT90-60	T Series, DXP, 20, 70	4N50130-G__S
<b>DeZURIK KNIFE GATE VALVES</b>		
<b>SERIES C &amp; L WITH CYLINDER ACTUATORS</b>		
NOTE: When ordering state type of cylinder support yoke (channel, angle or "W").		
<b>DeZURIK KNIFE GATE VALVES (C &amp; L SERIES)</b>		
<b>WITH CHANNEL TYPE YOKES</b>		
C & L 4" & 6" CGC w/ channel	70	4-D06050-S27
C & L 8" CGC w/ channel	70	4-D06060-S27
C & L 10" CGC w/ channel	70	4-D06065-S27
C & L 12" CGC w/ channel	70	4-D06066-S27
C & L 14" CGC w/ channel	70	4-D06067-S27
<b>DeZURIK KNIFE GATE VALVES (C &amp; L SERIES)</b>		
<b>WITH ANGLE TYPE YOKES</b>		
C & L 4" CGC w/ angle	20, 70	4-D06070-S2_
C & L 6" CGC w/ angle	20, 70	4-D06075-S2_
C & L 8" CGC w/ angle	20, 70	4-D06080-S2_
C & L 10" & 12" CGC w/ angle	20, 70	4-D06085-S2_
<b>DeZURIK KNIFE GATE VALVES (C &amp; L SERIES)</b>		
<b>WITH "W" TYPE YOKES</b>		
C & L 12" through 18" CGC w/ "W"	20, 70	4-D06100-S2_
C & L 20" CGC w/ "W"	20, 70	4-D06120-S2_
<b>EL-O-MATIC RACK &amp; PINION ACTUATORS</b>		
DA/SR 1.5, 3.5 & ED/ES 2.5	T Series, DXP, 20, 70	4-E15010-S2_
DA/SR 6 & ED/ES 4.0	T Series, DXP, 20, 70	4-E15015-S2_
DA/SR 15 & ED/ES 10	T Series, DXP, 20, 70	4-E15020-S2_
DA/SR 28 & ED/ES 20	T Series, DXP, 20, 70	4-E15025-S2_
DA/SR 50 & 75	T Series, DXP, 20, 70	4-E15030-S2_
DA/SR 110	T Series, DXP, 20, 70	4-E15035-S2_
DA/SR 250	T Series, DXP, 20, 70	4-E15040-S2_
<b>EL-O-MATIC RACK &amp; PINION ACTUATORS</b>		
<b>E &amp; P SERIES (NAMUR)</b>		
E 12	T Series, DXP, 20, 70	4-E15050-S2_
E 25,E40,E65,E100,E200,E350	T Series, DXP, 20, 70	4N20080-G__S
P35,P60,P150,P280	T Series, DXP, 20, 70	4N20080-G__S
P500,P750,P1100,P2500,P4000	T Series, DXP, 20, 70	4N30130-G__S
<b>ENCON SHOWER AND EYEWASH</b>		
Model 01-0502-16	80	4-E14010-S28
<b>FISHER DIAPHRAGM ACTUATORS</b>		
Types 57T & 555T	20, 70	4-F09010-S2_
<b>FISHER 470 ACTUATORS</b>		
470-40	20, 70	4-F09030-S2_
470, 471-46 & 60	20, 70	4-F09035-S2_
470, 471-80	20, 70	4-F09040-S2_
470, 471-80 w/ Target Magnet	Backpak	4-F09040-L45
470, 471, 46-80	70	4-F09041-S27
470, 471-100	20, 70	4-F09045-S2_
470, 471-130	20, 70	4-F09050-S2_
472-100 (same as 657-70)	20, 70	4-F09225-S2U
478-23 & 40 w/ 4-1/8" stroke	20, 70	4-F09055-S2_
478-68	20	4-F09057-S22
<b>FISHER 480/481 PISTON ACTUATORS</b>		
480, 481-12 Size.20	20	4-F09060-S22
480, 481-15 Size 40 & 60	20, 70	4-F09070-S2_
480, 481-16 Size 40 & 60	20, 70	4-F09080-S2_
486U -16, Size 40 & 60	70	4-F09090-S27

Manufacturer	Applicable Switches	Part Number
<b>FISHER DIAPHRAGM ACTUATORS</b> 512, 512R, 513 & 513R Sizes 20 & 32	70	4-F09100-S27
<b>FISHER 585 PISTON ACTUATORS</b> 585 Sizes 25 & 50 585 Size 100 585C Size 25 585C Size 50	70 70 20 70 70	4-F09120-S27 4-F09130-S22 4-F09140-S27 4-F09145-S27
<b>FISHER 657 ACTUATORS</b> 657/667 Sizes 30, 34, 40, 45, 46, 56, 60, 70, (Stroke 1-4") 657 Size 30 657 Sizes 30-60 657 Size 34 657 Size 40 657 Sizes 45 & 46 657 Sizes 50 & 60 657 Sizes 70 & 87 657 Sizes 70, 80 & 87 657 Size 80	DXP, T Series 20, 70 Backpak 20, 70 20, 70 20, 70 20, 70 20, 70 20, 70 Backpak 20, 70	4-F09203-S2_ 4-F09200-S2_ 4-F09202-L45 4-F09205-S2_ 4-F09210-S2U 4-F09215-S2U 4-F09220-S2U 4-F09225-S2U 4-F09227-L45 4-F09226-S2U
<b>FISHER 667 ACTUATORS</b> 657/667 Sizes 30, 34, 40, 45, 46, 56, 60, 70, 76 (Stroke 1-4") 667 Sizes 30 - 60 667 Size 30 667 Size 34 667 Size 40 667 Sizes 45 & 46 667 Sizes 50 & 60 667 Sizes 50 & 60 667 Size 70 & 76 667 Sizes 80 & 87	DXP, T Series Backpak 20, 70 20, 70 20, 70 20, 70 20, 70 20, 70 Backpak 20, 70 20, 70	4-F09203-S24 4-F09202-L45 4-F09300-S2U 4-F09305-S2U 4-F09310-S2U 4-F09315-S2U 4-F09320-S2U 4-F09222-L45 4-F09323-S2U 4-F09325-S2U
<b>FISHER 1008 ACTUATORS</b> 1008 Size 30, 40, 50	70	4-F09350-S27
<b>FISHER 1031 ACTUATORS</b> 1031 - 26 1031- 33 1031 - 45 1031 - 60 1031 - 80	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-X15110-S2_ 4-X15120-S2_ 4-X15130-S2_ 4-X15133-S2_ 4-X15136-S2_
<b>FISHER 1032 ROTARY ACTUATORS (NAMUR)</b> 1032-45,70,130,185,280,425,680 1032-1125,1370,2585,4580	T Series, DXP, 20, 70 T Series, DXP, 20, 70	4N20080-G__ S 4N30130-G__ S
<b>FISHER 1035 ROTARY ACTUATORS (NAMUR)</b> 1035-E25, E40,E65, E100, E200, & E350 1035-P500, P750, P1100 P2500, & P4000	T Series, DXP, 20, 70 T Series, DXP, 20, 70	4N20080-G__ _ 4N30130-G__ _
<b>FISHER 1051, 1052 &amp; 1061 ROTARY ACTUATORS</b> 1051 & 1052 Size 20 1051 & 1052 Size 33 1051, 1052 & 1061 Sizes 30, 40, 60, 68 & 70 1061 Sizes 80 & 100	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-F09400-S2_ 4-F09420-S2_ 4-F09450-S2_ 4-F09460-S2_
<b>FISHER 1063 AND 1064 ROTARY ACTUATORS</b> 1063/1064 Size 20 1063/1064 Size 75	T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-F09470-S2_ 4-F09475-S2_
<b>FISHER 1066 ROTARY ACTUATORS</b> 1066 Sizes 20 & 27 w/ 1/2" & 5/8" valve shafts 1066 Sizes 20 & 27 w/ 3/4", 7/8" & 1" valve shafts 1066 Size 75 1066 Sizes 20, 27 & 75 Style H Drive w/7/8" dia. shaft w/1-1/8" dia. shaft w/1-1/2" dia. shaft	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-F09480-S2_ 4-F09482-S2_ 4-F09485-S2_ 4-F09490-S2_ 4-F09492-S2_ 4-F09495-S2_

Manufacturer	Applicable Switches	Part Number
<b>FISHER 1075 MANUAL HANDWHEEL ROTARY ACTUATORS</b>		
1075-1	20, 70	4-F09500-S2_
1075-2	20, 70	4-F09510-S2_
<b>FISHER 1077 MANUAL HANDWHEEL ROTARY ACTUATORS</b>		
1077-0M	20, 70	4-F09550-S2_
1077-1M	20, 70	4-F09553-S2_
1077-2M	20, 70	4-F09555-S2_
1077-5M	20, 70	4-F09560-S2_
1077-6M	20, 70	4-F09565-S2_
1077-7M	20, 70	4-F09575-S2_
1077-9M	20, 70	4-F09580-S2_
<b>FISHER 1078 AAA MANUAL ACTUATORS</b>		
1078-AAA	T Series, DXP, 20, 70	4-F09590-S2_
1078-AA	T Series, DXP, 70	4-F09592-S2_
1078-A	T Series, DXP, 20, 70	4-F09595-S2_
1078-B	T Series, DXP, 70	4-F09597-S2_
<b>FISHER 3710 POSITIONER</b>	T Series, DXP, 70	4-F09710-S2_
<b>GENERAL TORQUE (SEE KTM)</b>		
<b>GENERAL VALVE - TWIN SEAL VALVES</b>		
Models C811G & C821G & CA811G		
C811G w/ 501-TC operator	70	4-G05010-S27
C821G w/ 21-518 operator	70	4-G05020-S27
CA811G w/ 625-TS operator	70	4-G05090-S27
T Series, DXP, 20, 70	4-G17250-S2_	
<b>GRINNEL ROTARY ACTUATORS (NAMUR)</b>		
Size 2, 4, 8, 12, 20, 35	T Series, DXP, 20, 70	4N20080-G_ _ _
Size 55, 70, 100, 150	T Series, DXP, 20, 70	4N30130-G_ _ _
<b>HAWS EYEWASH &amp; SHOWERS</b>		
8133 Eyewash	80	4-H02133-S18
7651 Eyewash	80	4-H02651-S18
7260B Eyewash	80	4-H02160-S18
8300/8309 Eyewash & Shower	80	4-H02300-S28
8317 Eyewash & Shower	80	4-H02317-S28
8330 Eyewash & Shower	80	4-H02330-S18
8605 Eyewash & Shower	80	4-H02605-S28
<b>HONEYWELL 800 SERIES DIAPHRAGM ACTUATORS</b>		
800 - Sizes 9 & 11	20, 70	4-H15809-S2_
800 - Size 18L	20, 70	4-H15819-S2_
<b>HYTORK ACTUATORS (NAMUR)</b>		
XL-45,70,130,185,280,425,680	T Series, DXP, 20, 70	4N20080-G_ _ _
XL-1125,1370,2585,4580	T Series, DXP, 20, 70	4N30130-G_ _ _
<b>ITT ENGINEERED VALVES DIA-FLOW</b>		
<b>AIR MOTORS (Must have indicator kit from ITT)</b>		
Size 12	70	4-I20020-S27
Sizes 25, 50 & 75	70	4-I20025-S27
<b>JAMESBURY MANUAL GEAR OPERATORS</b>		
MA 010	20, 70	4-N05110-S2_
MA 020	20, 70	4-N05120-S2_
MA 030	20, 70	4-N05130-S2_
MA 040	20, 70	4-N05140-S2_
MA 045	20, 70	4-N05145-S2_
<b>JAMESBURY RACK &amp; PINION ACTUATORS</b>		
SP25, 50, SP6SR60, SP9SR80, SP8SR40, SP13SR60, SP18SR80	T Series, DXP, 20, 70	4-N05310-S2_
SP100, 200, SP18SR40, SP26SR60, SP36SR80, SR52SR60, SP72SR80	T Series, DXP, 20, 70	4-N05320-S2_
<b>JAMESBURY ROTARY ACTUATORS</b>		
ST20, 50, 13MS & 20MS	T Series, DXP, 20, 70	4-N05210-S2_
ST200, 400, 60MS, 90MS, 115MS & 175MS	T Series, DXP, 20, 70	4-N05215-S2_
ST600, 1200, 1800, 2400, 160MS, 240MS, 290MS & 440MS MODEL G & H	T Series, DXP, 20, 70	4-N05330-S2_

Manufacturer	Applicable Switches	Part Number
<b>JAMESBURY QUADRA-POWR &amp; QUADRA-POWR II ACTUATORS</b>		
B (Size 30, 40, 50, 60S) QP 1M & 2M	T Series, DXP, 20, 70	4-N05310-S2_
C (Size 30, 40, 50, 60S) QP 3M	T Series, DXP, 20, 70	4-N05320-S2_
D, E & F (Size 30, 40, 50, 60S) QP 4M & 5M	T Series, DXP, 20, 70	4-N05330-S2_
<b>JAMESBURY VANE ACTUATORS</b>		
V60	T Series, DXP, 20, 70	4-N05310-S2_
V150	T Series, DXP, 20, 70	4-N05320-S2_
V400	T Series, DXP, 20, 70	4-N05330-S2_
<b>JAMESBURY PNEUMATIC ACTUATORS</b>		
RP-550, 800, 1000, 1200, 1600, 2500, 3500, 4500 & 5000	20, 70	4-N05400-S2_
<b>JAMESBURY ACTUATORS (NAMUR)</b>		
VP-02, 04	T Series, DXP, 20, 70	4N20080-G41S
VP-08, 10	T Series, DXP, 20, 70	4N30080-G41S
VP-12, 14, 22	T Series, DXP, 20, 70	4N50130-G41S
<b>KEYSTONE PNEUMATIC ACTUATORS</b>		
FIG. 790 Sizes 100, 200, 300	T Series, DXP, 20, 70	4-K05790-S2_
FIG. 790 Sizes 400 & 500	T Series, DXP, 20, 70	4-K05791-S2_
FIG. 790 Sizes 600 & 700	T Series, DXP, 20, 70	4-K05796-S2_
<b>KIELEY &amp; MUELLER DIAPHRAGM ACTUATORS</b>		
36RN	70	4-K09010-S27
37 & 38 DN & RN	20, 70	4-K09020-S2_
45D-15	20, 70	4-K09030-S2_
45D-18	20, 70	4-K09031-S2_
<b>KINETROL VANE ACTUATORS</b>		
029 w/ SAE hardware	T Series, DXP, 20, 70	4-K10029-S2_
039 w/ SAE hardware	T Series, DXP, 20, 70	4-K10039-S2_
059 w/ SAE hardware	T Series, DXP, 20, 70	4-K10059-S2_
079 w/ SAE hardware	T Series, DXP, 20, 70	4-K10079-S2_
089 w/ SAE hardware	T Series, DXP, 20, 70	4-K10089-S2_
099 w/ SAE hardware	T Series, DXP, 20, 70	4-K10099-S2_
109 w/ SAE hardware	T Series, DXP, 20, 70	4-K10109-S2_
129 w/ SAE hardware	T Series, DXP, 20, 70	4-K10129-S2_
149 w/ SAE hardware	T Series, DXP, 20, 70	4-K10149-S2_
**169 w/ SAE hardware	T Series, DXP, 20, 70	4-K10169-S2_
**189 w/ SAE hardware	T Series, DXP, 20, 70	4-K10189-S2_
**209-100 w/ SAE hardware	T Series, DXP, 20, 70	4-K10209-S2_
**Mounting hardware is supplied in carbon steel only.		
<b>KTM-GENERAL TORQUE RACK &amp; PINION ACTUATORS</b>		
AG09	T Series, DXP, 20, 70	4-K20009-S2_
AG14	T Series, DXP, 20, 70	4-K20014-S2_
AG15	T Series, DXP, 20, 70	4-K20015-S2_
AW17	T Series, DXP, 20, 70	4-K20017-S2_
AW20	T Series, DXP, 20, 70	4-K20020-S2_
<b>MAGNETROL LIQUID LEVEL CONTROLS</b>		
W/ 5-3/8" ENCLOSING TUBE w/ two 70 Series switches	73-13522-533	4-M00800-S27
<b>MASONEILAN-DRESSER CAMFLEX II ACTUATORS</b>		
Actuator size 4-1/2 for valve sizes 1, 1-1/2, 2	70	4-M02100-S27
Actuator size 6 for valve sizes 3" & 4"	70	4-M02120-S27
Actuator sizes 7 & 10 for valve sizes 6", 8", 10" & 12"	75	4-M02130-S27
<b>MASONEILAN 2600 SERIES YOKE MOUNTED ACTUATORS</b>		
Annin A Domotor 25 sq. inch, cylinder operator A & B, Spring diaphragm 70 sq. inch; 3/4" stroke	70	4-M02010-S27
Annin B Domotor 50 sq. inch, cylinder operator C, Spring diaphragm 70 sq. inch; 1-1/2" stroke	20, 70	4-M02015-S2_
Annin Domotor 100 sq. inch, cylinder operator C, Spring diaphragm 140 sq. inch; 2-1/2" stroke	20, 70	4-M02020-S2_
<b>MASONEILAN-DRESSER SIGMA F ACTUATORS</b>		
Sizes A & B	20, 70	4-M02300-S2_
Size C	20, 70	4-M02310-S2_

Manufacturer	Applicable Switches	Part Number
<b>MASONEILAN-DRESSER DIAPHRAGM ACTUATORS</b>		
<b>MODELS 37 &amp; 38</b>		
37/38 Size 9	20, 70	4-M02205-S2_
37/38 Sizes 11 & 13	20, 70	4-M02210-S2_
37/38 Sizes 15 & 18	20, 70	4-M02220-S2_
<b>MARWIN CONTROLS (NAMUR)</b>		
52/UT-0, 63/UT-1, 85/UT-2.5	T Series, DXP, 20, 70	4N30080-G_ _ _
<b>MASTERGEAR GEAR OPERATORS</b>		
MZF	20, 70	4-M03005-S2_
MVF & MVWD	20, 70	4-M03010-S2_
MBF	20, 70	4-M03020-S2_
MLF	20, 70	4-M03025-S2_
MMF, MNF & MPF	20, 70	4-M03030-S2_
<b>MATRYX PNEUMATIC ACTUATORS (MTP SERIES)</b>		
55	T Series, DXP, 20, 70	4-X15005-S2_
65	T Series, DXP, 20, 70	4-X15015-S2_
90	T Series, DXP, 20, 70	4-X15020-S2_
115	T Series, DXP, 20, 70	4-X15025-S2_
135	T Series, DXP, 20, 70	4-X15030-S2_
175	T Series, DXP, 20, 70	4-X15035-S2_
XL-45	T Series, DXP, 20, 70	4-X15045-S2_
XL-70, 185 & 280	T Series, DXP, 20, 70	4-X15050-S2_
XL-425 & 680	T Series, DXP, 20, 70	4-X15055-S2_
XL-1125 & 1370	T Series, DXP, 20, 70	4-X15060-S2_
XL-2585 & 4580 w/ stop block	T Series, DXP, 20, 70	4-X15066-S2_
<b>MORIN ACTUATORS</b>		
M060A, M12DA & SR	T Series, DXP, 20, 70	4-M14006-S2_
M23DA, M36DA, M46DA & SR, M72DA & SR	T Series, DXP, 20, 70	4-M14023-S2_
<b>NELES CONTROLS CYLINDER ACTUATORS</b>		
<b>MODELS BC &amp; BJ</b>		
Sizes 8, 9 & 10	T Series, DXP, 20, 70	4-N05410-S2_
Sizes 12 & 16	T Series, DXP, 20, 70	4-N05415-S2_
Size 20	T Series, DXP, 20, 70	4-N05420-S2_
Size 25	T Series, DXP, 20, 70	4-N05425-S2_
Size 32	T Series, DXP, 20, 70	4-N05430-S2_
Size 40	T Series, DXP, 20, 70	4-N05435-S2_
<b>ORBIT PISTON ACTUATORS</b>		
<b>LG &amp; LS SERIES</b>		
124D	20, 70	4-O18005-S2_
185D4, 14, 20, 23	20, 70	4-O18010-S2_
185D5	20, 70	4-O18015-S2_
205D5 & 6	20, 70	4-O18020-S2_
206	20, 70	4-O18025-S2_
266	20, 70	4-O18030-S2_
<b>ORBIT DIAPHRAGM ACTUATORS</b>		
80100, 80625, 160100, 160625 & 1601125	20, 70	4-O18040-S2_
Series 84, 164 & 165, 84100, 10084, 164100, 100164, 100165 & 100167	20, 70	4-O18050-S2_
84625, 164625, 62584, 625164 & 625165	20, 70	4-O18060-S2_
<b>PROTECH ACTUATORS (NAMUR)</b>		
72/73 Series		
100, 200, 250, 260 & 300	T Series, DXP, 20, 70	4N20080-G_ _ S
400 & 500	T Series, DXP, 20, 70	4N30130-G_ _ S
<b>ROTORK P &amp; H RANGE PNEUMATIC ACTUATORS</b>		
250 Series DA/SR (side mounting)	T Series, DXP, 20, 70	4-R16250-S2_
325 Series DA/SR (top mounting)	T Series, DXP, 20, 70	4-R16325-S2_
500 Series DA/SR	T Series, DXP, 20, 70	4-R16500-S2_
700 Series DA/SR	T Series, DXP, 20, 70	4-R16700-S2_
<b>TRIAC ACTUATORS (NAMUR)</b>		
TR-20, 40, 80, 130, 200	T Series, DXP, 20, 70	4N20080-G_ _ S
TR-500, 850, 1200, 1750	T Series, DXP, 20, 70	4N30130-G_ _ S



Manufacturer	Applicable Switches	Part Number
<b>UNITORQ ACTUATORS (NAMUR)</b> M10, 20, 30, 52, 73, 103, 148, 222, & 295 M586, 1213, 2366, 2958, & 4200	T Series, DXP, 20, 70 T Series, DXP, 20, 70	4N20080-G__S 4N30130-G__S
<b>VALTEK - MARK ONE ACTUATORS</b> 25 sq. inch w/ 2" spud 50 sq. inch w/ 2" & 2.62" spud 100 & 200 sq. inch w/ 3-3/8" and 4-3/4" spud size 100 & 200 sq. inch w/ 2-5/8" and 2-7/8" spud size	70 20, 70 20, 70 70	4-V01025-S27 4-V01050-S2_ 4-V01100-S2_ 4-V01150-S27
<b>VALTEK - VALDISK ACTUATORS</b> 25 & 50 sq. inch, 4.25 bolt circle 50 & 100 sq. inch, 6.25 bolt circle	20, 70 20, 70	4-V01026-S2_ 4-V01051-S2_
<b>WATTS PNEUMATIC ACTUATORS</b> DA/SR 48 DA/SR 68 & 109	20, 70 20, 70	4-W01080-S2_ 4-W01090-S2_
<b>WHITEY PNEUMATIC ACTUATORS</b> 90 MS-131 90 MS-133 90 MS-135 180 MS-153	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-W08131-S2_ 4-W08133-S2_ 4-W08135-S2_ 4-W08153-S2_
<b>WORCESTER CONTROLS PNEUMATIC ACTUATORS</b> Series 34 - Sizes A & B	T Series, DXP, 20, 70	4-W15340-S2_
<b>WORCESTER CONTROLS PNEUMATIC 37 SERIES ACTUATORS</b> 0537 & 1537 w/ female drive 0537 & 1537w/ male drive	70 70	4-W15370-S27 4-W15375-S27
<b>WORCESTER CONTROLS PNEUMATIC ACTUATORS</b> B38 C38 & C77 D38 & D77 E38 D5-38	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-W15380-S2_ 4-W15381-S2_ 4-W15382-S2_ 4-W15384-S2_ 4-W15385-S2_
<b>WORCESTER CONTROLS 39 SERIES ACTUATORS</b> 1039 1539 2039 2539 3039 3339 3539 4039 4539 5036 & 5040N	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-W15005-S2_ 4-W15010-S2_ 4-W15015-S2_ 4-W15020-S2_ 4-W15025-S2_ 4-W15033-S2_ 4-W15030-S2_ 4-W15035-S2_ 4-W15040-S2_ 4-W15045-S2_
<b>WORCESTER CONTROLS 39/R6 SERIES (NAMUR)</b> 1039/R6, 1539/R6, & 2039/R6 2539/R6, 3039/R6, 3339/R6 & 3539/R6 4039/R6 & 4239/R6	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4N20080-G__S 4N30080-G__S 4N50130-G__S
<b>XOMOX MATRYX PISTON ACTUATORS</b> 26051, 26061, 26062, 26071, 26081, 26002 33071, 33081, 33082, 33101, 33102, 33121 45102, 45121, 45122, 45141, 45161	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-X15110-S2_ 4-X15120-S2_ 4-X15130-S2_
<b>XOMOX MATRYX XACT VANE ACTUATORS</b> 60 & MX60 200 & MX 200 450, 750, 1250, MX 450, MX750, MX1250 3000 & MX3000	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-X15140-S2_ 4-X15150-S2_ 4-X15160-S2_ 4-X15190-S2_
<b>XOMOX TUFLINE VANE ACTUATORS</b> 7006 7020 7125	T Series, DXP, 20, 70 T Series, DXP, 20, 70 T Series, DXP, 20, 70	4-X15170-S2_ 4-X15175-S2_ 4-X15185-S2_