

Operating Requirements

Emerson Process Management recommends the following resources for AMS Suite: Machinery Health™ Manager 5.51:

Workstations

Minimum Requirements

Operating Systems	<ul style="list-style-type: none">Windows XP Professional SP2 & SP3, Windows 7 Professional, Windows 7 Ultimate, and Windows 7 Enterprise.
Processor/Memory	<ul style="list-style-type: none">1.5 GHz, 2 GB of RAM (XP), Windows 7, and 2 GB of RAM
Network	<ul style="list-style-type: none">Ethernet (TCP/IP protocol)
Browser	<ul style="list-style-type: none">Internet Explorer 6 or later
Screen Resolution	<ul style="list-style-type: none">XGA (1024 x 768)
Other	<ul style="list-style-type: none">RS232 serial communications port (9-pin)*, USB 1.1 port‡

Recommended Requirements

Operating System	<ul style="list-style-type: none">Windows XP Professional SP2 & SP3, Windows 7 Professional, Windows 7 Ultimate, and Windows 7 Enterprise.
Processor/Memory	<ul style="list-style-type: none">2.0 GHz Dual Core, 2 GB of RAM
Network	<ul style="list-style-type: none">Ethernet (TCP/IP protocol)
Browser	<ul style="list-style-type: none">Internet Explorer 7 or later
Screen Resolution	<ul style="list-style-type: none">SXGA (1280 x 1024) or better
Other	<ul style="list-style-type: none">RS232 serial communications port (9-pin)*, USB 2.0 port

Recommended Requirements for Online Live Transient Client

Operating System	<ul style="list-style-type: none">Windows XP Professional SP2 & SP3, Windows 7 Professional, Windows 7 Ultimate, and Windows 7 Enterprise.
Processor/Memory	<ul style="list-style-type: none">2.33 GHz Dual Core, 2 GB of RAM
Video Card	<ul style="list-style-type: none">DirectX 9.0b compatible
Network	<ul style="list-style-type: none">Ethernet (TCP/IP protocol)
Browser	<ul style="list-style-type: none">Internet Explorer 7 or later
Screen Resolution	<ul style="list-style-type: none">SXGA (1280 x 1024) or better
Other	<ul style="list-style-type: none">RS232 serial communications port (9-pin)*, USB 2.0 port

Additional Recommendations

Virtualization System	<ul style="list-style-type: none">Microsoft System Center Virtual Machine Manager 2008 R2
Antivirus	<ul style="list-style-type: none">Symantec™ Endpoint Protection v11.0.6200.754

* For communications with analyzers prior to the CSI 2130, a PC must have an RS232 serial port. A USB port is highly recommended for communications with the CSI 2130 Machinery Health Analyzer.

For communication with CSI 5200 Machinery Health Oil Analyzer, a PC must have an RS232 serial port

‡ For communication with the WDA Image Capture Kit, a USB 2.0 port is required.

NOTE: AMS Machinery Manager operates on 32-bit and 64-bit operating systems.

Servers

Minimum Requirements

Operating Systems

- LAN:**
 - Windows Server 2003 R2 with SP2, Windows Server 2008 SP2 Standard Edition, and Windows Server 2008 R2
- WAN:**
 - Windows Server 2003 R2 SP2 and Windows Server 2008 SP2 Standard Edition with Terminal Server, or Windows Server 2003 R2 SP2, Windows Server 2008 SP2 Standard Edition with Citrix XenApp 6†, and Windows Server 2008 R2 with Remote Desktop Services.

Processor/Memory

- Portable Systems:**
 - 1.83 GHz Dual Core, 2 GB of RAM
- Online Systems:**
 - Server-class 2.33 GHz Dual Core, 2 GB of RAM
 - Internet Explorer 7

Network

- Ethernet (TCP/IP protocol)

Screen Resolution

- XGA (1024 x 768)

Recommended Requirements

Operating Systems

- LAN:**
 - Windows Server 2003 R2 with SP2, Windows Server 2008 SP2 Standard Edition and Windows Server 2008 R2.
- WAN:**
 - Windows Server 2003 R2 SP2, Windows Server 2008 SP2 Standard Edition with Terminal Server and Windows Server 2008 R2 with Remote Desktop Services.

Processor/Memory

- Portable Systems:**
 - 2.33 GHz Dual Core, 2 GB of RAM
- Online Systems:**
 - Server-class 3.0 GHz Dual Core, 2 GB of RAM
 - Internet Explorer 7

Network

- Ethernet (TCP/IP protocol)

Screen Resolution

- SXGA (1280 x 1024) or better

Recommended requirements for CSI 6500 and CSI 2600 systems

Operating Systems

- Windows XP or Windows 7

Processor/Memory

- Pentium II or better, minimum clock frequency 500 MHz, memory must meet requirements of OS

Hard drive capacity

- 250 GB or greater

RS232 Interface

- One available interface

Network

- Ethernet (TCP/IP protocol)

Browser

- Internet Explorer 7 or later

Screen Resolution

- SXGA (1280 x 1024) or better

Additional Recommendations

Virtualization System

- Microsoft System Center Virtual Machine Manager 2008 R2

Antivirus

- Symantec™ Endpoint Protection v11.0.6200.754

† When running Citrix, Terminal Server is also required.

NOTE: AMS Machinery Manager operates on 32-bit and 64-bit operating systems, and requires a DVD for installation.

Emerson Process Management

©2012, Emerson Process Management.

Asset Optimization

835 Innovation Drive
Knoxville, TN 37932
T (865) 675-2400
F (865) 218-1401

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.

All rights reserved. AMS, and Machinery Health are marks of one of the Emerson Process Management group of companies. The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their respective owners.