

# Pressure/Temperature Ratings for Fisher™ Cast Iron Valve Bodies

The pressure/temperature ratings for flanged cast iron valves given in the following figure are in accordance with ASME B16.1. Fisher valves with Class B ratings are listed in table 1. Cast iron valves with screwed connections have CL250 ratings in accordance with ASME B16.4.


The American Society of Mechanical Engineers, United Engineering Center, Three Park Avenue, New York, New York 10016.

Information in the following figure has been extracted from Cast Iron Pipe Flanges and Flanged Fittings (ASME B16.1) with the permission of the publisher.

Table 1. Class B Ratings

Valve Body Design	Valve Size, NPS	CL125B	CL250B
E <sup>(1)</sup>	1, 1-1/2, 2, 2-1/2, 3, 4, 6, 8	X	X
YD, YS	1, 1-1/2, 2, 2-1/2, 3, 4, 6	X	X

1. Refers to all valve designs beginning with "E" that are available in cast iron, for example: ED, EDR, etc.



Pressure/Temperature Ratings

Neither Emerson, Emerson Automation Solutions, nor any of their affiliated entities assumes responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher is a mark owned by one of the companies in the Emerson Automation Solutions business unit of Emerson Electric Co. Emerson Automation Solutions, Emerson, and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Automation Solutions  
Marshalltown, Iowa 50158 USA  
Sorocaba, 18087 Brazil  
Cernay 68700 France  
Dubai, United Arab Emirates  
Singapore 128461 Singapore

[www.Fisher.com](http://www.Fisher.com)

