

Full-Size Performance. Compact Profile.

New FISHER® First Stage Residential Regulator – Type R222H

Perfect for underground tanks or limited dome spaces

Type R122H



c UL US LISTED

Type R622H



c UL US LISTED

Type R222H



c UL US LISTED

65% GREATER FLOW

40% SMALLER FOOTPRINT

UL® approved for LPG

- ✓ Highest flow compact on the market - up to 2.0 MBTU/hr
- ✓ Multiple end connections – FPOL, 1/2 in. and 3/4 in.
- ✓ Adjustable spring ranges at 5 and 10 psi set points
- ✓ Engineered for flow, setpoint accuracy and complete shutoff at -40°F / -40°C
- ✓ Greater stability at higher flow and inlet pressures
- ✓ High capacity internal relief that exceeds UL® standards
- ✓ Double failure overpressure protection
- ✓ Every unit manufactured and tested in an Emerson™ / Fisher facility

UL® is a mark owned by Underwriters Laboratories.

FISHER

www.fisherregulators.com
1-800-558-5853


EMERSON
Process Management

EMERSON. CONSIDER IT SOLVED.™

D40379101 © 2015 Emerson Process Management Regulator Technologies, Inc. All rights reserved. Fisher, Emerson Process Management, and the Emerson Process Management design are marks of the Emerson Process Management group of companies.