

Roxar Downhole

Country/Region	Registration Number
China	CN 103038444
China	CN 103097643
Denmark	EP 2078132
Denmark	EP 2150675
Denmark	EP 2158380
Denmark	EP 2102960
Denmark	EP 2601374
Eurasian Patent-EAPO	EA 014849
France	EP 2078132
France	EP 2150675
France	EP 2158380
France	EP 2102960
France	EP 2601374
Germany	EP 2078132
Germany	EP 2150675
Germany	EP 2158380
Germany	EP 2102960
Germany	EP 2601374
Netherlands	EP 2078132
Netherlands	EP 2150675
Netherlands	EP 2158380
Netherlands	EP 2102960
Netherlands	EP 2601374
Norway	NO 313647
Norway	NO 327349
Norway	NO 332873
Norway	NO 326643
Norway	NO 329210
Norway	NO 334696
Norway	NO 334036
Norway	NO 335999
Norway	EP 2150675
Norway	NO 336858
United Kingdom	GB 2382412
United Kingdom	GB 2393984
United Kingdom	GB 2385342
United Kingdom	GB 2377717
United Kingdom	GB 2361019
United Kingdom	EP 2078132
United Kingdom	EP 2150675
United Kingdom	EP 2158380
United Kingdom	EP 2102960
United Kingdom	EP 2601374
United States of America	US 6826964
United States of America	US 8330615
United States of America	US 8381812
United States of America	US 8167035
United States of America	US 8875792
United States of America	US 8752633
United States of America	US 9217327

Roxar Flow Assurance

Country/Region	Registration Number
Australia	AU 2003251240
Canada	CA 2362528
Canada	CA 2511748
China	CN 103189677
Denmark	EP 1082606
Denmark	EP 2102646
France	EP 1082606
France	EP 2102646
Germany	EP 1082606
Germany	EP 2102646
Netherlands	EP 1082606
Netherlands	EP 2102646
Norway	NO 323881
Norway	NO 313647
Norway	NO 319877
Norway	NO 321752
Norway	NO 325937
Norway	NO 328801
Norway	NO 327590
Norway	NO 332873
Norway	NO 308922
Norway	NO 325585
Norway	NO 308923
Norway	NO 317390
Norway	NO 323248
Norway	NO 321704
Norway	NO 330636
Norway	NO 329824
Norway	NO 330882
Norway	NO 335359
Norway	NO 333688
United Kingdom	GB 2382412
United Kingdom	GB 2429288
United Kingdom	EP 1923689
United Kingdom	EP 1082606
United Kingdom	EP 2102646
United States of America	US 6826964
United States of America	US 7578203
United States of America	US 6466035
United States of America	US 7654162
United States of America	US 8127621
United States of America	US 8570050
United States of America	US 8816705
United States of America	US 9151430

Roxar Flow Metering

Country/Region	Registration Number
Australia	AU 2003251240
Canada	CA 2511748
Denmark	EP 1875186
Denmark	EP 2160572
Denmark	EP 1082606
Denmark	EP 2417424
Denmark	EP 2500699
France	EP 1875186
France	EP 2160572
France	EP 1082606
France	EP 2417424
France	EP 2500699
Germany	EP 1875186
Germany	EP 2160572
Germany	EP 1082606
Germany	EP 2417424
Germany	EP 2500699
Italy	EP 2417424
Italy	EP 2500699
Netherlands	EP 1875186
Netherlands	EP 2160572
Netherlands	EP 1082606
Netherlands	EP 2417424
Netherlands	EP 2500699
Norway	NO 313647
Norway	NO 321752
Norway	NO 320172
Norway	NO 328909
Norway	NO 328055
Norway	NO 324823
Norway	NO 328801
Norway	NO 332802
Norway	NO 332873
Norway	NO 328726
Norway	NO 324571
Norway	NO 308922
Norway	NO 321930
Norway	NO 3275581
Norway	NO 317390
Norway	NO 315584
Norway	NO 323248
Norway	NO 321704
Norway	NO 324582
Norway	NO 331270
Norway	NO 329824
United Kingdom	GB 2382412
United Kingdom	GB 2429288
United Kingdom	GB 2411476
United Kingdom	GB 2437021
United Kingdom	EP 1875186
United Kingdom	EP 2160572
United Kingdom	EP 1082606
United Kingdom	EP 2417424

Roxar Flow Metering

United Kingdom	EP 2500699
United States of America	US 6826964
United States of America	US 7578203
United States of America	US 7293471
United States of America	US 7978815
United States of America	US 7938019
United States of America	US 7704016
United States of America	US 7181980
United States of America	US 7775116
United States of America	US 7133786
United States of America	US 6466035
United States of America	US 6182504
United States of America	US 7481118
United States of America	US 6915707
United States of America	US 7770469
United States of America	US 8570050
United States of America	US 8525534
United States of America	US 8483530
United States of America	US 8966994

Country/Region	Registration Number
Norway	NO 333421
Norway	NO 336002
United Kingdom	GB 2509832
United Kingdom	GB 2509831
United Kingdom	GB 2509607
United States of America	US 7663968
United States of America	US 7512529