

ATEX Instruction Sheet

Part Number: ATEX279

Publish date: July 2021

SISNet Distance Extender

KJ2222X1-BA1 SISNet Distance Extender

Hazardous Atmosphere



II 3G Ex ec IIC Gc
FM16ATEX0056U
FM21UKEX0017U



CL. I Div. 2 GP. A,B,C,D
CL. I Zone 2 AEx/Ex ec IIC Gc
FM17US0286U
FM17CA0145U

Power Specifications

Input Power 24 VDC at 250 mA (max)

Environmental Specifications

Ambient Temperature	-40°C to +70°C
Shock	10g ½ Sinewave for 11msec
Vibration	1mm Peak to Peak from 2 to 13.2Hz; 0.7g from 13.2 to 150Hz
Airborne Contaminants	ISA-S71.04 –1985 Airborne Contaminants Class G3
Relative Humidity	5 to 95% Non-Condensing

Note: Refer to the product label for serial number and location and date of manufacture.

Warning: This product has specific instructions for installation, removal and operation in hazardous areas. Refer to document 12P2046 "*DeltaV™ Scalable Process System Zone 2 Installation Instructions*". Other installation instructions are available in the "*DeltaV™ M-Series Hardware Installation and Reference*" manual.

Removal and Insertion

This unit cannot be removed or inserted with system power energized unless the area is known to be non-hazardous.

Maintenance and Adjustment

This unit contains no user serviceable parts and should not be disassembled for any reason. Calibration is not required.

Other Safety Approvals



LR87534