
For Compressed Air and Vacuum

The Aventics Poppet Valves are ideal for single acting cylinders, Air Bellows and vacuum material handling.

- CAD Drawings Available
- High Flow
- Rugged Design
- Low Cost
- cURus Approved Coils



How to Order




227 Series Pedal Valve

- 2 Position, 5 Way (5/2)
- Nylon shell & steel reinforced base plate
- Die cast zinc alloy valve body
- Spring return & detented models
- Large opening for foot operation



Technical Data


Ports (NPTF)	1/4" Spring	1/4" Pedal
Cv	136	
Maximum Operating Pressure	145 PSIG (10 Bar)	
Temperature Range	23°F to +122°F ambient (-5°C to +50°C ambient)	
Fluid Temperature Range	23°F to +122°F ambient (-5°C to +50°C ambient)	




Spring Return Pedal


Operating Data


Foot Pedal Description	Part No.
1/4" GTAP Spring Return	G227A34F20A0000
1/4" GTAP Without Spring	G227A34D20A0000



Detented Operation Pedal







NOTE: Exhaust ports 3 & 5 are located under the cover

Pedal Valve Dimensions: inches (mm)

