

Branson™ Sonifier Cell Disruptor

Acoustic Enclosure

Overview

Operating the Sonifier® in the Soundproof Enclosure can minimize mechanical noise produced by ultrasonic processing. The sturdy cabinet is lined with waterproof, sound-absorbing material, which is impervious to most solutions or laboratory reagents and can be easily cleaned. A fully-transparent door enables viewing of the process while limiting the noise to an acceptable level.

The decibel rating will lower by 20-25db.

Openings at the top and bottom of enclosure make for easy access for use with either a cup horn or standard probes.

Comes with inside column and adjustable clamp plate.

Side panel allows for placement of horns, tips and manuals.



Specifications

Actual Weight	Shipping Weight	I.D.	O.D.	Part #	Adapter #
19.5 lbs.	30 lbs.	13"W x 11"D x 21.5"H (330 x 280 x 546mm)	18.5"W x 12.5"D x 28"H (470 x 318 x 711mm)	101-063-275	100-121-074 (Only Needed for SFX 150)

For more information:
www.Emerson.com/Branson

BRANSON™

