

# BACK PRESSURE REGULATORS

MAINTAIN DESIRED OUTLET PRESSURE FOR CHANGES IN DOWNSTREAM DEMAND



## FR (Bronze, cast iron, stainless steel)

- **Body Size:** 1/2 to 2 in. / 15 to 50 mm
- **Pressure Range:** 0 to 600 psig / 0 to 41.4 barg
- **Maximum Capacity:** 4100 SCFM / 162 GPM
- **Temperature:** -320 to 600°F / -195 to 315°C



## FRM/FRM2 (Bronze, cast iron, stainless steel)

- **Body Size:** 1/4 to 1/2 in. / 8 to 15 mm
- **Pressure Range:** 0 to 600 psig / 0 to 41.4 barg
- **Maximum Capacity:** 60 SCFM / 10 GPM
- **Temperature:** -320 to 500°F / -195 to 260°C



## K Series (Bronze, Brass)

- **Body Size:** 1/4 to 2 in. / 8 to 50 mm
- **Pressure Range:** 5 to 1500 psig / 0.3 to 103.4 barg
- **Maximum Capacity:** 200 GPM
- **Temperature:** 450°F / 232°C



## KP (Brass)

- **Body Size:** 1, 1 1/4, 1 1/2, 2 in. / 25, 32, 38, 50 mm
- **Outlet Pressure Range:** 15 to 200 psig / 1 to 13.8 barg
- **Maximum Capacity:** 3010 SCFM
- **Temperature:** 160°F / 71°C