

FINAL LINE

REGULATORS USED TO CONTROL SUPPLY PRESSURE OF CRYOGENIC GAS



A-401 (Bronze)

- **Body Size:** 1/2 in. / 15 mm
- **Outlet Pressure Range:** 20 to 400 psig / 1.41 to 28.12 barg
- **Maximum Inlet Pressure:** 600 psig / 42.18 barg
- **Temperature:** -320 to 150°F / -195 to 65°C



A-31 (Brass)

- **Body Size:** 1/8, 1/4, 3/8 in. / 3.5, 8, 10 mm
- **Outlet Pressure Range:** 2 to 180 psig / 0.14 to 12.4 barg
- **Maximum Inlet Pressure:** 300 psig / 20.68 barg
- **Maximum Capacity:** 0.9 SCFM
- **Temperature:** 180°F / 82°C



E-55 (Bronze)

- **Body Size:** 1/2 to 2 in. / 15 to 50 mm
- **Outlet Pressure Range:** 10 to 300 psig / 0.69 to 20.7 barg
- **Maximum Inlet Pressure:** 400 psig / 27.6 barg
- **Maximum Capacity:** 1830 SCFM / 140 GPM
- **Temperature:** -320 to 150°F / -195 to 65°C