

RELIEF VALVES

SAFETY RELIEF VALVES MAINTAIN CRYOGENIC SYSTEM PRESSURE BELOW RATED LIMITS



C-776 (Bronze)

- **Body Size:** 1/2 x 3/4 to 2 x 2 1/2 in. / 15 x 20 to 50 x 63.5 mm
- **Pressure Range:** 1/2 to 3/4: 15 to 600 psig / 1 to 41.1 barg, 1 to 2: 15 to 500 psig / 1 to 34.5 barg
- **Maximum Capacity:** 13,632 SCFM
- **Temperature:** -320 to 150°F / -195 to 65.5°C



C600 (Brass)

- **Body Size:** 1/4, 3/8, 1/2 in. / 8, 10, 15 mm
- **Pressure Range:** 15 to 600 psig / 1 to 41.4 barg
- **Maximum Capacity:** 534 SCFM
- **Temperature:** -320 to 200°F / -195 to 93.3°C