

STEAM SERVICE

MAINTAIN DESIRED OUTLET PRESSURE FOR CHANGES IN DOWNSTREAM DEMAND



B Series (Bronze, Iron)

- **Body Size:** 250 psig / 17.2 barg
- **Outlet Pressure Range:** 2 psi / 0.14 barg
- **Maximum Inlet Pressure:** 400 psig / 27.6 barg
- **Maximum Capacity:** 5699 lbs/hr
- **Temperature:** 400°F / 204°C



G-60 (Iron, Bronze, Carbon Steel, Stainless Steel)

- **Body Size:** 1/4 to 1 1/2 in. / 8 to 38 mm
- **Outlet Pressure Range:** 1 to 600 psig / 0.07 to 41.4 barg
- **Maximum Inlet Pressure:** 700 psi / 48.2 bar
- **Maximum Capacity:** 3510 lbs/hr
- **Temperature:** -320 to 750°F / -195 to 398°C