

WATER SERVICE

MAINTAIN DESIRED OUTLET PRESSURE FOR CHANGES IN DOWNSTREAM DEMAND



A Series (Brass, Bronze)

- **Body Size:** 1/8 to 1/2 in. / 3.5 to 15 mm
- **Outlet Pressure Range:** 0 to 250 psig / 0 to 17.2 barg
- **Maximum Inlet Pressure:** 1100 psig / 75.8 barg
- **Maximum Capacity:** 13.5 GPM
- **Temperature:** 180°F / 82°C



BBC (Bronze)

- **Body Size:** 1 to 2 in. / 8 to 50 mm
- **Outlet Pressure Range:** 5 to 250 psig / 0.34 to 17.52 barg
- **Maximum Inlet Pressure:** 400 psig / 27.6 barg
- **Maximum Capacity:** 78 GPM
- **Temperature:** -320 to 150°F / -195 to 65°C



G-60 (Iron, Bronze, Carbon Steel, Stainless Steel)

- **Body Size:** 1/4 to 1 1/2 in. / 8 to 38 mm
- **Outlet Pressure Range:** 1 to 250 psig / 0.07 to 17.2 barg
- **Maximum Inlet Pressure:** 700 psi / 48.3 bar
- **Maximum Capacity:** 121 GPM
- **Temperature:** -320 to 750°F / -195 to 398°C



E-55 (Bronze)

- **Body Size:** 1/2 to 2 in. / 15 to 50 mm
- **Outlet Pressure Range:** 25 to 300 psig / 1.7 to 20.7 barg
- **Maximum Inlet Pressure:** 400 psig / 27.6 barg
- **Maximum Capacity:** 140 GPM
- **Temperature:** 180°F / 82°C



LS (Bronze)

- **Body Size:** 1/2, 3/4 in. / 15, 19 mm
- **Outlet Pressure Range:** 40 to 500 psig / 2.8 to 34.5 barg
- **Maximum Inlet Pressure:** 2400 psig / 165.5 barg
- **Maximum Capacity:** 59 GPM
- **Temperature:** 180°F / 82°C