

Flow Controls Obsolete and Inactive Products

Valves, Actuators, Accessories, and Instruments

Obsolete products may not be manufactured again in any Emerson location under any conditions. Recommended spare parts availability is guaranteed for 10 years after the last production on manufactured trim replacement parts and 5 years of best effort on die cast parts, elastomers, buyout components, and electronic components.

Inactive products are not generally promoted or available for sale but can still be quoted and manufactured under specific restricted circumstances. Conditions associated with inactive products: a product engineer may not be assigned, limited or reduced spare parts commitment, and product ownership and manufacturing availability usually designated to a facility focused on specials or a service company. Use of these products outside of the restriction requires approval of the Product Marketing Manager.

Should you need price and delivery for parts on any of these obsolete or inactive product lines listed, contact your [Emerson sales office](#).

Obsolete Products

Obsolete Product	Recommended Replacement	Obsolete Product	Recommended Replacement
7 Series	Auma	115 & 115C (obsolete 4/6/90 & 5/5/97)	None
7C	None	125	357
30 (obsolete 4/7/97)	None	126/127PJ (obsolete 6/3/91)	D2T, D3, D4
37M	None	126/127PQ (obsolete 6/3/91)	D2T, D3, D4
38	None	126/127PQA (obsolete 6/3/91)	D2T, D3, D4
38F	None	126/127PQC (obsolete 6/3/91)	D2T, D3, D4
38S	None	126/127PQF (obsolete 6/3/91)	D2T, D3, D4
43M, MS, S	None	126/127PT (obsolete 6/3/91)	D2T, D3, D4
44M	None	126/127PTA (obsolete 6/3/91)	D2T, D3, D4
49M, 49MP	None	128PQ (obsolete 6/3/91)	D2T, D3, D4
55B	None	128PQA	D2T, D3, D4

Obsolete Product	Recommended Replacement	Obsolete Product	Recommended Replacement
128PQC (obsolete 4/1/02)	D2T, D3, D4	310 (obsolete 2/6/95)	310A
128PQF (obsolete 6/3/91)	D2T, D3, D4	314 (obsolete 10/1/03)	None
169A & 169AS	None	315 (obsolete 10/1/03)	None
171F (3/8-inch)	None	320	None
171L (3/8-inch)	None	321 (obsolete 11/7/05)	REXA Xpac
183	None	323 (obsolete 9/01)	None
184	None	329 (obsolete 11/7/05)	REXA Xpac
186	None	330SA (obsolete 9/01)	None
220C	None	346/347	None
249A Series	249B	347-1061-V100	None
249N (obsolete 8/10/98)	249K	350 (obsolete 11/7/05)	REXA Xpac
249PT	None	350-8, 352-8	None
249V (obsolete 9/1/09)	249VS	352 (obsolete 11/7/05)	REXA Xpac
249VT	None	353 (obsolete 11/7/05)	REXA Xpac
254 (obsolete 6/1/95)	252	354 (obsolete 11/7/05)	REXA Xpac
254E & 254F (obsolete 3/1/98)	252	357 (obsolete 12/1/03)	D3, D4
260B	None	361 (obsolete 8/2/91)	None
260C (obsolete 4/7/97)	None	364/365	Buyout
261C	None	376	377
262C (obsolete 4/10/00)	262K	390	None
271E	None	422 (obsolete 3/12/08)	None
273	249 Series	424	None
279V & 279VBU	None	430	None
299 (obsolete 4/10/00)	299H	450	None
299SO (obsolete 4/10/00)	299HS	451	None
304 (obsolete 3/1/09)	4400	470 Size 30 & 40	585C

Obsolete Product	Recommended Replacement	Obsolete Product	Recommended Replacement
470 sizes 60 through 130 (obsolete 12/00)	585C	617 & 618 (obsolete 4/99)	None
471 sizes 60 through 130 (obsolete 12/00)	585C	643	None
475 sizes 60 through 130 (obsolete 12/00)	585C	650	None
477	None	654	None
478 (obsolete 9/01)	1061	657-8 (obsolete 9/01)	1052
490, 491, 495 (obsolete 12/00)	685	658	None
494, 496, 498	None		
513 & 513R (obsolete 6/10/96)	Baumann™ Spring & Diaphragm Actuator	658-2	None
		666	None
528TY	None	666P	None
529 (obsolete 12/31/05)	GX	666PH	None
551 (obsolete 7/6/06)	None	666PHR	None
571S	None	666PR	None
573S	None	666T	None
585 (Sizes 25 & 50) (obsolete 7/1/95)	585C	666TH	None
585 (Sizes 100) (obsolete 10/1/03)	657,667	666THR	None
585CLS	785C		
601	None	666TR	None
603 (obsolete 11/1/09)	None	688	None
607	None	690	None
608	None	772B	None
610	None	779K	None
611	None	787	None
612	None	864	None
613	None	1009	None
616/616R (obsolete 4/7/97)	655/655R	1018S (obsolete 12/31/04)	GX

Obsolete Product	Recommended Replacement	Obsolete Product	Recommended Replacement
1031 (obsolete 5/01)	G Series	3000 (obsolete 9/20/04)	None
1032 (obsolete 5/04)	HYTORK	3024	None
		3024S (obsolete 9/1/04)	3024C
1033 (obsolete 2/1/05)	None	3025 size P462, P900, P460-200	3025 size 1 and 2
1035 (obsolete 3/21/14)	Bettis RPE	3050 (obsolete 7/98)	3611JP
1051	2052	3060 (obsolete 7/98)	3621JP
1052 size 20-60	2052	3201	Buyout
1063, 1064	Bettis RPE	3511 & 3516	3610J & 3610JP
1065	Buyout	3521	Buyout
1066, 1066SR (obsolete 3/21/14)	Bettis RPE	3550T, M, G	None
1075 (obsolete 4/99)	1077	3551	4400
1076	1078	3552	4400
1082, 1083	None	3554	Buyout
1100 Series (obsolete 7/1/15)	easy-e	3555	None
1250 (obsolete 10/01)	GX	3560	3582
2340, 2341	DLC3100	3575 (obsolete 8/31/06)	None
2390 (10-50 mA) (obsolete 11/2/90)	None	3579	None
2390/2390B (obsolete 12/00)	DLC3100	3580	3582
2504	None	3583	None
		3590 (obsolete 6/1/97)	DVC7K or DVC6200
2511, 2512, 2513, 2514	2500, 2500S, 2503	4000 (obsolete 11/01)	None
2601 Series (obsolete 7/6/90)	None	4060 (obsolete 11/01)	3611JP
2602	None	4070 (obsolete 11/01)	3621JP
2660-266T (obsolete 4/1/95)	L2	4100Z (obsolete 9/1/03)	4195K , C1, or DPC2K
2680-268T (obsolete 9/27/02)	L2	4101Z (obsolete 8/4/97)	4195KS, C1, or DPC2K
2800-252V	2100E	4102Z (obsolete 8/4/97)	4195KS, C1P, or DPC2K
2900, 2901-244V (obsolete 6/3/91)	L2	4102ZR (obsolete 8/4/97)	4195K, C1P, or DPC2K

Obsolete Product	Recommended Replacement	Obsolete Product	Recommended Replacement
4103Z (obsolete 5/25/95)	4194S, C1B, or DPC2K	8510 (3 thru 12-inch) (obsolete 6/10/96)	8580
		8510 (30 & 36-inch) (obsolete 6/10/96)	8532
4103ZR (obsolete 5/25/95)	4194SR, C1B or DPC2K	8511	8560/8580
4104Z (obsolete 8/4/97)	4195KS, C1P, or DPC2K	8522 (obsolete 6/10/96)	8560/8580
4106Z (obsolete 5/25/95)	4195K, C1B, or DPC2K	8550 (obsolete 4/1/95)	8560 or 8580
4106ZR (obsolete 5/25/95)	4195KR, C1B, or DPC2K	8551 (obsolete 11/2/90)	None
		8555, 8556	8580
4150/4160 Series	4190, C1, or DPC2K	8560	8580
4150K, 4150KR (obsolete 1/1/09)	4195, C1, or DPC2K	8570A, 8570B	8580
4151K (obsolete 10/1/03)	4195K or DPC2K	9000 (obsolete 12/31/05)	GX/667 easy-e™
4152K, 4154K, 4155K (obsolete 1/1/09)	4190, C1, or DPC2K	9710	None
4153K (obsolete 10/1/03)	4195K or DPC2K	9720	None
4156K & 4166K	4196A, B, C or DPC2K	A 25 - 40 mm (Double Port) (obsolete 11/2/90)	ED/EZ
4157IK, 4158K (obsolete 1/1/09)	C1 or DPC2K	A31A, A31D (obsolete 02/02)	8532/8580
4159K (obsolete 10/1/03)	4194 or DPC2K	A41	8580
4160K, 4160KR (obsolete 1/1/09)	4195K, C1, or DPC2K	A61D (obsolete 02/02)	8532/8580
4162K, 4164K (obsolete 1/1/09)	4190, C1, or DPC2K	A81 (obsolete 10/1/15)	8580
4170, 4180 Series	4190 Series or DPC2K	AC (except 10-inch)	ET
4170, 4180 Series	None		
4200, 4300 Series	None	AC141 (obsolete 8/4/97)	None
5000 (obsolete 9/20/04)	None	AF, AFB	None
5190 & 5190S (obsolete 5/5/97)	None	AP	easy-e
5453, 5458	4194, 4194H, or DPC2K	AQR	None
6000 Silencers	PulSCO Silencers	ARS	easy-e
6020 Silencers	PulSCO Silencers	AS	easy-e
7800 (obsolete 11/2/90)	None	AV	easy-e
8500	None	A61D (obsolete 2/02)	8532/8580
8501	None	B (obsolete as Fisher product)	Baumann 2400SB

Obsolete Product	Recommended Replacement	Obsolete Product	Recommended Replacement
BA	None	CC (obsolete 9/01)	EH
Baumann 10 Rotary Actuator	None	CE	
Baumann 25 Rotary Actuator	None	1 & 2-in (obsolete 7/1/95) 3 & 4-in (obsolete 3/1/96)	CP
Baumann 54R Rotary Actuator	None	1/2 & 3/4-inch (obsolete 11/1/96)	
Baumann 863-1	3661	CP (obsolete 12/31/05)	GX, easy-e
Baumann 865-1	3660	CVG (obsolete 1/1/01)	Globe PRV
Baumann 21000 (obsolete 1/2/10)	None	CVP (obsolete 1/1/99)	Angle PRV
Baumann 25000 Lo-T (obsolete 1/2/10)	None	CVP-D (obsolete 1/1/93)	Y-Body
Baumann 25000/25000 Lo-T 3-Way (obs 1/2/10)	None	CVS-A,-C (obs 1/1/99)	TBX, PRV w/ Desuperheater
Baumann 42000 (obsolete 1/2/10)	None	CVS-E (obsolete 9/01)	CVX
Baumann 86000	None	CVX-A,-AA (obs 1/1/04) T	BX, PRV w/ Desuperheater
Baumann Belimo NV Series Electric Actuator	Baumann Belimo SV Series Electric Actuator	CVX-AY (obs 1/1/04)	Globe PRV w/ Desuperheater
Baumann Resistance Plate Multi-Port (obs 1/2/10)	None	CVX-CY,-CZ (obs 1/1/04)	Globe PRV w/ Desuperheater
BF (obsolete 9/01)	CP	CVX-S (obs 1/1/04)	TBX-S, 6010, 6011, Whisper Disk
BFC	CP	CVX-T (obsolete 1/1/04)	TBX-T
BP	None	CZA (obsolete 8/02)	None
BPO (obsolete 1/1/91)	None	D2 (obsolete 7/24/15)	D2T
BV500 (obsolete 4/1/05)	Vee-Ball/eplug (V500)	DED (obs 1/1/90)	DMA, DMA/AF, DMA/AF-HTC
B21A (obsolete 6/10/96)	8532/8580	DHY	None
C	None	DN	None
CC (obsolete 9/1/01)	EH		
Cast Bracket	2052	DNY	None
Cavitrol V for Design U	Cav Hex	DPD (obsolete 1/1/87)	None

Obsolete Product	Recommended Replacement	Obsolete Product	Recommended Replacement
DS & DSE (obsolete 8/02)	ED, ET	EK & EKR (obsolete 9/00)	ET, EZ
DSV Butterfly	8580/8532	EL (obsolete 11/7/05)	EU & EW
DSW	None	EP (obsolete 11/7/05)	easy-e or EW w/C-Seal
DT4000 (obsolete 5/97)	None	ESP (obsolete 1/1/02)	None
DVC5010 (obsolete 10/1/03)	DVC7K or DVC6200	EST	None
DVC5020 (obsolete 10/1/03)	DVC7K or DVC6200	ESR (obsolete 1/00)	easy-e, EDR, ETR
DVC5030 (obsolete 10/1/03)	DVC7K or DVC6200	EUD, 12 to 20 inch	Large ED
DVC5040 (obsolete 12/31/05)	DVC7K or DVC6200	EUT, 12 to 20 inch	Large ET
DVC6000 Series	DVC7K or DVC6200	EWB	EWD
DVC6200 HW1	DVC7K or DVC6200	EWD, 16 to 24 Inch	Large EWD
DVG (obsolete 11/7/05)	DFA	EWN NPS 16x10 (obsolete 3/27/15)	Large ED/ET
DVG/AF (obsolete 1/1/13)	DFA	EWP (obsolete 11/7/05)	easy-e or EW w/C-Seal
DVG-RSH (obs 1/1/00)	DFA, DMA, DMA/AF, DMA/AF-HTC	EWT, 16 to 24 Inch	Large EWT
DY	None	F & FA	None
EAB (obsolete 9/01)	None	FBG	Large ET/ED
EB (Spec. B, C, D F)	GX	FloVue/System 9000 (obs 12/31/05)	GX/667 easy-e valve
EC-G (obsolete 9/7/90)	None	FSV (obsolete 1/1/04)	None
EF, 667FM	None	FY	None
EHAD, EHAS, EHAT 1-8 in. CL 1500 & 1500 intermediate rated (obsolete 7/1/12)	HPAD, HPAS, HPAT	G	None
EHD, EHS, EHT 1-8 x 6 in. CL 1500 & 1500 intermediate rated (obsolete 12/31/03)	HPD, HPS, HPT	GG	None
EHP (obsolete 11/7/05)	EH w/C-Seal	GB	None
EJ/EWJ	ED Multi Ring	GBY	None
		GL (obsolete 10/01)	GX
		GR	None
		GS (obsolete 1/1/96)	Baumann 24000

Obsolete Product	Recommended Replacement	Obsolete Product	Recommended Replacement
Gulde 1011, 1013	easy-e or EH	IC	easy-e w/Style 3 Ext
Gulde 1012	EH	ITT GRINNELL SAUNDERS (obsolete 1/5/03)	None
Gulde 1018	GX or easy-e	KB (obsolete 4/99)	None
Gulde 1019, 1088	EA	Lever-Lock Handlever Actuators	None
Gulde 1021	easy-e	LPD (obs 1/1/95)	DVI, DMA, DMA/AF, DMA/AF-HTC
Gulde 1030	easy-e	M, MY, MFY, 1664	None
Gulde 1035	HP/EH	MPD (obs 1/1/95)	DVI, DMA, DMA/AF, DMA/AF-HTC
Gulde 1040	YD/Y5/GX	N850/N860 (obsolete 3/01)	None
Gulde 1042	None	NL Trunnion Mounted Ball Valve (obsolete 6/19)	None
Gulde 1045	YD/Y5 up to PN100	P	357
Gulde 1051	EA or HPA	PRC (obsolete 1/1/86)	None
Gulde 1065, 1070/1072	HPA	PTA	None
Gulde 1075,1076, 1078, 1080, 1081/1083, 1089	None	PV (obsolete 9/01)	None
Gulde 1162	ET-C	Q	None
Gulde 1163, 1215, 1500	None	SBV	V150S
Gulde 1210	Vee-Ball	SC (5/5/97)	None
Gulde 2016, 2101, 3026, 3027, 3030	None	SC (steam cooler) (obsolete 1/1/99)	TBX-T
GY	None	SPD (obsolete 1/1/97)	DVI
HC; HCB	None	SS (steam silencer) (obsolete 1/1/99)	TBX-S, 6010, 6011, Whisper Disk
H/HH/HD	None	SS 8 (obsolete 3/12/08)	None
HSC	EH	SS 31	None
HSS	EH		
HSQ	EH		
HSY	None		
HSYY	None		

Obsolete Product	Recommended Replacement	Obsolete Product	Recommended Replacement
SS 44	None	Yarway AT-54 (obsolete 2019)	AT-18
SS 78 (obsolete 3/12/08)	None	Yarway AT-55/65 (obsolete 2018)	DMA-AF/HTC TBX-T
SS 79U	None		
SS 105	None	Yarway AT-59 (obsolete 2018)	AT-18 DMA-AF/HTC
SS 112 (obsolete 3/12/08)	None	Yarway AT-60/70 (obsolete 2016)	DMA family
SS 117 (obsolete 3/12/08)	None		
SS 121	None	Yarway AT-64 (obsolete 2019)	AT-28
SS 132 (obsolete 3/12/08)	None	Yarway AT-68 (obsolete 2016)	DMA-AF/HTC
SS 138, SS 138A	SS 138B		
SS 146	ET-C, EWT-C, EZ-C	Yarway AT-69 (obsolete 2018)	AT-28 DMA-AF/HTC
SS 147 (obsolete 3/12/08)	None	Yarway AT-78 (obsolete 2016)	DMA-AF/HTC
SS 154 (obsolete 3/12/08)	None	Yarway AT-79 (obsolete 2018)	DMA-AF/HTC
SS 157 (obsolete 3/12/08)	None		
SS 201 (obsolete 3/12/08)	None	Yarway AT-80/81 (obsolete 2018)	TBX-T
SS 252A	None		
V25 (obsolete 3/6/92)	V250	Yarway AT-88 (obsolete 2018)	DVI
V100 (obsolete 9/01)	V150, V200, V300	Yarway AT-90/91 (obsolete 2019)	AT-38 special dimensions
VC1000 (obsolete 9/01)	None	Yarway AT-92/93 (obsolete 2019)	AT-18 special dimensions
Vonk Choke Valves	None	Yarway AT-98 (obsolete 2016)	DMA-AF/HTC
VSX (obsolete 4/10/00)	VSX2	YSC (obsolete 3/12/08)	None
Whisper V	Diffuser	Z	None
Yarway™ AT-11 (obsolete 2018)	GX/EZ	Z500 (obsolete 9/2/20)	None
Yarway AT-13/23 (obsolete 2018)	DMA-AF	ZLA	RSS
Yarway AT-14/44 (obsolete 2016)	DSA application		
Yarway AT-24/34 (obsolete 2016)	DSA application		
Yarway AT-33/43 (obsolete 2018)	DMA(-AF)		

Inactive Products

Inactive Product	Designated Manufacturing Facility	Restrictions on Use	Preferred Product
259B	Sakura	Nuclear replacement	249B
472 Series	Marshalltown, Cernay, Sakura,	Nuclear replacement	657/667
473 Series	Marshalltown, Cernay, Sakura,	Nuclear replacement	657/667
476		NABALCO	377 Series
3572	Ba'olan	Customer Demand	657/667-3582
3573	Ba'olan	Customer demand	657/667-3582
7600	Direct replacement if application cannot be met with another butterfly, nuclear replacement. Consult Factory	Application outside scope of POSI-SEAL, 8510B, 8532, 8560, and for direct replacement, nuclear	8580, A11
8510	Cernay	14 to 24-inch European requirements only	8532
8510B	Szekesfehervar	PN 63 and PN 100 ratings only	8580
A Single port (25 - 300 mm)	Cernay, Sakura,	UOP requirements, nuclear replacement	GX, E
A Double port (50 - 400 mm)	Marshalltown, Cernay, Sakura, India	UOP requirements, nuclear replacement	E
AA	Marshalltown, Cernay, Sakura,	Applications outside scope of EA only	EA
CVX-C, -CA	Marshalltown	Replacement only	TBX, PRV w/ Desuperheater
CVX-P	Marshalltown	Replacement only	Angle PRV
DBQ, DBAQ	Cernay, Marshalltown, Sakura,	Nuclear and direct replacement only, use HP & EH in other applications	HP, EH, Gulde 1089
U (4, 6, 8, 10, 12-inch)	Wetherill Park, Cernay, Marshalltown	High chrome iron and nuclear only	V150
U (16 & 24-inch)	Wetherill Park, Cernay, Sekura	Gas shutoff	V150
Y, YY	Marshalltown, Cernay, Sakura,	Greater than 150 mm only	YD & YS

Inactive Nuclear Power Products Only

Products are strictly limited to nuclear power applications where no other Emerson products can be qualified or accepted.

Inactive Product	Designated Manufacturing Facility	Restrictions on Use	Preferred Product
AC (size 10-inch only)	Sakura, Marshalltown	Nuclear deaerator control, nuclear replacement	ET
DB	Sakura	Nuclear spray water	HP & EH
DBQ, DBAQ	Cernay, Marshalltown, Sakura, Wetherill Park	Nuclear and direct replacement only, use HP & EH in other applications	HP, EH, Gulde 1089
DVG, DVG/AF	Marshalltown	Replacement only	DFA
EHP	Marshalltown, Cernay, Sakura		C-Seal
EL	Marshalltown, Cernay, Sakura	Replacement only, all new applications should use EU or EW	EU & EW
ENA	Marshalltown, Cernay, Sakura	Nuclear only	None
EP	Marshalltown, Cernay, Sakura		C-Seal
EWP	Marshalltown, Cernay, Sakura		C-Seal
E High Pressure	Marshalltown, Cernay, Sakura	Nuclear only	HP & EH
HS & HSV	Sakura, Marshalltown	Nuclear replacements only	EH
1073, 1074	Marshalltown	Nuclear	1077, 1078, 1079
7700	Sakura	Replacements, nuclear	8560 & 8510B
9100	Cernay	Nuclear European use only 14 to 20-inch	8510B & 8560
9200	Cernay, Marshalltown	Nuclear replacement	8560 & 8510B

D104336X012 © 2018, 2025 Fisher Controls International LLC. All rights reserved.

Neither Emerson, nor any of its affiliated entities assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher, Baumann, easy-e, Topworx, and Yarway are marks owned by one of the companies in the Emerson business unit of Emerson Electric Co. Emerson and the Emerson logo are trademarks and service marks of Emerson Electric Co. HART is a registered trademark of FieldComm Group. The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Emerson is under license. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson
Marshalltown, Iowa 50158 USA
Sorocaba, 18087 Brazil
Cernay, 68700 France
Dubai, United Arab Emirates
Singapore 128461 Singapore

www.Fisher.com

FISHER™

