



THREAD	STANDARD LENGTH	MIN LENGTH E (M)	MAX LENGTH E (M)
3/4"	1.73" (44mm)	3.75" (95mm)	157.4" (4000mm)
1"	1.73" (44mm)	3.74" (94mm)	157.4" (4000mm)

© ROSEMOUNT MEASUREMENT LIMITED 2017
THE REPRODUCTION, DISTRIBUTION & UTILISATION OF THIS DOCUMENT
AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT
EXPRESS AUTHORISATION IS PROHIBITED. OFFENDERS WILL BE HELD
LIABLE FOR THE PAYMENT OF DAMAGES. ALL RIGHTS RESERVED IN
THE EVENT OF GRANT OF PATENT, UTILITY MODEL OR DESIGN.

DIMENSIONS IN MILLIMETRES UNLESS OTHERWISE STATED

CUSTOMER:

CUSTOMER PO #

RML SO #

EMERSON SO #

CERTIFIED:

DATE:

PROJECTION



MODEL

PRINT MAY NOT BE
TO SCALE STATED.
IF IN DOUBT ABOUT
DIMENSIONS THEN ASK.
TO BS8888

TITLE

DRG, TYPE 1, 2120, THREADED
NYLON HOUSING



A3
AutoCAD

SCALE
1:2.5

DRAWN
DJS

DATE
20/03/12

DRG. NO.
02120-1005

SHEET 1 of 1