Non-Metallic Weatherproof Boxes, Covers and Lampholders

NEC/CEC: Listed for Ordinary Locations

Applications

- Marine rated boxes and covers are ideal for use in highly corrosive areas, beaches, docks, pools, or other wet location areas.
- Use in branch circuit wiring for wet, damp or dry locations.
- May be used as a junction box or a device box for switches, receptacles, GFCI's etc.
- Lampholders are for use in exterior and interior applications to provide safety and security for driveways, doorways and walkways.

Features

- Rugged PVC or polycarbonate construction prevents entry of dirt, dust and moisture.
- Resistant to impact, heat or low temperature distortion, and mold.
- Mounting can be achieved with formed in place mounting lugs.
- Smooth, accurately tapped hubs prevent wire abrasion.
- Clear UL marking and volumetric marking cast into each box facilitate electrical inspection.
- Continuous box and cover compression ensure complete sealing at gasket interface to prevent moisture entry.
- Lockable covers.
- Closure plugs (2) provided with each box.
- Remaining hubs are knockout (KO) design. No closure plugs required.
- Mounting hardware and gasket provided with each cover.
- Locking swivel knuckle on lampholders permits positive lamp positioning and accurate directional aiming.
- Lampholders are supplied with locknuts, porcelain sockets and internal gaskets for reliability and weather protection.
- Complete installation instructions provided with each item.

Standard Materials

- Boxes: PVC
- Covers: PVC or polycarbonate
- Cover screws: Nickel plated steel
- Gaskets: closed cell foam
- Sockets: porcelain (lampholders)

NEC/CEC Certifications and Compliances

• UL Standard: 514C, 514D, 1598 as applicable

- cULus Listed: E109438, E477255
- CSA Standard: C22.2 No. 18.2 (2008), C22.2 No. 42.1, C22.2 No. 42.1




Most of the boxes, covers and lampholders are individually shrink wrapped, labeled and bar coded for ease of handling and identification. Sturdy corrugated boxes with easy lift-off top with shrink wrapping facilitate merchandising.

Non-Metallic Weatherproof Boxes, Covers and Lampholders

Closure plugs and mounting lugs included.

NEC/CEC: Listed for Ordinary Locations



WSM

E

F WSP

WRX

Dimensions In Millimeters (Inches)												
Α	В	C	D	E	F	G	H	I	Catalog Number			
47.63 (1.87)	71.00 (2.8)	83.80 (3.3)	35.50 (1.4)	116.00 (4.6)	82.55 (3.25)	83.34 (3.3)	50.00 (2.0)	16.00 (0.6)	WSM150GNM			
47.63 (1.87)	71.00 (2.8)	83.80 (3.3)	35.50 (1.4)	116.00 (4.6)	82.55 (3.25)	83.34 (3.3)	50.00 (2.0)	16.00 (0.6)	WSM150WNM			
90.50 (3.6)	117.70 (4.6)	129.60 (5.1)	46.00 (1.8)	117.70 (4.6)	82.55 (3.1)	83.34 (3.3)	_	33.80 (1.3)	WSP25075GNM			
90.50 (3.6)	117.70 (4.6)	129.60 (5.1)	46.00 (1.8)	117.70 (4.6)	82.55 (3.1)	83.34 (3.3)	_	33.80 (1.3)	WSP25075WNM			
88.90 (3.5	108.60 (4.3)	127.00 (5.0)	22.00 (0.9)	69.85 (2.8)	88.90 (3.5)	_	38.00 (1.5)	16.00 (0.6)	WRX50GNM			
88.90 (3.5	108.60 (4.3)	127.00 (5.0)	22.00 (0.9)	69.85 (2.8)	88.90 (3.5)	_	38.00 (1.5)	16.00 (0.6)	WRX50WNM			

1 UL Listed Marine.

8

547

EMERSON

Non-Metallic Weatherproof Covers

NEC/CEC: Listed for Ordinary Locations


	Description	Orientation	For use with devices	Color	Catalog Number	Dimensions In Millimeters (Inches)	
• •	Blank Cover	Universal	_	Gray	WCB14GNM ①	72.89 (2.9) 47.60 (1.9) 60 (1.9) 60 (1.9) 60 (1.9) (1.	
PVC Material				White	WCB14WNM ①		
	Toggle Cover	Horizontal	_	Gray	WCT1GNM @	76.42 (3.0) 47.60 - + 47.60 - + 66.62 - - - - - - - - - - - - - - - - - - -	
PVC Material				White	WCT1WNM ②	36.25 (1.4) (1.8)	
	Lockable Cover	Horizontal	Duplex	Gray	WHD1GNM @		
Polycarbonate Material				White	WHD1WNM @	17.00 (0.7)	
	1-Gang Lampholder Cover	Universal	Lampholders	Gray	WC1350GNM ②		
Polycarbonate Material				White	WC1350WNM 2	C1 29.20 (3.0) 29.20 (1.2)	

Material

① UL Listed Marine. ② cULus Listed.

Non-Metallic Weatherproof Covers


NEC/CEC: Listed for Ordinary Locations



UL Listed Marine.
cULus Listed.

Non-Metallic Weatherproof Covers

NEC/CEC: Listed for Ordinary Locations



① cULus Listed. 2 UL Listed Marine. 3 Duplex inserts included with cover.



Ø

Ø