

Fisher™ 63EGLP and 63EGLP-16 Relief Chart for LPG and NH₃ Applications



Fisher 63EGLP-16-250
/ 63EGLP-16-NH₃



Fisher 63EGLP-250
/ 63EGLP-NH₃

LPG Hemispherical Head Tanks with 2 in. Openings

Tank Capacity	Standard OD (in.)	Fisher 63EGLP-16-250
12K	84	2
18K	109.346	2
30K	109.346	3
30K	131.875	3

NH₃ Hemispherical Head Tanks with 2 in. Openings

Tank Capacity	Standard OD (in.)	Fisher 63EGLP-16-NH ₃
12K	84	1
18K	109.346	1
30K	109.346	2
30K	131.875	1

LPG Hemispherical Head Tanks with 4 in. Openings

Tank Capacity	Overall Length (ft)	Standard OD (in.)	Fisher 63EGLP-250
30K		109.346	1
30K		131.875	1
45K		131.875	1
60K	<= 88	131.875	1
60K	+88	131.875	2
90K	130	131.875	2

NH₃ Hemispherical Head Tanks with 4 in. Openings

Tank Capacity	Standard OD (in.)	Fisher 63EGLP-NH ₃
30K	109.346	1
30K	131.875	1
45K	131.875	1
60K	131.875	1
90K	131.875	1

LPG Semi Ellipsoidal Head Tanks with 2 in. Openings

Tank Capacity	Standard OD (in.)	Fisher 63EGLP-16-250
12K	84	2
18K	109.346	2
30K	109.346	3
30K	131.875	3

NH₃ Semi Ellipsoidal Head Tanks with 2 in. Openings

Tank Capacity	Overall Length (ft)	Standard OD (in.)	Fisher 63EGLP-16-NH ₃
12K		84	1
18K		109.346	1
30K		109.346	2
30K	<= 46.8	131.875	1
30K	46.8	131.875	2

LPG Semi Ellipsoidal Head Tanks with 4 in. Openings

Tank Capacity	Standard OD (in.)	Fisher 63EGLP-250
30K	109.346	1
30K	131.875	1
45K	131.875	1
60K	131.875	1
90K	131.875	2

NH₃ Semi Ellipsoidal Head Tanks with 4 in. Openings

Tank Capacity	Standard OD (in.)	Fisher 63EGLP-NH ₃
30K	109.346	1
30K	131.875	1
45K	131.875	1
60K	131.875	1
90K	131.875	1

D450395T012