Repair Kits and Service Parts - Spare Parts Kits						
		Description	Series	Kit Number		
	0		651	M651AU434133001		
		Polycarbonate Bowl & Bowl Guard - Includes NBR Bowl Seal for Filters, Filter/Regulators and Lubricators (Electronic Liguid Level Indicator only)	652	M652AU440511001		
		······,····g-······ ····················	653	M653AU507439001		
			651	M651AU434133008		
		Polycarbonate Bowl & Bowl Guard - Includes NBR Bowl Seal for Lubricators	652	M652AU440511008		
			653	M653AU507439006		
			651	M651AU434133002		
	1.00	Metal bowl without sight gauge. Includes NBR Bowl Seal	652	M652AU440511002		
Bowls*			653	M653AU507439002		
DOWIS	ð		651	M651AU434133011		
		Metal bowl without sight gauge. Includes FKM Bowl Seal	652	M652AU440511011		
			653	M653AU507439005		
	0	Metal bowl with borosilicate (glass) sight gauge. Includes NBR Bowl Seal	651	M651AU434133004		
			652	M652AU440511004		
			653	M653AU507439004		
			651	M651AU434133015		
		Metal bowl with borosilicate (glass) sight gauge. Includes FKM Bowl Seal	652	M652AU440511015		
			653	M653AU507439013		
		Metal bowl without sight gauge. Includes NBR Bowl Seal	653	M653AU507439002		
High Pressure		Metal bowl without sight gauge. Includes FKM Bowl Seal	653	M653AU507439005		
Bowls	0	Metal bowl with borosilicate (glass) sight gauge. Includes NBR Bowl Seal	653	M653AU507439004		
		Metal bowl with borosilicate (glass) sight gauge. Includes FKM Bowl Seal.	653	M653AU507439013		
High Flow Bowls	-	Metal bowl without sight gauge. Includes NBR Bowl Seal. (Coalescing Filter and Filter/Regulator High Flow)	653	M653AU523308001		
		Metal bowl without sight gauge. Includes FKM Bowl Seal. (Coalescing Filter and Filter/Regulator High Flow)	653	M653AU523308002		

* For lubricator replacement metal bowls, please also order bowl plug p/n M699AQ440512001. This is not required if the Electronic Liquid Level Indicator is used.

AVENTICS[®]



Repair Kits and Service Parts - Spare Parts Kits						
		Description	Series	Kit Number		
		Drain Plug Assembly. Provides an option to customers that do not want to use a bowl drain. Includes NBR Bowl Seal.	651 652 653	M699AQ440512001		
		Semi-Automatic/Manual Drain Assembly - with NBR seals. This normally open drain can be used as a manual drain or set to semi-automatic, which will drain the bowl upon a loss of system pressure. Drain material is plastic.	651 652 653	M699AQ440512002		
		Semi-Automatic/Manual Drain Assembly - with FKM seals. This normally open drain can be used as a manual drain or set to semi-automatic, which will drain the bowl upon a loss of system pressure. Drain material is plastic.	651 652 653	M699AQ440512007		
	9	Manual Stainless Steel Drain Assembly - with NBR seals. Provides the user with an alternative to the plastic semi-automatic drain.	651 652 653	M699AQ440512003		
Drains	Ť	Manual Stainless Steel Drain Assembly - with FKM seals. Provides the user with an alternative to the plastic semi-automatic drain.	651 652 653	M699AQ440512008		
		Automatic Drain Assembly - Normally Open - with NBR seals. This drain uses a float that initiates the bowl to drain when the liquid rises. In addition, all fluid will drain when the pressure drops below 22 PSI. Drain material is brass. This drain can also be operated manually.	651 652 653	M699AQ501862001		
		Automatic Drain Assembly - Normally Closed - with NBR seals. When under pressure this drain uses a float that initiates the bowl to discharge when the liquid rises. When not under pressure the drain is closed. Drain material is brass. This drain can also be operated manually.	651 652 653	M699AQ501862002		
		Pulse Drain - with NBR seals. The diaphragm in this drain pulses when there is a pressure differential such as a valve cycling or cylinder stroking downstream. This action flexes the diaphragm and allows the filter to discharge the entrapped water. This drain features an incorporated barbed fitting which fits 3/16 ID tubing for easy discharge of liquid and contaminant.	651 652 653	M699AQ440512015		
	Bowl and Drain Assembly - Includes Polycarbonate Bowl/Guard and Semi-Autom Drain Assembly (NBR Seals).		651	M651AU514009001		
Bowl & Drain		Bowl and Drain Assembly - Includes Polycarbonate Bowl/Guard and Semi-Automatic Drain Assembly (NBR Seals).	652	M652AU513311001		
Assembly			653	M653AU514103001		
			651	M651AH507403001		
		U-Cup Seal Kit (NBR Seals). Kit contains 10 U-Cup seals. This seal is used for all bowls.	652	M652AH507085001		
Bowl Seal			653	M653AH514106001		
Kits	$\mathbf{\bigcirc}$		651	M651AH507403002		
		U-Cup Seal Kit (FKM Seals). Kit contains 10 U-Cup seals. This seal is used for all bowls.	652	M652AH507085002		
			652	M653AH514106002		
	August		651	M651AY524218001		
Side Cover Kits	AVENTICS	Blank Side cover Kit with no product identification.	652	M652AY524218002		
COVET INITS			653	M653AY524218003		



Repair Kits and Service Parts - Spare Parts Kits							
		Description	Series	Kit Number	Color		
			651	M651AE434063001			
		5 Micron Particulate Filter Element	652	M652AE433582001	White		
			653	M653AE439490001			
	\bigcirc		651	M651AE434063002	_		
		25 Micron Particulate Filter Element	652	M652AE433582002	Yellow		
			653	M653AE439490002			
			651	M651AE525276001	_		
		0.3 Micron Coalescing Filter Element	652	EKF22D	Green		
			653	EKF32D	Green		
		0.3 Micron Coalescing Filter Element (High Flow)	653	M653AE516209001			
			651	M651AE525276003			
		0.01 Micron Coalescing Filter Element	652	EKF22E	Red		
			653	EKF32E	Keu		
Filter		0.01 Micron Coalescing Filter Element (High Flow)	653	M653AE516209003			
Elements			651	M651AE525276002			
		0.3 Micron Coalescing Filter Element - with 3 Micron pre-filter	652	EKF22DD	Green		
			653	EKF32DD	Gleen		
		0.3 Micron Coalescing Filter Element - with 3 Micron pre-filter (High Flow)	653	M653AE516209002			
			651	M651AE525276004			
		0.01 Micron Coalescing Filter Element - with 3 Micron pre-filter	652	EKF22ED			
			653	EKF32ED	- Red		
		0.01 Micron Coalescing Filter Element - with 3 Micron pre-filter (High Flow)	653	M653AE516209004			
			651	EKF12F			
	9	Adsorber (Activated Carbon) Filter	652	EKF22F			
			653	EKF32F	- White/Clear		
		Adsorber (Activated Carbon) Filter (High Flow)	653	M653AE516209005			



Repair Kits and Service Parts - Spare Parts Kits

	Description			Series	Kit Number
				651	P651AT504958001
	Body-to-Body Assembly Clamps (Includes NBR O-Ring). Clamp material is aluminum.				P652AT502466001
0		653	P653AT507291001		
				651	P651AT504958003
	Body-to-Body Assembly Clamps (Include FKM O-Ri aluminum.	ng). Clamp	materialis	652	P652AT502466003
				653	P653AT507291003
	Body-to-Body Assembly Clamps (Includes NBR O-Rin	g) and Wall	/Panel Bracket Kit	651	P651AT535310001
	includes one bracket and two screws for attaching bracket	acket to bo	dy clamp. Clamp	652	P652AT535311001
5 1	material is aluminum.			653	P653AT535312001
1	Body-to-Body Assembly Clamps (Includes FKM O-Rin	g) and Wall	/Panel Bracket Kit	651	P651AT535310002
	includes one bracket and two screws for attaching bracket			652	P652AT535311002
	material is aluminum.			653	P653AT535312002
			1/4 ISO228/1-G	651	T651AT504959002
		NBR	1/2 ISO228/1-G	652	T652AT502468002
AL N.	End Plate Kit: Includes two end plates and body- to-body assembly clamps & O-Ring. End plate material is aluminum.	O-Ring	1 ISO228/1-G	653	T653AT507292002
19			1-1/4 ISO228/1-G	653	T653AT507292020
			1/4 ISO228/1-G	651	T651AT504959008
0		FKM O-Ring	1/2 ISO228/1-G	652	T652AT502468008
			1 ISO228/1-G	653	T653AT507292008
			1-1/4 ISO228/1-G	653	T653AT507292026
- Bo	Panel Adapter P1 + P2 to mount 651 or 652 product on both side of the panel. Certified NEMA 1,4; IP66.	FKM O-Ring	not threaded _	651	T651AT522204001
0000				652	T652AT519954001
1000 C	P2 Panel Adapter to connect P1 inlet to 651 or 652	FKM	1/4 ISO228/1-G	651	T651AT522204003
⁰ .0.00	product. Certified NEMA 1,4; IP66.	O-Ring	1/2 ISO228/1-G	652	T652AT519954003
000	P1 Panel Adapter to connect P2 outlet to 651 or 652	FKM	1/4 ISO228/1-G	651	T651AT522204005
· 0. 0.	product. Certified NEMA 1,4; IP66.	O-Ring	1/2 ISO228/1-G	652	T652AT519954005
				651	M651AH536213001
		1	NBR O-Ring	652	M652AH536214001
\bigcap	Kit Contains 10 O-Ring seals for body to body kit.			653	M653AH536215001
\mathcal{O}	The contains to or hing scals to body to body kit.			651	M651AH536213002
		F	KM O-Ring	652	M652AH536214002
				653	M653AH536215002



Repair Kits and Service Parts - Spare Parts Kits						
	Description	Series	Kit Number			
a the sha	Wall/Panel Bracket Kit includes one bracket and two screws for attaching bracket to body clamp. Two brackets are required for mounting three or more products. One bracket is suitable for mounting two products. Material is aluminum.	651 652 653	P699AT502467001			
651/ 652	Side Mounting Brackets (Includes two brackets): Designed for mounting single		P651AT503860001			
653	products to wall or panel, but is capable of handling up to 3 stations. Material is stainless steel. Recommended only for static applications (without vibration).	652	P652AT503860002			
		653	P653AT503860003			
	Panel Nut: Used for Regulators and Filter-Regulators where adjustment knob is fed through a panel and the panel nut is then used to secure the product to the panel. Material is polyamide.	651	P651AT513928001			
		652	P652AT513177001			
	Panel Nut & Bracket: The panel nut and bracket are used to mount a Regulator or	651	P651AT503861001			
	Filter/Regulator to a wall or panel. Materials are stainless steel and polyamide.	652	P652AT503861002			
eco.	651 Adapter Kit for L1 Valve Series	651	M651AY528751001			
	652 Adapter Kit for L2 Valve Series	652	M652AY528750001			



Repair Kits and Service Parts - Spare Parts Kits						
		Description	Series	Kit Number		
No Gauge		No Gauge Cover Kit - NBR Seal. Includes gauge cover, screw and o-ring	651/652/653	M699AG503396001		
No Gauge		No Gauge Cover Kit - FPM Seal. Includes gauge cover, screw and o-ring	651/652/653	M699AG503396002		
		Integrated Gauge - Series 651/652/653: 0-6 bar Scale with NBR seals	651/652/653	M699AG438047002		
		Integrated Gauge - Series 651/652/653: 0-6 bar Scale with FPM seals	651/652/653	M699AG438047014		
		Integrated Gauge - Series 651/652/653: 0-12 bar Scale with NBR seals	651/652/653	M699AG438047001		
		Integrated Gauge - Series 651/652/653: 0-12 bar Scale with FPM seals	651/652/653	M699AG438047013		
		Integrated Gauge - Series 653: 0-25 bar Scale with NBR seals	651/652/653	M699AG438047003		
		Integrated Gauge - Series 653: 0-25 bar Scale with FPM seals	651/652/653	M699AG438047015		
Integrated gauges*	0	Pressure Range Indicators (Red/Green) for low profile integrated gauges. Desired range can be easily set in the field. This kit allows customers to add the pressure range indicator to existing low profile integrated gauges in the field.	651/652/653	M699AG500179001		
		Integrated Gauge with Pressure Range Indicators - 651/652/653 Series: 0-6 bar Scale with NBR seals	651/652/653	M699AG438047008		
	64	Integrated Gauge with Pressure Range Indicators - 651/652/653 Series: 0-12 bar Scale with NBR seals	651/652/653	M699AG438047007		
	- All	Integrated Gauge with Pressure Range Indicators - 653 Series and Shut-off Isolation Valves: 0-25 bar Scale with NBR seals	651/652/653	M699AG438047009		

* Each of the Integrated and Round Gauges are dual scale. The scale that is listed in the description has the units located near the outside of the scale. The other units would be on the inside.

Note: For all pressure switches & round gauges that are added to the 651/652/653 series products in the field, a port plate is required. The port plate can be added at the time of order entry or as a kit.



SERIES 651/652/653

Repair Kits and Service Parts - Spare Parts Kits					
		Description	Series	Kit Number	
Digital Gauge		Digital Pressure Gauge - 651/652/653 Series: 0-145 PSI Scale (User can change units: bar, MPa, Kgf/cm²) 1/8" ISO 7/1 Rc	651/652/653	M699AG504650002	
		Round Gauge - 0-4 bar 1/8 ISO 7/1 Rc and 40 mm Face Diameter	651/652/653	34300015	
		Round Gauge - 0-10 bar 1/8 ISO 7/1 Rc and 40 mm Face Diameter	651/652/653	34300014	
		Round Gauge - 0-12 bar 1/8 ISO 7/1 Rc and 40 mm Face Diameter	651/652/653	34300041	
		Round Gauge - 0-25 bar 1/8 ISO 7/1 Rc and 50 mm Face Diameter	651/652/653	34200063	
Round Gauges*		Round Gauge - 0-4 bar 1/8 ISO 7/1 Rc and 50 mm Face Diameter	651/652/653	34200061	
		Round Gauge - 0-12 bar 1/8 ISO 7/1 Rc and 50 mm Face Diameter	651/652/653	34200062	
		Round Gauge - 0-16 bar 1/8 ISO 7/1 Rc and 50 mm Face Diameter	651/652/653	34200997	
		Stainless Steel Round Gauge - 0-12 bar 1/8 ISO 7/1 Rc and 50 mm Face Diameter	651/652/653	34303242	
Port Plates	00	Gauge Port Plate Assembly - 1/8 ISO 7/1 Rc	651/652/653	M699AG440510002	
Pressure		DPS280 Pressure Switch/Sensor - NPN M8 with Cable 1/8 ISO 7/1 Rc	651/652/653	DPS280NRQ8	
Switch/Sen- sor		DPS280 Pressure Switch/Sensor - PNP M8 with Cable 1/8 ISO 7/1 Rc	651/652/653	DPS280PRQ8	

* Each of the Integrated and Round Gauges are dual scale. The scale that is listed in the description has the units located near the outside of the scale. The other units would be on the inside.

Note: For all pressure switches & round gauges that are added to the 651/652/653 series products in the field, a port plate is required. The port plate can be added at the time of order entry or as a kit.



Repair Kits and Service Parts - Spare Parts Kits

Repair Kits and Service Parts - Spare Parts Kits							
		Description	Series	Kit Number			
	ê	Lubricator Dome Repair Kit - NBR seals. Includes dome cover, screw and O-Rings.	651 652 653	M699AY506842001			
Lubricator		Lubricator Dome Repair Kit - FKM seals. Includes dome cover, screw and O-Rings.	651 652 653	M699AY506842002			
Repair Kits		Lubricator Level Switch assembly kit. Includes level switch, stainless steel retainer ring, O-Ring and bushing.	651 652 653	M699AG506837001			
		Lubricator Bowl Plug assembly: Includes Lubricator bowl plug, stainless steel retainer ring and NBR O-Ring.	651 652 653	M699AQ440512001			
	Ţ	Particulate Filter Repair Kit - Includes the filter retainer, head baffle, lower end cap and bowl baffle.	651	M651AY570170001			
			652	M652AY506833001			
			653	M653AY514105001			
		Differential Pressure Pop-Up Indicator (NBR Seals). This is used for the Coalescing Filters to provide visual indication when the filter element needs to be replaced.	651 652 653	M699AG439851001			
Filter Kits	P	Differential Pressure Pop-Up Indicator (FKM Seals). This is used for the Coalescing Filters to provide visual indication when the filter element needs to be replaced.	651 652 653	M699AG439851004			
		DPI Plug (NBR Seals). This is used to plug the top port on the filter when a Differential Pressure Indicator is not used.	651 652 653	M699AG439851002			
		DPI Plug (FKM Seals). This is used to plug the top port on the filter when a Differential Pressure Indicator is not used.	651 652 653	M699AG439851005			
	٢	Electric Differential Pressure Indicator (NBR Seals). This is used for the Coalescing Filter only. It provides a contact that will actuate when the filter element needs to be replaced.	651 652 653	M699AG439851003			



Repair Kits and Service Parts - Spare Parts Kits							
		Description	Series	Kit Number			
			651	M651AY514012001			
		Adjusting Screw Repair Kit - Includes adjusting screw, nut, washer and screw.	652	M652AY506952001			
		· · · · · · · · · · · · · · · · · · ·	653	M653AY514104001			
	2		651	M651AY514012002			
	4	Key Lockable Adjusting Screw Repair Kit - Includes adjusting screw, adjusting nut, flat	652	M652AY506952002			
	T	washer and screw.	653	M653AY514104002			
		Tamper Resistant Repair Kit - Includes adjusting screw, adjusting nut, flat washers	651	M651AY514012003			
	T	and screws.	652	M652AY506952003			
			653	M653AY514104003			
			651	M651AY519042001			
	-	Replacement Knob for Regulator or Filter/Regulators.	652	M652AY519042003			
			653	M653AY519042005			
			651	M651AY519042002			
		Replacement Knob for the tamper resistant or key lockable Regulator or Filter/Regulators	652	M652AY519042004			
			653	M653AY519042006			
			651	M651AY507175001			
	4	Poppet Repair Kit (NBR Seals): Includes poppet, stem & seals.	652	M652AY506863001			
	1		653	M653AY507270001			
		Poppet Repair Kit (FKM Seals): Includes poppet, stem & seals.	651	M651AY507175002			
			652	M652AY506863002			
			653	M653AY507270002			
Regulator							
& Filter Regulator		Diaphragm Assembly Repair Kit (Pilot Operated Regulator NBR Seals).	652	M652AH435268001			
Kits		Diaphragm Assembly Repair Kit (Pilot Operated Regulator FKM Seals).	652	M652AH435268002			
		Diaphragm Assembly Repair Kit (Relieving Regulator NBR Seals)	651	M651AH504954001			
			652	M652AH434213001			
			653	M653AH502120001			
		Diaphragm Assembly Repair Kit (Relieving Regulator FKM Seals)	651	M651AH504954002			
			652	M652AH434213002			
			653	M653AH502120002			
	<u> </u>		651	M651AH504954003			
		Diaphragm Assembly Repair Kit (Non-relieving Regulator NBR Seals)	652	M652AH434213003			
			653	M653AH502120003			
	Tell		651	M651AH504954004			
		Diaphragm Assembly Repair Kit (Non-relieving Regulator - FKM Seals)	652 653	M652AH434213004			
			651	M653AH502120004 M651AY514010001			
		Main Spring (3 bar)	652	M652AY513313001			
			653	M653AY516711001			
			651	M651AY504691001			
		Main Spring (4 bar)	652	M652AY438708001			
	Q		653 651	M653AY516710001 M651AY504692001			
	E.	Main Spring (8 bar)	652	M652AY438709001			
			653	M653AY516709001			
			651	M651AY514011001			
		Main Spring (10 bar)	652	M652AY513314001			
			653	M653AY516708001			



Repair Kits and Service Parts - Spare Parts Kits							
		Description	Series	Part/Kit Number			
		Horizontal Solenoid Operator (190) - With Impulse Manual Operator	651 652	19090017			
		Horizontal Solenoid Operator (190) - Without Manual Override	651 652	19090005			
		24 VDC coil with 3 Pin M12 Connection, for 190 Pilot Horizontal Solenoid Operator	651 652	43005525			
		24 VDC coil with DIN Spade connection for 190 Pilot Horizontal Solenoid Operator	651 652	43004473			
	100	120 VAC coil with DIN Spade connection for 190 Pilot Horizontal Solenoid Operator	651 652	43004471			
		24 VAC coil with DIN Spade connection for 190 Pilot Horizontal Solenoid Operator	651 652	43004469			
	M	240 VAC coil with DIN Spade connection for 190 Pilot Horizontal Solenoid Operator	651 652	43004472			
		DIN Connector, without LED - 190 Pilot Horizontal Solenoid Operator	651 652	88122602			
		DIN Connector, with LED, for 24 VAC/DC coil - 190 Pilot Horizontal Solenoid Operator	651 652	88122603			
3/2 Slow		DIN Connector, with LED, for 120 VAC coil - 190 Pilot Horizontal Solenoid Operator	651 652	88122605			
Start/ Quick Exhaust		DIN Connector, with LED, for 240 VAC coil - 190 Pilot Horizontal Solenoid Operator	651 652	88122608			
Valve Kits		Vertical Solenoid Operator (189) - Without Manual Override	651 652	18990007			
		24 VDC coil with 3 Pin M12 Connection, for 189 Pilot Vertical Solenoid Operator	651 652	43005523			
		24 VDC coil with DIN Spade connection for 189 Pilot Vertical Solenoid Operator	651 652	43004166			
	_	120 VAC coil with DIN Spade connection for 189 Pilot Vertical Solenoid Operator	651 652	43004419			
	AL -	24 VAC coil with DIN Spade connection for 189 Pilot Vertical Solenoid Operator	651 652	43004416			
		240 VAC coil with DIN Spade connection for 189 Pilot Vertical Solenoid Operator	651 652	43004422			
		DIN Connector, without LED - 189 Pilot Vertical Solenoid Operator	651 652	88122404			
		DIN Connector, with LED, for 24 VAC/DC coil - 189 Pilot Vertical Solenoid Operator	651 652	88122405			
		DIN Connector, with LED, for 120 VAC coil - 189 Pilot Vertical Solenoid Operator	651 652	88122407			
		DIN Connector, with LED, for 240 VAC coil - 189 Pilot Vertical Solenoid Operator	651 652	88122410			



Repair Kits and Service Parts - Spare Parts Kits						
		Description	Series	Part/Kit Number		
		Horizontal Solenoid Operator (192) - With Impulse Manual Operator	653	19291012		
		Horizontal Solenoid Operator (192) - Without Manual Override	653	19291010		
		24 VDC coil with 3 Pin M12 Connection, for 192 Pilot Horizontal Solenoid Operator	653	43005664		
		24 VDC coil with DIN Spade connection for 192 Pilot Horizontal Solenoid Operator	653	43005642		
	6.1.2	115 VAC/120 VAC coil with DIN Spade connection for 192 Pilot Horizontal Solenoid Operator	653	43005617		
3/2 Slow Start/ Quick Exhaust Valve Kits		24 VAC coil with DIN Spade connection for 192 Pilot Horizontal Solenoid Operator	653	43005604		
Valve Rits		230 VAC/240 VAC coil with DIN Spade connection for 192 Pilot Horizontal Solenoid Operator	653	43005627		
		DIN Connector, without LED - 192 Pilot Horizontal Solenoid Operator	653	88122602		
		DIN Connector, with LED, for 24 VAC/DC coil - 192 Pilot Horizontal Solenoid Operator	653	88122603		
		DIN Connector, with LED, for 115 VAC/120 VAC coil - 192 Pilot Horizontal Solenoid Operator	653	88122605		
		DIN Connector, with LED, for 230 VAC/240 VAC coil - 192 Pilot Horizontal Solenoid Operator	653	88122608		
Jumper Plate Kit	the co	Jumper Plate Kit: For Air Operated Internally Piloted 3/2 Slow Start-QE Valve	651 652 653	M699AY513316001		
Pilot Port Plate		Pilot Port Plate: For Air Operated Externally Piloted 3/2 Slow Start-QE Valve, 1/8 ISO 7/1 Rc	651 652 653	M699AY513318001		
		Pilot Port Plate: For Air Operated Externally Piloted 3/2 Slow Start-QE Valve, 1/8 NPTF	651 652 653	M699AY513318002		



Accessories						
		Description	Series	Part Number		
Scissor Lock	0	Scissor Lock for Shut Off Isolation Valve & Lockout Valve	651 652 653	VB-1		
		Metal Muffler – G 1/4 (Shut Off Isolation Valves & Slow Start/Quick Exhaust Valves)	651 652	M2MB		
		Metal Muffler – G 3/8 (Shut Off Isolation Valves & Slow Start/Quick Exhaust Valves)	653	МЗМВ		
Mufflers/Silencers		Metal Muffler – G 1/2 (Slow Start/Quick Exhaust & Lockouts)	652	M4MB		
Mumerspinencers		Metal Muffler – G 1 (Slow Start/Quick Exhaust & Lockouts)	653	M6MB		
		Polyethylene Muffler – G 1/4 (Shut Off Isolation Valve)	651 652	34600407		
		Polyethylene Muffler – G 3/8 (653 - Shut Off Isolation Valve)	653	34600408		
Key Locking Device		Key Lock for Regulator and Filter/Regulator supplied seperately with 2 keys	651 652 653	M699AY438663001		

