

HART Reference Card

00829-0100-4716, Rev AA

May 2008

Rosemount 3095

Rosemount 3095 MultiVariable™ Mass Flow Transmitter

Product Discontinued

Table 1. 3095 Fast Key Sequence

Function	HART Fast Keys	Function	HART Fast Keys
% Rnge	1, 1, 2	Diff press damp	1, 4, 2, 4
% Rnge	1, 1, 5, 1, 3	Diff press	1, 1, 1
4V is	1, 1, 5, 4, 1	Diff press	2
AO Alm typ	1, 4, 1, 1, 1	Drain vent matl	1, 3, 5, 8
AO1	1, 1, 3	Factory Trim	1, 2, 2, 2, 3
AO1	3	Fill Fluid	1, 3, 5, 5
AP Damping	1, 4, 2, 5, 2	Final asbly num	1, 3, 4, 5
AP Sens Trim	1, 2, 2, 1, 2	Flange type	1, 3, 5, 7
AP Units	1, 3, 2, 2	Fld dev rev	1, 3, 4, 9, 2
Absolute (AP)	1, 1, 4, 2	Flnge matl	1, 3, 5, 6
Atm Press Cnfg	1, 4, 2, 3	Flo rate	1, 1, 4, 5
Burst mode	1, 4, 1, 2, 4, 2	Flow Rate Special Units	1, 4, 5, 1
Burst option	1, 4, 1, 2, 4, 1	Flow Units	1, 3, 2, 5
Change PV Assgn	1, 1, 5, 1, 5	GP Damping	1, 4, 2, 5, 4
Change SV Assgn	1, 1, 5, 2, 3	GP Sens Trim	1, 2, 2, 1, 3
Change TV Assgn	1, 1, 5, 3, 3	GP Units	1, 3, 2, 4
Change 4V Assgn	1, 1, 5, 4, 3	Gage (GP)	1, 1, 4, 4
D/A Trim	1, 2, 2, 2, 1	Hardware rev	1, 3, 4, 9, 4
DP Low Flow Cutoff	1, 4, 6	Isoltr matl	1, 3, 5, 4
DP LRV	4	LCD Settings	1, 4, 3
DP Sens Trim	1, 2, 2, 1, 1	Loop test	1, 2, 1, 1
DP Snsr Range	1, 3, 5, 1	Manufacturer	1, 3, 4, 6
DP URV	5	Message	1, 3, 4, 3
DP Unit	1, 3, 2, 1	Model	1, 3, 4, 7
Date	1, 3, 4, 4	Num remote seal	1, 3, 5, 13
Descriptor	1, 3, 4, 2	Num req preams	1, 4, 1, 2, 2

HART®

ROSEMOUNT

www.rosemount.com



EMERSON
Process Management

Rosemount 3095

Function	HART Fast Keys	Function	HART Fast Keys
Num resp preams	1, 4, 1, 2, 3	Scaled D/A trim	1, 2, 2, 2, 2
O ring matl	1, 3, 5, 9	Snsr module hw rev	1, 3, 4, 9, 6
PV is	1, 1, 5, 1, 1	Snsr module sw rev	1, 3, 4, 9, 5
Poll addr	1, 4, 1, 2, 1	Software rev	1, 3, 4, 9, 3
Process temp unit	1, 3, 2, 3	Status group 1	1, 6
Process temp	1, 1, 4, 3	Totalizer	1, 4, 4
RS fill fluid	1, 3, 5, 11	Totalizer Special Units	1, 4, 5, 2
RS isoltr matl	1, 3, 5, 12	TV is	1, 1, 5, 3, 1
RS type	1, 3, 5, 10	Tag	1, 3, 1
RTD Config	1, 4, 2, 2	Temp Sens Trim	1, 2, 2, 1, 4
Range values	1, 3, 3	Temp damp	1, 4, 2, 5, 3
Reset	1, 2, 1, 3	Universal rev	1, 3, 4, 9, 1
SP Snsr Range	1, 3, 5, 2	View status	1, 2, 1, 2
SP Type	1, 3, 5, 3	Write protect	1, 3, 4, 8
SV is	1, 1, 5, 2, 1	Xmtr Var Slot Assn	1, 4, 1, 2, 4, 3


HART Reference Card

00829-0100-4716, Rev AA

May 2008

Rosemount 3095

Figure 1. Rosemount 3095 HART Menu Tree



Rosemount 3095

Rosemount and the Rosemount logotype are registered trademarks of Rosemount Inc. All other marks are the property of their respective owners.

Emerson Process Management

Rosemount Inc.

8200 Market Boulevard
Chanhassen, MN 55317 USA
T (U.S.) 1-800-999-9307
T (International) (952) 906-8888
F (952) 949-7001

Rosemount Flow

Groeneveldselaan 6-8
3903 AZ Veenendaal
The Netherlands
T 31 (0) 318 549 549
F 31 (0) 318 549 559

Emerson Process

Management Asia Pacific Private Limited

1 Pandan Crescent
Singapore 128461
T (65) 6777 8211
F (65) 6777 0947

www.rosemount.com



ROSEMOUNT®

