

WET/DRY VACS



RIDGID PROFESSIONAL- INDUSTRIAL WET/DRY VACS

Size	4 Gal
Power	5 Peak Horsepower
Drain	No
Cord Length	20'
Accessories Included	Car Nozzle, Diffuser
Filter Type Included	VF3500, ½ Height Standard Filter
Hose Included	Locking 1½" x 8' Pro Hose (Fits 1½" Accessories)
Special Features	Ergonomic Handle w/ Cord Wrap



50313
4000RV

Size	4.5 Gal Pro Pack®
Power	5 Peak Horsepower
Drain	No
Cord Length	20'
Accessories Included	Two 1½" Wands, Utility Nozzle, Crevice Tool, Dusting Brush
Filter Type Included	VF3500, ½ Height Fine Dust Filter
Hose Included	Locking 1½" x 7' Expandable Hose (Fits 1½" Accessories)
Special Features	Carry Handle, Accessory Storage, Tool Box Design



50318
4500RV

Size	10 Gal Pro Pack® Plus
Power	5.0 Peak Horsepower
Drain	Yes
Cord Length	20'
Accessories Included	Two 2½" Wands, Crevice Tool, Utility Nozzle, Dusting Brush
Filter Type Included	VF5000, Fine Dust Filter
Hose Included	Locking 1½" x 7' Expandable Hose (Fits 1½" Accessories)
Special Features	Telescopic Transport Handle, Carry Handle, Accessory Storage, Large Tool Box Design



50328
1000RV

Size	6 Gal
Power	4.25 Peak Horsepower
Drain	No
Cord Length	10'
Accessories Included	Two 1½" Wands, Utility Nozzle
Filter Type Included	VF4000, Standard Filter
Hose Included	Locking 1½" x 8' Pro Hose (Fits 1½" Accessories)
Special Features	Carry Handle, Caster Foot Storage



50308
6000RV

Size	12 Gal
Power	5 Peak Horsepower
Drain	Yes
Cord Length	15'
Accessories Included	Two 2½" Wands, Car Nozzle, Utility Nozzle, Wet Nozzle
Filter Type Included	VF4000, Standard Filter
Hose Included	Locking 1½" x 8' Pro Hose (Fits 2½" Accessories)
Special Features	Carry Handle w/ Cord Wrap, Integrated Handles, Caster Foot Storage



50323
1200RV

Size	14 Gal w/ Cart
Power	6 Peak Horsepower
Drain	Yes
Cord Length	20'
Accessories Included	Two 2½" Wands, Car Nozzle, Utility Nozzle, Wet Nozzle, Crevice Tool
Filter Type Included	VF5000, Fine Dust Filter
Hose Included	Locking 1½" x 8' Pro Hose (Fits 2½" Accessories)
Special Features	Carry Handle w/ Cord Wrap, Large Rear Wheels w/ Cart, Accessory Storage, Scroll Noise Reduction



50348
1400RV

Size	16 Gal w/ Detachable Blower
Power	6.5 Peak Horsepower
Drain	Yes
Cord Length	20'
Accessories Included	Two 2½" Wands, Car Nozzle, Utility Nozzle, Wet Nozzle, Locking Blowing Wand
Filter Type Included	VF4000, Standard Filter
Hose Included	Locking 1½" x 8' Pro Hose (Fits 2½" Accessories)
Special Features	Detachable Blower, Quick Release Cord Wrap, Accessory Storage, Caster Foot Storage



50343
1620RV

Size	16 Gal Stainless w/ Cart
Power	6.5 Peak Horsepower
Drain	Yes
Cord Length	20'
Accessories Included	Two 2½" Wands, Car Nozzle, Utility Nozzle, Wet Nozzle, Crevice Tool
Filter Type Included	VF5000, Fine Dust Filter
Hose Included	Locking 1½" x 8' Pro Hose (Fits 2½" Accessories)
Special Features	Carry Handle w/ Cord Wrap, Accessory Storage, Scroll Noise Reduction, Stainless Steel Drum, Large Rear Wheels w/ Cart



50353
1610RV

Size	14 Gal 2-Stage Motor w/ Cart
Power	11.5 Amps
Drain	Yes
Cord Length	25'
Accessories Included	Two 2½" Wands, Floor Brush, Utility Nozzle, Wet Nozzle, Crevice Tool, Diffuser
Filter Type Included	VF5000, Fine Dust Filter
Hose Included	Locking 1½" x 10' Pro Hose (Fits 2½" Accessories)
Special Features	Carry Handle w/ Cord Wrap, Scroll Noise Reduction, Accessory Storage, 2 Stage Motor, Large Rear Wheels w/ Cart



50358
RV2400A

Size	16 Gal 2-Stage Motor w/ Cart
Power	11.5 Amps
Drain	Yes
Cord Length	25'
Accessories Included	Two 1½" Metal Wands, Master Nozzle with Squeegee Insert, Brush Insert, Carpet Insert, Crevice Tool, Dusting Brush, Claw Nozzle, Diffuser
Filter Type Included	VF5000, Fine Dust Filter
Hose Included	Locking 1½" x 10' Pro Hose (Fits 2½" Accessories)
Special Features	Carry Handle w/ Cord Wrap, Scroll Noise Reduction, Accessory Storage, 2-Stage Motor, Large 'Non-Marking' Rear Wheels w/ Cart



50363
RV2600B

Size	12 Gal Motor-on-Bottom
Power	6.5 Peak Horsepower
Drain	Yes
Cord Length	20'
Accessories Included	Two 1½" Wands, Wet Nozzle, Car Nozzle, Utility Nozzle, Crevice Tool
Filter Type Included	VF5000, Fine Dust Filter
Hose Included	Locking 1½" x 8' Pro Hose (Fits 2½" Accessories)
Special Features	Easy to Empty Drum w/ Motor-on-Bottom Design, Scroll Noise Reduction, Foot Activated Switch, Accessory Stretch Caddy



50333
1250RV

Size	16 Gal Motor-on-Bottom w/ Cart
Power	6.5 Peak Horsepower
Drain	Yes
Cord Length	20'
Accessories Included	Two 2½" Wands, Utility Nozzle, Crevice Tool, Car Nozzle
Filter Type Included	VF5000, Fine Dust Filter
Hose Included	Locking 1½" x 8' Pro Hose (Fits 2½" Accessories)
Special Features	Easy to Empty Drum w/ Motor-on-Bottom Design, Scroll Noise Reduction, Non-Marking Large Rear Wheels w/ Cart, Foot Activated Switch, Accessory Caddy



50338
1650RV

Size	14 Gal HEPA
Power	11.5 Amps
Drain	Yes
Cord Length	25'
Accessories Included	Two 2½" Wands, Utility Nozzle, Floor Brush, Wet Nozzle, Crevice Tool, Dusting Brush, Turbo Nozzle with Adapter, Diffuser
Filter Type Included	1 Filter Bag (VF3502), HEPA Pre-Filter, Certified HEPA Filter
Hose Included	Locking 1½" x 10' Pro Hose (Fits 2½" Accessories)
Special Features	Carry Handle w/ Cord Wrap, Scroll Noise Reduction, Accessory Storage, Certified HEPA Filtration, 2-Stage Motor, Meets Requirements for RRP



50368
RV2400HF

Size	14 Gal Smart Pulse™ w/ Cart
Power	11.5 Amps
Drain	Yes
Cord Length	25'
Accessories Included	Muffler/Diffuser
Filter Type Included	2 VF3800 PTFE Coated Filters
Hose Included	Locking 1½" x 15' Pro Hose (Fits 2½" Accessories)
Special Features	Carry Handle w/ Cord Wrap, Accessory Storage, 2 Stage Motor, Large Non-Marking Rear Wheels w/ Cart



50373
RV3410

RIDGID® Professional - Industrial Vacs are built with a commitment to superior performance, technology and quality.

These Vacs are available exclusively at RIDGID® Distributors throughout the United States and Canada.

MOTOR ON BOTTOM

50338 1650RV
50333 1250RV



THE MOST POWERFUL RIDGID® VAC EVER
24% greater than our previous best.

- **STABLE**
Low center of gravity provides stability.
- **EASY TO EMPTY**
Filter stays in drum when emptying, allowing for easier, cleaner debris disposal. Drum detaches from the power sled/cart with quick-slide lock lever.
- **HANDS-FREE**
Foot-activated power switch allows for easy access and hands-free operation.

50373 RV3410 SMART PULSE™ VAC



- 1 Airstream puffs into filter.**
- 2 Filters alternate pulsing.**
- 3 Vacuum stream continues uninterrupted.**

The Smart Pulse™ vac is designed with two filters and an integrated sensor. The sensor is continuously monitoring suction efficiency. When a pressure difference inside the vac vs. the outside of the filter is recognized by the sensor, the vac begins an alternating pulsing cycle, back-flushing air through the filter. This process cleans the filter automatically, yet only when needed, providing uninterrupted performance and maximizing efficiency.

RIDGID® Professional-Industrial Vacs Provide:

- Powerful performance
- Rugged, long-lasting construction
- Thoughtful on-board accessory storage
- Innovative designs that provide versatility

QWIK LOCK® FILTERS

*See product specification for compatibility.



STANDARD FILTER
5 microns / 95% efficiency

- Everyday Dirt & Dust



FINE DUST FILTER
1 micron / 99% efficiency

- Everyday Dirt & Dust
- Cold Ashes
- Fine Powders
- Sawdust
- Drywall & Cement Dust



HEPA MEDIA FILTER
1 micron / 99.7% efficiency

- Everyday Dirt & Dust
- Sawdust
- Drywall & Cement Dust
- Cold Ashes
- Fine Powders
- Pet Dander
- Pollens
- Allergens
- Dust Mites
- Mold Spores
- Dryer Lint
- Furnace Filter



WET PICK-UP FILTER

- High Volume Liquid Pickup
- Water Borne Debris



PTFE FILTER

Slick coating of filter resists debris collection allowing more efficient operation.

RIDGID® Professional-Industrial Vacs are built to last and come standard with the best warranty in the industry. Our reputation for superior quality and durability allows us to stand behind our Vacs with the **RIDGID® Full Lifetime Warranty** against defects in workmanship and material.



DUST BAGS


*See product specification for more details.



The use of a dust bag allows for clean, quick and easy debris removal. These dust bags install easily into the drum and are adaptable to most vac models.




VF3501 23738 Fits 3-4.5 gallon vacs
VF3502 23743 Fits 12-16 gallon vacs
VF3503 40153 Fits 6-10 gallon vacs



MAXIMIZE YOUR VAC

WITH ACCESSORIES YOU NEED FOR THE JOB



2½" Wet Nozzle 72912 (VT2510)
1½" Wet Nozzle 31738 (VT1710)
Squeegee for liquid clean-ups.

2½" Floor Brush 72922 (VT2514)
1½" Floor Brush 40168 (VT1714)
Excellent for large area clean-ups.

2½" Dusting Brush 72887 (VT2501)
1½" Dusting Brush 31718 (VT1701)
Versatile, go anywhere, do anything brush.

2½" Crevice Tool 72932 (VT2502)
1½" Crevice Tool 31723 (VT1702)
Great for getting into tight spots.

2½" Blower/Car Nozzle 72937 (VT2503)
1½" Blower/Car Nozzle 29848 (VT1781)
Ideal for cleaning car, boat, RV, or van.

2½" Extension Wands 72902 (VT2508)
1½" Extension Wands 31728 (VT1708)
Extends vac reach.

Muffler/Diffuser 72927 (VT2525)
For quieter operation.

Claw Nozzle 26578 (VT2540)
Deep and thorough cleaning.
Fits 2½", 1½" & 1¼" hose sizes.

Carpet Nozzle 26573 (VT2530)
Cleans carpet and hard surfaces.
Fits 2½" & 1¼" Vacs.

2½" Utility Nozzle 72907 (VT2509)
1½" Utility Nozzle 31733 (VT1709)
Perfect for cleaning up large areas.

Locking 1½" x 7' Expandable Hose 54223 (VT1721)
Length expands from 2' to 7' and locks onto vac for uninterrupted cleaning.

Locking 1½" Pro Hose

- 8 foot:
Fits 2½" Accessories 54193
Fits 1½" Accessories 54183
- 10 foot:
Fits 2½" Accessories 30458
Fits 1½" Accessories 31098
- 15 foot: (Comes with RV3410)
Fits 2½" Accessories 54188

Prevents clogged debris and locks onto vac for uninterrupted cleaning.

PRO HOSE

- All units include the Pro Hose (except the 4500RV and 1000RV which feature a Locking Expandable Hose).
- The Pro Hose does not crimp or collapse and offers 180° Flexibility.
- The Pro Hose is equipped with a large 1½" opening (with 2½" adaptor cuff when applicable) and a smooth interior surface that prevents debris from clogging.
- The locking mechanism secures the hose to the vac quickly and easily, so as to not pull loose during use.




PREMIUM ANTI-STATIC HOSE



- The 15' Premium Non-Static Dissipative Locking Hose won't pull loose during use and reduces static build up when used with the 14 Gal Smart Pulse™ Vac.

HOSE & ACCESSORY DIAMETERS

All RIDGID® Hoses fit all RIDGID® Vacs.



Accessories available online at: RIDGID.com

