

Emerson Pro Series Thermostats

Family	Model Number	MaxStage Heat/Cool		Program Style	Comments
		Conventional	Heat Pump		
Sensi™ Wi-Fi 	1F86U-42WF	2/2	4/2	7 Day	Universal 4H/2C – Wi-Fi Thermostat
80 Series™ 	1F85U-42PR	2/2	4/2	7 Day, 5+1+1 Day or Off	Universal 4H/2C
	1F85U-42NP	2/2	4/2	Non-Prg	Universal 4H/2C
	1F85U-22PR	2/2	2/1	7 Day, 5+1+1 Day or Off	Universal 2H/2C
	1F85U-22NP	2/2	2/1	Non-Prg	Universal 2H/2C
	1F83H-21PR		2/1	7 Day, 5+1+1 Day or Off	Heat Pump 2H/1C
	1F83H-21NP		2/1	Non-Prg	Heat Pump 2H/1C
	1F83C-11PR	1/1	1/1	7 Day, 5+1+1 Day or Off	Single Stage 1H/1C
	1F83C-11NP	1/1	1/1	Non-Prg	Single Stage 1H/1C
Easy Install 	1HDEZ-1521	2/2	4/2	7 Day	Universal 4H/2C – Hi-Def
	1F98EZ-1421	2/2	4/2	7 Day	Universal 4H/2C – Easy Install
	1F98EZ-1441	2/2	4/2	7 Day	Universal 4H/2C – Easy Install (with outdoor remote sensor)
	1F98EZ-1621	2/2	4/2	7 Day	Universal 4H/2C – Wireless Easy Install
12" Blue™ Series 	1F95-1291	2/2	4/2	7 Day	Universal 4H/2C – Humidity
	1F95-1280	2/2	4/2	7 Day	Universal 4H/2C – Commercial
	1F95-1277	2/2	4/2	7 Day	Universal 4H/2C
	1F97-1277	1/1	2/1	7 Day	Single Stage or Heat Pump 2H/1C
6" Blue™ Series 	1F95-0680	2/2	4/2	7 Day	Universal 4H/2C – Commercial
	1F95EZ-0671	2/2	4/2	7 Day	Universal 4H/2C – Easy Reader
	1F95-0671	2/2	4/2	7 Day	Universal 4H/2C
2" Blue™ Series 	1F86EZ-0251	1/1		Non-Prg	Single Stage 1H/1C – Easy Set
	1F89EZ-0251		2/1	Non-Prg	Single Stage or Heat Pump 2H/1C – Easy Set
	1F80-0261	1/1		5/1/1 Day	Single Stage 1H/1C
	1F80-0224	1/1		24 Hour	Single Stage 1H/1C
	1F86-0244	1/1		Non-Prg	Single Stage 1H/1C
	1F82-0261		2/1	5/1/1 Day	Heat Pump 2H/1C
	1F89-0211		2/1	Non-Prg	Heat Pump 2H/1C
Classic 80 Series 	1F87-361	1/1	1/1	7 Day	Single Stage 1H/1C
	1F80-361	1/1	1/1	5/1/1 Day	Single Stage 1H/1C
	1F82-261		2/1	5/1/1 Day	Heat Pump 2H/1C
	1F86-344	1/1	1/1	Non-Prg	Single Stage 1H/1C
	1F89-211		2/1	Non-Prg	Heat Pump 2H/1C
70 Series 	1F78-151	1/1	1/1	5/2 Day	Single Stage 1H/1C
	1F72-151		2/1	5/2 Day	Heat Pump 2H/1C
	1F78-144	1/1	1/1	Non-Prg	Single Stage 1H/1C
	1E78-140	1/0		Non-Prg	Heat Only 1H/ØC (Vertical)
	1F79-111		2/1	Non-Prg	Heat Pump 2H/1C
	1E78-144	1/1	1/1	Non-Prg	Single Stage 1H/1C (Vertical)
	1E78-151	1/1	1/1	5/2 Day	Single Stage 1H/1C (Vertical)