
## Type C403, C404, C413 & C414 3-Inch Single and Double Flanged Internal Valve Parts Sheet

Pai	rts List		Key	Description	Part Number
	Disc Guide Kit for C403:	T13201T0012	15D	Spring	T1154737022
	Includes key numbers 13, 39 (2 required),	11020110012	15E	Washer (2 required)	T1154825072
	40 (2 required), 47, and Loctite Compound	۸	15F*	Male Adaptor	T1154901012
	40 (2 required), 47, and Locule Compound	u	15G*	Packing Ring (3 required)	T1155001012
			15H*	Female Adaptor	1H941601012
	Replacement Parts KitPacking Assem	•	15J	Stub Shaft	T2043135072
	Includes Key Numbers 7, 11, 15B, 15F,150	G, 15H, 15K, 19,	15K*	Liner Bushing	T1155106992
	23, 43, 44, 54 and both upper gaskets (val	ve to tank) for	15L	Rod Wiper	T1155206992
	pre 1990 and post 1990 constructions	,	15M	Bonnet	T1155324102
	C403 and C413	RC40324T012	15P	Cam	T1155521992
	C404 and C414	RC40424T012	15R	Cap Screw	
	C404 and C414	110404241012		C403 and C413	T12576T0012
				C404 and C414	1B848024052
			15S	Washer	1C225628982
Key	Description	Part Number	18	Lever	T1155919312
-	•		19*	Cotter Pin	1H837128982
1	Body		20	Nameplate	Not Orderable
	C403 and C413	T8013922012	21	Drive Screw (2 required)	1A368228982
	C404 and C414	T8015322012	22	Pipe Plug (C403 and C413 only)	T13718T0012
2	Stem Assembly		23*	Washer	T1188228982
	C403 and C413	T11887000A2	25	Strainer	T12317T0012
	C404 and C414	T12766T00A2	29	Cap Screw (C404 and C414 only)	
2A	Stem			(4 required)	T12775T0012
	C403 and C413	T1177235032	30	Fusible Link	1J157443992
	C404 and C414	T12763T0012	33	Travel Stop (C403 and C413 only)	T1240838072
2B	Follower Assembly	T11880000A2	35	Bushing (C404 and C414 only)	T12767T0012
	Plug Holder	T1187135132	37	Cage	T40298T0012
00	Wear Plug	T1187201012	38	Strainer Cap	
2C	Groove Pin	1J1560T0012		C403	T12318T0012
3	Excess Flow Spring Closing Flow GPM Propane			C404	T13473T0012
	(Yellow) 150	T1192537022	39	Nut (C403 Only) (2 required)	1J719228982
	(Orange) 200	T1192337022	40	Bolt	
	(Pink) 250	T1215237022		C403 (2 required)	T1127235132
	(Black) 400	T1177337022		C404 (2 required)	T12776T0012
	(Cadmium) 500	T1226237022	41	C413 (2 required) Stud Bolt	1D617032992
4	Spring Seat		41	C403 and C413 (16 required)	1N946228982
•	C403 and C413	T1153624102		C403 and C413 (16 required) C404 and C414 (8 required)	1P790832982
	C404 and C414	T12764T0012	42	Nut (16 required)	1A368124112
5	Closing Spring	T1153737022	43	Gasket, Upper (Valve to Tank)	17300124112
6	Disc Holder	T2042924102	70	Post 1990 Construction	T13603T0012
7*	Main Disc	T1177403032		Pre 1990 Construction	1P877799152
8	Disc Retainer	T1177525072	44	Gasket, Lower (Valve to Pump)	000.02
9	Screw (3 required)	1A954828992	• •	C403 and C413	T1056138992
10	Disc Retainer	T1154224102		C404 and C414	1P877699152
11*	Bleed Disc	T11543T0012	45	Lubricant	Dow Corning 111
12	Disc Holder	T1154424102	46	Seal 5	Loctie 242
13	Nut		47	Guide Bracket (C403 and C413 Only)	T20798T0012
	C403 and C413	T13200T0012	49	Seal 11	Loctite 277
	C404 and C414	T12765T0012	50	Lube 5	Never Seize
15B	Liner Bushing		51	Lube 9	Magnalube G
	C403 and C413	T1154506992	52	Seal 12	PipeThread Tape
	C404 and C414	T12762T0012	53	Cap Screw (C403 and C413 Only)	p
15C	Washer	T1154625072		(2 required)	T12776T0012
			54	Instruction Manual	D450034T012

<sup>\*</sup> Recommended Spare Part







KEYS 18, 19, 24, 30, 42, 43, 44, 45 NOT SHOWN

Figure 1. C403-24 and C413-24 Assembly

T80154\_2




Figure 2. C404-24 and C414-24 Assembly

T40326

## **LP-Gas Equipment**

**Emerson Process Management Regulator Technologies, Inc.** 

USA - Headquarters McKinney, Texas 75069-1872 USA Telephone: 1 (800) 558-5853 Telephone: 1 (972) 548-3574

For further information visit www.fisherregulators.com/lp

The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their prospective owners. Fisher is a mark owned by Fisher Controls, Inc., a business of Emerson Process Management.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Process Management does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any Emerson Process Management product remains solely with the purchaser.

