

White-Rodgers Distributor Residential Cooling Season Stocking List

THERMOSTATIC EXPANSION VALVES

TXV+CONNECT 2-1/2TR-22 066657	TXV with Chatleff and Aeroquip adapters 1-1/2 to 3 tons R-22
TXV+CONNECT 5TR-22 066658	TXV with Chatleff and Aeroquip adapters 3-1/2 to 5 tons R-22
TXV+CONNECT 1-1/2TR-410A 066660	TXV with Chatleff and Aeroquip adapters 1-1/2 tons R410A
TXV+CONNECT 2TR-410A 066661	TXV with Chatleff and Aeroquip adapters 2 tons R-410A
TXV+CONNECT 3TR-410A 066662	TXV with Chatleff and Aeroquip adapters 3 tons R-410A
TXV+CONNECT 4TR-410A 066663	TXV with Chatleff and Aeroquip adapters 4 tons R-410A
TXV+CONNECT 5TR-410A 066664	TXV with Chatleff and Aeroquip adapters 5 tons R-410A

FILTER DRIERS

EK 083S 047608	Premium Liquid Line Drier, 8 cu. in. 3/8" ODF
EK 163S 047614	Premium Liquid Line Drier, 16 cu. in. 3/8" ODF
BSL 083S 066759	Economy Liquid Line Drier, 8 cu. in. 3/8" ODF
BSL 163S 066761	Economy Liquid Line Drier, 16 cu. in. 3/8" ODF
BFK 083S 043323	Premium Bi-Directional Drier, 8 cu. in. 3/8" ODF
BFK 163S 043333	Premium Bi-Directional Drier, 16 cu. in. 3/8" ODF
BSB 083S 066130	Economy Bi-Directional Drier, 8 cu. in. 3/8" ODF
BSB 163S 066131	Economy Bi-Directional Drier, 16 cu. in. 3/8" ODF

CONTACTOR & CONTACTOR UPGRADE

90-244	Contactors 30 Amp, 2 pole, 24V coil
90-245	Contactors 30 Amp, 2 pole, 120V coil
49P11-843	Electronic Contactor upgrade for mechanical contactors up to 40 Amp, 1.5 pole

HEAT PUMP DEFROST CONTROL

47D01U-843	Single Stage Heat Pump Defrost Control for PSC fan systems
------------	--

TRANSFORMERS & RELAYS

90-340	Relay DPDT, 24V coil, contact ratings: 12FLA@125V, 6FLA@ 250/277V
90-290Q	Fan Relay SPNO, 24V coil, contact ratings: 8FLA@125V/250V
90-293Q	Fan Relay SPDT, 24V coil, contact ratings: 8FLA@125V/250V
90-370	Fan Relay SPDT, 24V coil, contact ratings: 12FLA@125V, 8FLA@250V
90-380	Fan Relay SPNO/SPNC, 24V coil, contact ratings: 12FLA@125V, 8FLA@250V
90-T40F3	Transformer 40VA 60Hz, 120/208/240V Pri, 24V sec, foot mount

INTEGRATED FURNACE CONTROLS

50M56U-843	Single Stage HSI Integrated Furnace Control Kit for PSC inducer and blower motors
21M51U-843	Two Stage HSI Integrated Furnace Control Kit for PSC inducer and blower motors
21V51U-843	Two Stage HSI Integrated Furnace Control Kit for PSC inducer and variable speed blower motors

SENSI™ THERMOSTATS

1F95U-42WF	Wi-Fi, Universal, Touchscreen, White
1F95U-42WFB	Wi-Fi, Universal, Touchscreen, Black
1F87U-42WF	Wi-Fi, Universal, Classic

80 SERIES™ THERMOSTATS

1F85U-42PR	Universal, Programmable
1F85U-42NP	Universal, Non-Programmable
1F85U-22PR	Universal, Programmable
1F85U-22NP	Universal, Non-Programmable
1F83C-11NP	Conventional, Non-Programmable
1F83C-11PR	Conventional, Programmable
1F83H-21PR	Heat Pump, Programmable
1F83H-21NP	Heat Pump, Non-Programmable

CLASSIC 80 SERIES™ THERMOSTATS

1F82-261	Heat Pump, Programmable
1F89-211	Heat Pump, Non-Programmable
1F80-361	Conventional, Programmable
1F86-344	Conventional, Non-Programmable

BLUE SERIES™ THERMOSTATS

1F95-1291	Universal, 12", Humidity
1F95-1277	Universal, 12", Programmable
1F95-1280	Universal, 12", Commercial
1F95EZ-0671	Universal, Easy Reader™
1F95-0680	Universal, 6", Commercial
1F95-0671	Universal, 6", Programmable
1F82-0261	Heat Pump, 2", Programmable
1F89-0211	Heat Pump, 2", Non-Programmable
1F97-1277*	Conventional, 12", Programmable
1F80-0261	Conventional, 2", Programmable
1F80-0224	Conventional, 2", Programmable
1F86-0244	Conventional, 2", Non-Programmable

* Also for Heat Pump 2H/1C

70 SERIES™ THERMOSTATS

1F78-144	Conventional, Non-Programmable
----------	--------------------------------