



NOTES:

1. FLOW PATH VALVE ENERGIZED: — — —
FLOW PATH VALVE DE-ENERGIZED: ———
2. OPTIONAL 4 OR 8 STREAMS. THE LAST STREAM USED IS THE CALIBRATION INPUT.
3. INSTALL 3" OF .004 ID 1/16 TUBING FOR FLOW RESTRICTION.



TOP VIEW OF ANALYZER OVEN FROM FRONT



SSO-1 WIRING

SI METRIC						
THIRD ANGLE PROJECTION						
	E	3-12-07	DLT	ECO-XX-5002636	EM	DLT
	D	6-4-04	DLT	ECO-XX-206304	EM	DLT
MATERIAL	C	5-25-04	DLT	ECO-XX-205951	EM	DLT
N/A	B	3-26-04	HM	ECO-XX-200113	DLT	BLB
FINISH	A	11-7-03	HM	RELEASED	EM	SB
N/A	REV	DATE	DRN	DESCRIPTION	CHKD	APPD
PROJ. FILE NO. - NONE	FILENAME: CE25004E1.DWG, DATE: 03-12-07, TIME: 2:02 P.M.					

THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK. IT SHALL NOT BE REPRODUCED AND SHALL BE RETURNED TO US ON DEMAND. ALL RIGHTS ARE RESERVED.

GEOMETRIC TOLERANCES & DIMENSIONS PER ANSI Y14.5 LATEST REVISION

UNLESS OTHERWISE NOTED ALL DIMENSIONS IN INCHES
 .X.XX ±.015
 X.XXX ±.005
 ANGULAR ±0° 30'
 FINISH 200 RA MAX

BREAK ALL SHARP CORNERS TO .003-.015 RADIUS AND REMOVE ALL BURRS

EMERSON
Process Management

TITLE
FLOW CONFIG.
DET. 1 B/F TO MEAS.
MODEL 700

DRN HM	DATE 11-4-03	DWG NO.	REV
CHKD EM	DATE 11-7-03	CE-25004	E
APPD SB	DATE 11-7-03	SCALE NTS	P/N SEE ORDER
			SHT 1 OF 1