


Fisher™ Type 63EGLP Bulk Plant Relief Valve

HIGHER RELIEF CAPACITY AND LOWER MAINTENANCE THAN MULTI-PORT RELIEF

Innovative Dual Pilot-Operated Technology for overpressure protection of your Liquid Petroleum (Propane, Butane, etc.) and Natural Gas Liquids stationary storage tanks



Multi-Port Relief

Type 63EGLP



Advantages of Type 63EGLP to Multi-Port Relief Valves

- ✓ 40% greater relief capacity
- ✓ 33% greater surface area protection reduces number of relief valves/tank
- ✓ Compact profile and 60 lbs lighter reduces installation time
- ✓ Replacement cost of about \$2000 for 2 pilots compare to about \$4500 for 4 spring relief valves
- ✓ Pilot spring is in atmosphere instead of in product, minimizing chance for harsh chemicals to attack spring under compression

UL® is a mark owned by Underwriters Laboratories.

NUMBER OF VALVES REQUIRED/TANK ⁽¹⁾		
Tank Size (Gal / L)	Fisher Type 63EGLP	Competitor's Multi-port
30,000 / 113,562	1	1
45,000 / 170,344	1	2
60,000 / 227,125	2	2
90,000 / 340,687	2	2
120,000 / 454,250	2	3

1. Recommended values for standard above ground tanks, based on 250 psig set point. Actual relief capacity/surface area must be calculated by user.

FISHER™

www.fisherregulators.com
1-800-558-5853


EMERSON™
Process Management

EMERSON. CONSIDER IT SOLVED.™

D4503807012 © 2015, 2016 Emerson Process Management Regulator Technologies, Inc. All rights reserved. Printed in the U.S.A. 03/16. Fisher, Emerson Process Management, and the Emerson Process Management design are marks of the Emerson Process Management group of companies.