

Who can best match your needs for fast and reliable delivery of control valves in Europe?



Your Best Match control valve solution Solve your needs fast and reliably

Keeping a plant up and running is a difficult task. Managing turnarounds and assuring maximum plant uptime can easily cause serious headaches. Your plant could be down longer than scheduled because the new control valve you ordered is late. Or the length of your maintenance plan could impact your plant productivity because of the long lead time of purchased valves. And in many cases, you don't get the proper support in selecting the right control valve with short and reliable lead time.

As a consequence, the timing of your maintenance is delayed and unreliable. Your production will suffer, because your plant will be up and running late, meaning loss of production and efficiency. This affects the financial bottom line of your plant.

Emerson can help you solving these issues with its **Best Match** control valves.

WHAT IF, YOU COULD

- execute your plant upgrade projects faster without compromising on quality or reliability of the control valves?
- plan your maintenance more efficiently and accurately based on short and very reliable control valve lead times?
- Get the best solution that 100% covers your process and SH&E requirements, and taking into account price, lead time and delivery reliability?

"Every hour a plant is down costs \$40,000 to \$50,000. That works out to about \$1 million per day"

ARC Advisory Group



Your Best Match control valves SOLUTIONS



HP series High pressure
Sub types HPD, HPT & HPS
NPS 1 to 6 and CL 900
to 2500 WCC



GX General & Chemical Service
DN 15 to 100 / PN 10 to 40
NPS 1/2 to NPS 4 / CL150 & 300
WCC, CF3M, 1.0619, 1.4409
GX 3-way



easy-e™ universal
Sub types: ES, ED, ET, EZ, EWT, EWD
DN 25 to 300, PN 16 to 40
NPS 1 to 8, CL 150 to 600
LCC, WCC, WCC HT, CF8M SST



High Performance Butterfly Valves
Types: 8580 & Control-Disk™
NPS 2 to 12 and CL150 to 600 /
PN 10 to 40
WCC, 1.0619, CF3M SST,
1.4409 SST



Vee-Ball™ valve
Types: V150 & V300
DN25 to 200 and PN 10 to 40
NPS 1 to 8 and CL150 to 300
WCC, 1.0619, CF3M SST,
1.4409 SST
Types: V500
DN25 to 150 and PN10 to 40
NPS1 to 6 and CL 150 to 600
CF3M, WCC and WCC HT

Your Best Match control valve solution at a glance

Best Match control valves offer excellent and highly reliable lead times by giving priority throughout the whole production process to a large range of main stream valves, and by completely revising the supply chain and production processes.

Best Match control valves offer a huge product range which gives you a good chance to find a valve that serves your need :

- 3 to 12 weeks reliable lead times depending on size, material, and complexity
- 17 types of valves
- 62.000 control valves constructions

How can you benefit?

Call your local Fisher sales consultant to work out the **Best Match** control valves solution for your needs.



What's your opportunity?

Get your valves when you need them!

The solution: Fisher Best Match control valves program with short and highly reliable leadtimes.



How can you reach us?

Please consult www.fisher.com to find your local sales office.



Video



Emerson Process Management

Patrijsweg 140
NL 2289 EZ Rijswijk
T +31 (0)70-4136666
www.fisher.com



© 2015 Emerson Process Management. All rights reserved.

The Emerson logo is a trademark and service of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, nothing herein is to be construed as a warranty or guarantee, express or implied, regarding the products or services described herein or their use, performance, merchantability or fitness for a particular purpose. Individual results may vary. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice. Responsibility for proper selection, use, and maintenance of any product or service remains solely with the purchaser and end user.



D352366X0NL / printed in Europe / 9-15

