

20-1000 Series

Regulators - Pressure Reducing

D20101932X012

Specifications

For other materials or modifications, please consult TESCOM.

OPERATING PARAMETERS

Pressure rating per criteria of ANSI/ASME B31.3

Maximum Inlet Pressure

3600 psig / 248 bar

Outlet Pressure Ranges

50-89 psig / 3.4-6.1 bar

90-200 psig / 6.2-13.8 bar

201-320 psig / 13.9-22.1 bar

Leakage

Bubble-tight

Filtration

40 micron nominal

Operating Temperature

-40°F to 200°F / -40°C to 93°C

Flow Capacity (approximate)

$C_v = 0.5$

MEDIA CONTACT MATERIALS

Body

Aluminum 6061-T6 with Nickel Plating

Seat

Vespe[®]

Main Valve

17-4 Stainless Steel

Sensor

Aluminum 6061-T6

Sensor Insert

17-4 Stainless Steel

Remaining Parts

300 Series Stainless Steel, Teflon[®], Buna-N, Ethylene Propylene

OTHER

Cleaning

CGA 4.1 and ASTM G93

Connections

1/4" Inlet, 3/8" Outlet, NPTF, and SAE

Weight

1.4 lbs / 0.6 kg

Vespe[®] and Teflon[®] are registered trademarks of E.I du Pont de Nemours and Company.



TESCOM 20-1000 Series regulator is designed with lightweight aluminum construction for onboard compressed natural gas vehicles with 7 liter engines and larger. Piston sensed for long service life with a heat exchanger to prevent freezing.


Application

- Compressed natural gas vehicles

Features and Benefits

- Piston-sensed design provides a long service life and enhanced safety
- High flow, low pressure drop
- Balanced valve design minimizes supply pressure effect
- Lightweight, precision machined aluminum construction
- Used in diverse applications for a broad range of temperatures, flows, and pressures
- Wide variety of preset outlet pressures are available
- Heat exchanger eliminates freeze-up
- NGV 3.1 approved



20-1000 Series Regulator Drawing



All dimensions are reference & nominal
Metric [millimeter] equivalents are in brackets

20-1000 Series Regulator Flow Charts

For more information on how to read flow curves, please refer to the Flow Curves and Calculations document (debul2007x012) in the TESCOM catalog or on www.tescom.com.



20-1000 Series Regulator Part Number Selector

Repair Kits, Accessories & Modifications may be available for this product. Please contact TESCOM for more information.

Example for selecting a part number:

20-10	3	1	- 2	9	01			
BASIC SERIES	BODY MATERIAL	MAXIMUM OUTLET PRESSURES	SET PRESSURE RANGES	PORT TYPE	INLET AND OUTLET SIZE	SET PRESSURE		
20-10	3 – 6061-T6 Aluminum	1 – 125 psig 8.6 bar	50-89 psig 3.4-6.1 bar	1 – SAE 2 – NPTF	9 – 1/4" Inlet 3/8" Outlet	01 – 50 psig 3.4 bar	10 – 275 psig 19.0 bar	19 – 65 psig 4.5 bar
						02 – 75 psig 5.2 bar	11 – 300 psig 20.7 bar	20 – 70 psig 4.8 bar
		03 – 100 psig 6.9 bar	12 – 90 psig 6.2 bar	21 – 89 psig 6.1 bar				
		04 – 125 psig 8.6 bar	13 – 185 psig 12.8 bar	22 – 140 psig 9.7 bar				
		05 – 150 psig 10.3 bar	14 – 110 psig 7.6 bar	26 – 80 psig 5.5 bar				
		06 – 175 psig 12.1 bar	15 – 120 psig 8.3 bar	27 – 105 psig 7.2 bar				
		07 – 200 psig 13.8 bar	16 – 170 psig 11.7 bar	28 – 60 psig 4.1 bar				
		08 – 225 psig 15.5 bar	17 – 320 psig 22.1 bar	29 – 115 psig 7.9 bar				
		09 – 250 psig 17.2 bar	18 – 135 psig 9.3 bar	30 – 95 psig 6.6 bar				



WARNING! Do not attempt to select, install, use or maintain this product until you have read and fully understood the *TESCOM Safety, Installation and Operation Precautions*.

D20101932X012 © 2012 Emerson Process Management Regulator Technologies, Inc. All rights reserved. 05/2012.
 Tescom, Emerson Process Management, and the Emerson Process Management design are marks of one of the Emerson Process Management group of companies. All other marks are the property of their respective owners.