

NOW AVAILABLE

- Polyetheretherketone (PEEK) soft seat option for ANSI Class VI shutoff at temperatures up to 400°F / 204°C
- Expanded spring ranges on smaller sizes of Type SR8 models NPS 1/2 to 1-1/2 / DN 15 to 40 allowing setpoints up to 125 psi / 8,6 bar

Other Options

- Pressure loaded spring case design permits varying setpoints from a remote location
- Barstock machined version of the 316 Stainless steel spring case for aesthetics
- 10 Ra finish (optional) on wetted surfaces
- Vacuum protection option including a lower diaphragm support to protect against vacuum conditions
- Gauge port in body
- T-Handle adjusting screw
- Various DIN and ISO end connections



Emerson Process Management Regulator Technologies, Inc.

**Americas
Worldwide Headquarters**
310 East University Drive
McKinney, Texas 75069-1872 USA
T: +1 800 558 5853
T: +1 972 548 3574
F: +1 972 542 6433

TESCOM Corporation
12616 Industrial Boulevard
Elk River, Minnesota 55330-2445 USA
T: +1 800 447 1250
T: +1 763 241 3238
F: +1 763 241 3224

For further information visit www.emersonprocess.com/regulators

D350923X012 © 2011 Emerson Process Management Regulator Technologies, Inc. All rights reserved. Printed in the U.S.A. 10/11.
Fisher, Emerson Process Management, and the Emerson Process Management design are marks of one of the Emerson Process Management group of companies. All other marks are the property of their respective owners.



Emerson Process Management Regulator Technologies, Inc.

Europe
Natural Gas: T: +39 051 4190611
Industrial: T: +39 051 4190606
LP-Gas: T: +420 2 710 35 607
TESCOM: T: +49 (0) 38823 31 0

Emerson Process Management Regulator Technologies, Inc.

Asia Pacific
T: +65 6770 8337
Middle East
T: +971 4811 8100



Fisher Types SR5 + SR8

The Clean, Clear
Choice for Sanitary
Process Control



EMERSON. CONSIDER IT SOLVED.

Engineered for precise pressure control in a sanitary environment.

Fisher® Type SR5 Sanitary Pressure Reducing Regulator and Type SR8 Sanitary Backpressure Regulator are designed for applications in pharmaceutical, biotechnology, food and beverage, consumer products, cosmetics, chemical, and other industries – where sanitary process control is required for steam, gases, and liquids.

Fisher Sanitary Regulators Features:

- FDA and USP Class VI approved elastomers
- Designed exclusively for use in clean/sterile environments
- Superior flow performance and accuracy
- Available in sizes NPS 1/2, 3/4, 1, 1-1/2, 2, and 3 / DN 15, 20, 25, 40, 50, and 80
- Suitable for clean-in-place (CIP) and sanitize-in-place (SIP) systems
- Suitable for water-for-injection (WFI) and clean steam systems
- Self-draining design
- Tri-Clamp® end connections

Fisher Types SR5 + SR8


The Clean, Clear
Choice for Sanitary
Process Control




Construction materials enhance purity of plant products and environment.

Each Fisher Sanitary Regulator has a 316L Stainless steel body, wetted metal trim parts and a 316 Stainless steel spring case. The wetted surfaces are mechanically polished to a 20 R_a Microinch finish (standard) and then electropolished. Diaphragms are available in 316L Stainless steel, Fluorocarbon (FKM) with a Polytetrafluoroethylene (PTFE) coating or Ethylenpropylene (EPDM). Metal or soft seats are available.


Type SR5 Pressure Reducing



Sanitary Regulator Performance Comparison



Type SR8 Backpressure



The Fisher Type SR8 Sanitary Regulator has the same superior construction and features as the Type SR5 but functions as a backpressure regulator.

Superior flow performance and accuracy.

To evaluate the performance of a regulator, compare the stated capacities at equivalent operating pressures and offset factors. The Type SR5 is designed to deliver high flows with minimal offset to maintain an even pressure over the full range of flow. In addition, the large turndown ratio eliminates the need for reduced flow (C_v) trims.