

CG-Hoses DIN

DIN 13260II - NIST

MEDI
CAL



Europe only

Angle plug DIN 13260 II, gascode marking and hose colour neutral, with NIST-connector, length of hose 1,5 m

- O₂ = D45690-72N150-56
- Air = D45691-72N150-56
- Air/O₂ = D45695-72N150-56
- Vac = D45694-72N150-56
- N₂O = D45693-72N150-56
- CO₂ = D45692-72N150-56

Angle plug DIN 13260 II, gascode marking and hose colour acc. to ISO 32, with NIST-connector, length of hose 1,5 m

- O₂ = D45690-72I150-56
- Air = D45691-72I150-56
- Air/O₂ = D45695-72I150-56
- Vac = D45694-72I150-56
- N₂O = D45693-72I150-56
- CO₂ = D45692-72I150-56

Angle plug DIN 13260 II, gascode marking and hose colour neutral, with NIST-connector, length of hose 3 m

O₂ = D45690-72N300-56
Air = D45691-72N300-56
Air/O₂ = D45695-72N300-56
Vac = D45694-72N300-56
N₂O = D45693-72N300-56
CO₂ = D45692-72N300-56

Angle plug DIN 13260 II, gascode marking and hose colour acc. to ISO 32, with NIST-connector, length of hose 3 m

O₂ = D45690-72I300-56
Air = D45691-72I300-56
Air/O₂ = D45695-72I300-56
Vac = D45694-72I300-56
N₂O = D45693-72I300-56
CO₂ = D45692-72I300-56

Angle plug DIN 13260 II, gascode marking and hose colour neutral, with NIST-connector, length of hose 5 m

O₂ = D45690-72N500-56
Air = D45691-72N500-56
Air/O₂ = D45695-72N500-56
Vac = D45694-72N500-56
N₂O = D45693-72N500-56
CO₂ = D45692-72N500-56

Angle plug DIN 13260 II, gascode marking and hose colour acc. to ISO 32, with NIST-connector, length of hose 5 m

O₂ = D45690-72I500-56
Air = D45691-72I500-56
Air/O₂ = D45695-72I500-56
Vac = D45694-72I500-56
N₂O = D45693-72I500-56
CO₂ = D45692-72I500-56

Europe only