

Part Number D301153X012

October 2015

FloBoss™ 103 and 104 Flow Manager Instruction Manual



FloBoss 103



FloBoss 104

Remote Automation Solutions

Revision Tracking Sheet

October 2015

This manual may be revised periodically to incorporate new or updated information. The revision date of each page appears at the bottom of the page opposite the page number. A change in revision date to any page also changes the date of the manual that appears on the front cover. Listed below is the revision date of each page (if applicable):

Page	Revision
All pages	October-2015
All pages	February-2015
All pages	July-2014
All pages	August-2011
All pages	August-2004
All pages	April-2004
All pages	December-2003
All pages	October-2002
Initial issue	April-2002

Contents

Chapter 1 – General Information	1-1
1.1 Scope of Manual	1-1
1.2 Product Overview.....	1-2
1.2.1 Components and Features.....	1-3
1.2.2 Hardware.....	1-5
1.2.3 Firmware	1-8
1.2.4 Options and Accessories	1-9
1.2.5 FCC Information.....	1-10
1.3 Product Functions	1-10
1.3.1 Flow Measurement.....	1-11
1.3.2 History Points	1-12
1.3.3 Security	1-15
1.3.4 Function Sequence Tables (FST).....	1-15
1.3.5 PID Control.....	1-15
1.3.6 Spontaneous-Report-By-Exception (SRBX) Alarming.....	1-15
1.3.7 Pass Through Communications.....	1-16
1.3.8 Protocol Automatic Switching.....	1-16
1.3.9 User C Capability	1-16
1.4 Product Electronics	1-16
1.4.1 Termination Board Overview.....	1-16
1.4.2 Processor and Memory	1-17
1.4.3 Liquid Crystal Display.....	1-17
1.4.4 Communications Ports	1-17
1.4.5 RTD Input.....	1-19
1.4.6 Real-Time Clock.....	1-19
1.4.7 Diagnostic Monitoring.....	1-19
1.4.8 Automatic Self Tests	1-19
1.4.9 Low Power Mode	1-20
1.5 Additional Technical Information.....	1-21
 Chapter 2 – Installation and Use	 2-1
2.1 Installation Overview	2-1
2.2 Installation Requirements.....	2-2
2.2.1 Environmental Requirements.....	2-2
2.2.2 Site Requirements.....	2-3
2.2.3 Compliance with Hazardous Area Standards	2-3
2.3 Mounting.....	2-4
2.3.1 General Guidelines	2-4
2.3.2 Pipe Stand Mounting (FloBoss 103/FloBoss 104).....	2-7
2.3.3 Orifice Plate Mounting (FloBoss 103)	2-7
2.3.4 Meter Mounting (FloBoss 104).....	2-8
2.4 Startup and Operation.....	2-11
2.4.1 Starting the FB100	2-12
2.4.2 Operation.....	2-13

2.5	Configuration.....	2-13
-----	--------------------	------

Chapter 3 – Power Connections **3-1**

3.1	Power Installation Requirements	3-1
3.2	Grounding Installation Requirements.....	3-2
3.2.1	Grounding Guidelines	3-2
3.2.2	Installing Grounding for the FB100	3-3
3.3	Determining Power Requirements	3-4
3.4	Solar Powered Installations.....	3-4
3.4.1	Sizing the Solar Panel.....	3-5
3.5	Batteries	3-6
3.5.1	Overcharging Potential.....	3-6
3.5.2	Determining Battery Requirements.....	3-7
3.5.3	Replacing the Batteries	3-7
3.6	Wiring Connections	3-8
3.6.1	Wiring Connections.....	3-8
3.6.2	Connecting Enclosure Ground Wiring.....	3-8
3.6.3	Connecting Main Power Wiring.....	3-9
3.7	Backing Up Configuration and Log Data.....	3-10

Chapter 4 – Input/Output **4-1**

4.1	I/O Description	4-1
4.1.1	Selecting the Type of I/O	4-2
4.2	I/O Wiring Requirements.....	4-3
4.3	Analog Input.....	4-3
4.3.1	Wiring the Analog Input.....	4-3
4.4	Analog Output	4-4
4.4.1	Wiring the Analog Output (6-point I/O Board).....	4-4
4.4.2	Wiring the Analog Output (4-point I/O Board).....	4-5
4.5	Discrete Input	4-5
4.5.1	Wiring the Discrete Input.....	4-6
4.6	Discrete Output	4-6
4.6.1	Wiring the Discrete Output.....	4-7
4.7	Pulse Input	4-7
4.7.1	Wiring the Pulse Input.....	4-7
4.8	RTD Input.....	4-8
4.8.1	Wiring the RTD Input.....	4-8

Chapter 5 – Communications **5-1**

5.1	Communications Overview	5-1
5.2	EIA-485 (RS-485) Communications Wiring	5-2
5.3	Local Operator Interface Port Wiring	5-2
5.4	Serial Communications Card	5-3
5.5	Dial-up Modem Communications Card	5-4

Chapter 6 – Dual-Variable Sensor (DVS) **6-1**

6.1	Dual-Variable Sensor	6-1
6.1.1	Making Process Connections	6-2
6.1.2	Configuring the DVS	6-2

Chapter 7 – Pulse Interface Module **7-1**

7.1	Pulse Interface Module	7-1
7.1.1	Making Process Connections.....	7-3
7.1.2	Configuring the Pulse Interface Module.....	7-3

Chapter 8 – Calibration **8-1**

8.1	Calibration (AI, RTD & Meter)	8-1
8.2	Performing a Calibration	8-1
8.3	Adjusting for Zero Shift.....	8-7
8.4	Verifying a Calibration	8-8

Chapter 9 – Troubleshooting **9-1**

9.1	Troubleshooting Guidelines	9-1
9.2	Troubleshooting Checklists	9-2
9.2.1	Dial-up Modem	9-2
9.2.2	Serial Communications	9-2
9.2.3	Optional I/O	9-2
9.2.4	Software Issues.....	9-3
9.2.5	Power Issues.....	9-3
9.2.6	Dual-Variable Sensor (FB103).....	9-3
9.2.7	Pulse Interface Module (FB104)	9-4
9.2.8	Resistance Temperature Detector	9-4
9.3	Procedures	9-5
9.3.1	Preserving Configuration and Log Data.....	9-5
9.3.2	Resetting the FB100	9-5
9.3.3	Restarting and Reconfiguring.....	9-6
9.3.4	Connecting the Termination Board to the Backplane	9-7

Appendix A – Glossary **A-1**

Index **I-1**

[This page is intentionally left blank.]